





N ATTENUATOR 20 DB 3 GHZ 50W

PAGE 1/2 ISSUE 18-03-16B SERIES PART NUMBER R417020120

**SCALE 1:2** 





All dimensions are in mm.



| COMPONENTS            | MATERIALS        | PLATING (μm)                      |
|-----------------------|------------------|-----------------------------------|
| 5 1                   | 074111 F00 07FF1 | DAGGNATED                         |
| Body                  | STAINLESS STEEL  | PASSIVATED                        |
| Male center contact   | BERYLLIUM COPPER | GOLD 0.5 OVER NICKEL PHOSPHORUS 2 |
| Female center contact | BERYLLIUM COPPER | GOLD 0.5 OVER NICKEL PHOSPHORUS 2 |
| Outer contact         | -                | -                                 |
| Insulator             | PTFE             |                                   |
| Gasket                | SILICONE RUBBER  |                                   |
| Substrate             | ALUMINA          |                                   |
| Resistor              | THICK FILM       |                                   |
| Others parts          | ALUMINIUM        | BLACK PAINTING                    |







PAGE 2/2 ISSUE 18-03-16B SERIES PART NUMBER R417020120

## **ELECTRICAL CHARACTERISTICS**

| Frequency (GHz) | DC - 1 | 1 - 2 | 2 - 3 |
|-----------------|--------|-------|-------|
| V.S.W.R (≤)     | 1.10   | 1.25  | 1.35  |
| Deviation(±dB)  | 2.00   | 2.00  | 2.00  |

| Operating Frequency Range   | DC - 3 | GHz                   |  |
|---|--------|-----------------------|--|
| Impedance   | 50     | Ω                     |  |
| Nominal Attenuation   | 20     | dB                    |  |
| Peak power at 25°C (1µs, 1‰)  | 5000   | W                     |  |
| Average power at 25°C   | 40     | W (Free Air Cooled)   |  |
|   | 50     | W (Conduction Cooled) |  |
| For conduction cooling, a plate 500 cm2 x 3 mm(78 sq.in*1/8) min. is required |        |                       |  |


## MECHANICAL CHARACTERISTICS

| Connectors | N                 | Male Female | MIL-C 39012 |
|------------|-------------------|-------------|-------------|
| Weight     | <b>357,2700</b> g |             |             |

## **ENVIRONMENTAL CHARACTERISTICS**

| Operating temperature range | -55 /+125 | °C |
|-----------------------------|-----------|----|
| Storage temperature range   | -55 /+125 | °C |

#### Power derating Versus temperature



# **SPECIFICATION**

# OTHER CHARACTERISTICS