
PART NO. RFD-43M-F							
REV	DESCRIPTION	DWN	DATE	APPROVED			
	ENGINEERING RELEASE	CZS	11/14/19	JDMc			



SPECIFICATIONS:

IMPEDANCE: 50 OHMS FREQUENCY RANGE: DC-7.5 GHz VSWR MAX: <1.1 @ 3GHz 3rd ORDER IM: <-160 dBc

						ARE REFERENCE UNLI		
7	SHELL	1	BRASS	WHITE BRONZE	UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES			
6	GASKET	1	SI RUBBER					
5	C-RING	1	BRASS		AND [MILLIMETERS]			
4	CONTACT	1	BeCu	SILVER	DRAWN	11/14/19		
3	PIN	1	BeCu	SILVER	C. ZUNIGA	11/14/19		
2	INSULATOR	1	PTFE		CHECKED			
1	BODY	1	BRASS	WHITE BRONZE	ORJ DRAWN			
#	DESCRIPTION	QTY	MATERIAL	FINISH	C. ZUNIGA	11/14/19		

CUSTOMER OUTLINE DRAWING

ALL DIMENSIONS ARE REFERENCE ONLY

> THIS DRAWING CONTAINS
> INFORMATION PROPRIETARY TO
> RF INDUSTRIES, ANY
> UNAUTHORIZED USE OF THIS
> DRAWING IS EXPRESSLY
> PROHIBITED WITHOUT WRITTEN PERMISSION FROM RF
> INDUSTRIES. ANY VIOLATION :
> PUNISHABLE UNDER U.S. COPYRIGHT LAWS.

PROPRIETARY AND CONFIDENTIAL

Jeonne Cors (858) 549-6340 DIVISION OF RF INDUSTRIES, LTD. (858) 549-6345 FAX

7610 MIRAMAR RD.

4.3-10 MALE TO FEMALE ADAPTER

, I											
۱ ۱	SIZE	CABLE	GROUP	DWG NO.					REVISION		
EN IS	А	N	/A	RFD-43M-F							
13	SCALE	: NTS	ENGINEE	RING IE	000000	SHEET	1	OF	1		