

#### SURFACE MOUNT MICROPROCESSOR CRYSTAL

Page 1 of 3

#### RH100-38.400-10-F-1010-TR


## SPECIFICATIONS

PARAMETER	VALUE
NOMINAL FREQUENCY	38.400 MHz
MODE OF OSCILLATION	Fundamental
FREQUENCY TOLERANCE AT 25°C	±10 ppm max
FREQUENCY STABILITY OVER TEMPERATURE	±10 ppm max
OPERATING TEMPERATURE RANGE	-20°C to +70°C
STORAGE TEMPERATURE RANGE	-40°C to +85°C
AGING	±2 ppm per year max
LOAD CAPACITANCE	10 pF
EQUIVALENT SERIES RESISTANCE	60 Ω max
SHUNT CAPACITANCE	5 pF max
DRIVE LEVEL	500 μW max
INSULATION RESISTANCE	500 MΩ min




Photo is not actual part

## MECHANICAL SPECIFICATION



# CARRIER TAPE DIMENSIONS



NOTE: REFER TO EIA-481 FOR DIMENSIONS

## PACKAGING

178 mm REEL DIAMETER 8 mm TAPE WIDTH, 4 mm PITCH QUANTITY: 3000 PIECES PER REEL


IN ACCORDANCE WITH EIA-481

# SURFACE MOUNT MICROPROCESSOR CRYSTAL

Page 2 of 3

## RH100-38.400-10-F-1010-TR

## REFLOW PROFILE



Reflow profile				
Temperature Min Preheat	T <sub>SMIN</sub>	125°C		
Temperature Max Preheat	T <sub>SMAX</sub>	150°C		
Time (T <sub>SMIN</sub> to T <sub>SMAX</sub> )	ts	60-180 sec.		
Temperature	T∟	217°C		
Peak Temperature	$T_P$	260°C		
Ramp-up rate	R <sub>UP</sub>	3°C/sec max.		
Ramp-down rate	R <sub>DOWN</sub>	6°C/sec max.		
Time within 5°C of Peak Temperature	t <sub>P</sub>	10 sec.		
Time t[25°C] to Peak Temperature	t[25°C] to Peak	480 sec.		
Time	t∟	60-150 sec.		

# ENVIRONMENTAL

PARAMETER	VALUE
MOISTURE SENSITIVITY LEVEL	1
RoHS	Compliant
REACH SVHC	Compliant
HALOGEN-FREE	Compliant
ESD CLASSIFICATION LEVEL	N/A
TERMINATION FINISH	Au





#### SURFACE MOUNT MICROPROCESSOR CRYSTAL

Page 3 of 3

RH100-38.400-10-F-1010-TR

#### MARKING

R38.400 xxKEyw

x – Internal Production ID code

y - Year code

w - Week code

YEAR CODE		
Year	Code	
2019	9	
2020	0	
2021	1	
2022	2	
2023	3	
2024	4	
2025	5	
2026	6	
2027	7	
2029	8	
2029	9	

ALPHA WEEK CODE TABLE					
Week	Code	Week	Code	Week	Code
1	a	19	s	37	K
2	b	20	t	38	L
3	c	21	u	39	M
4	d	22	v	40	N
5	e	23	w	41	О
6	f	24	X	42	P
7	g	25	У	43	Q
8	h	26	z	44	R
9	i	27	A	45	S
10	j	28	В	46	T
11	k	29	C	47	U
12	1	30	D	48	V
13	m	31	E	49	W
14	n	32	F	50	X
15	0	33	G	51	Y
16	p	34	H	52	Z
17	q	35	I		
18	r	36	J		

#### APPROVAL

DRAWN BY	KJackson, February 26, 2016
APPROVED BY	KJackson, February 26, 2016
REVISION	A, Initial Release
	B, Updated to current spec levels
	KJ 1/26/17
	C, , Updated to current spec levels
	by XS, February 18, 2021

Raltron Electronics / RAMI Technology USA, LLC, including its affiliates, employees, agents and other persons acting on its behalf (collectively Raltron/RAMI Tech), disclaim any and all liability for any errors or inaccuracies contained in this data sheet. While Raltron/RAMI Tech has made every reasonable effort ensure the accuracy of all product information, specifications and data contained herein, Raltron/RAMI Tech does not guarantee that the information is provided only for reference purposes only and is subject on or revision, at any time without notice. Raltron/RAMI Tech does not assume any liability arising out of an application or use of any product described herein and disclaims any warranties expressed or implied. The user of products in such applications shall assume all risks of such use and will agree to hold Raltron/RAMI Tech, harmless against all damages.

Copyright © 2016, Raltron Electronics / RAMI Technology USA, LLC. All rights reserved. No part of this document may be reproduced in any form without the prior written permission of Raltron Electronics / RAMI Technology USA, LLC.