





COAXIAL TERMINATION TNC MALE 6 GHZ 30W

PAGE 1/2 ISSUE 06-11-19B SERIES TERMINATION PART NUMBER R404752000





All dimensions are in mm. Tolerances according ISO 2768 m-H



COMPONENTS	MATERIALS	PLATING (μm)
Body	STAINLESS STEEL	PASSIVATED
,	***************************************	
Center contact	BERYLLIUM COPPER	GOLD 0.5 OVER NICKEL PHOSPHORUS 2
Outer contact		
Insulator	PTFE	
Gasket	SILICONE RUBBER	
Substrate	ALUMINIUM NITRIDE	
Resistor	THICK FILM	
Others parts	ALUMINIUM	BLACK ANODIZATION





COAXIAL TERMINATION TNC MALE 6 GHZ 30W

PAGE 2/2	ISSUE 06-11-19B	SERIES TERMINATION	PART NUMBER R404752000
-----------------	-----------------	-----------------------	-------------------------------

ELECTRICAL CHARACTERISTICS

Frequency (GHz)	DC - 3	3 - 6
V.S.W.R (≤)	1.20	1.40

DC - 6	GHz	
50	Ω	
50	Ω ± 5%	
2000	W	
30	W (Free Air Cooled)	
	W (Conduction Cooled)	
	50 50 2000	


MECHANICAL CHARACTERISTICS

Connectors	TNC	Male	MIL C39012
Weight	187,1900 g		

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range	-55/+125	°C
Storage temperature range	-55/+125	°C

Power derating Versus temperature



SPECIFICATION

OTHER CHARACTERISTICS

MOUNTED WITH VERTICAL COOLING FINS AND NATURAL CONVECTION