
**Technical Data Sheet** 

TNC ATTENUATOR 19 DB 3 GHZ 1W





This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.

## **Technical Data Sheet**

TNC ATTENUATOR 19 DB 3 GHZ 1W



	1550E <b>U</b>	9-04-20B	SERIE ATTENUA	S Ator		PA	ART NUMB	ER <b>R412519124</b>	
			Ē	ELECTRIC	CAL CHA	RACTERIST	<u>cs</u>		
From		-	DC - 2	2	- 3	1			
	Frequency (GHz) V.S.W.R (≤)		1.20		- 3 .30	-			
	iation(±dB)		1.0		1.0	-			
	~ /					1			
Ope	rating Frequ	ency Range	9			DC - 3		GHz	
	Impedance Nominal Attenuation		0					Ω	
Nom				50 19			dB		
Peak power at 25°C					100			W	
Ave	rage power a	at 25°C				1		W (Free Air Cooled)	
								W (Conduction Coole	ed)
Wei	ynt		16,77	g					
							7100		
			EN erating tempe rage tempera	rature ran	ige	IARACTERIS	-40 / +85 °	C C	
			erating tempe rage tempera	rature ran ture range	e	HARACTERIS	-40 / +85 ° -40 / +85 °		
			erating tempe	rature ran ture range	r derating Ve		-40 / +85 ° -40 / +85 °		
			2rating temper rage tempera (%) under (%) unde	Power	r derating Ve	ersus temperatur	-40 / +85 ° -40 / +85 °		
			2rating temper rage tempera (%) under (%) unde	Power	e derating Va derating Va -7.5 Temp	ersus temperatur	-40 / +85 ° -40 / +85 °		

This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.