






N ATTENUATOR 6 DB 2 GHZ 100W

PAGE 1/2 ISSUE 27-02-18B SERIES ATTENUATOR PART NUMBER R417706118







All dimensions are in mm.



COMPONENTS	MATERIALS	PLATING (μm)
Body Male center contact	STAINLESS STEEL BERYLLIUM COPPER	PASSIVATED GOLD 0.5 OVER NICKEL PHOSPHORUS 2
Female center contact Outer contact	BERYLLIUM COPPER	GOLD 0.5 OVER NICKEL PHOSPHORUS 2
Insulator Gasket Substrate	PTFE SILICONE RUBBER ALUMINA	
Resistor Others parts	THICK FILM ALUMINIUM	BLACK PAINTING





N ATTENUATOR 6 DB 2 GHZ 100W

PAGE 2/2	ISSUE 27-02-18B	SERIES ATTENUATOR	PART NUMBER R417706118
-----------------	------------------------	----------------------	-------------------------------

ELECTRICAL CHARACTERISTICS

Frequency (GHz)	DC - 1	1 - 2
V.S.W.R (≤)	1.10	1.25
Deviation(±dB)	1.0	1.0

Operating Frequency Range	DC - 2	GHz
Impedance	50	Ω
Nominal Attenuation	6	dB
Peak power at 25°C (1µs, 1‰)	5000	W
Average power at 25°C	100	W (Free Air Cooled)
		W (Conduction Cooled)


MECHANICAL CHARACTERISTICS

Connectors	N	Male Female	MIL-C 39012
Weight	712,1200 g		

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range	-55 /+125 °C
Storage temperature range	-55 /+125 °C

Power derating Versus temperature



SPECIFICATION

OTHER CHARACTERISTICS