#### **Micro RF Coaxial Connector**

# MHF<sup>®</sup> 5

Low-profile (mated height = 1.0 mm max.), supports to 12 GHz

Product Specifications:			Applicable Cable Size:	
Mated Heigh	nt (mm max.)	1.0	0.D. 0.48 mm / AWG 38	
Rece. SMT	Size (mm)	2.0 x 2.0	O.D. 0.64 mm / AWG 36	
Applicable	Frequency	DC ~ 12 GHz	O.D. 0.81 mm / AWG 36	
Characteristic Impedance		50 ohm		
VSWR (L=100 mm)	DC~3 GHz	(1)(2)(3) 1.3 max.	Applicable Standards (Refe	
	$3\sim$ 6 GHz	(1)(2)(3) 1.5 max.	5G sub-6, Wi-Fi 6E, LTE/LT LPWA, Bluetooth, GPS	
	$6\sim$ 9 GHz	(1)(2)(3) 1.6 max.		
	9~12 GHz	(1) 1.6 max. (2) 1.8 max. (3) 1.7 max.		

O.D. 0.64 mm / AWG 36
O.D. 0.81 mm / AWG 36
Applicable Standards (Reference Only): 5G sub-6, Wi-Fi 6E, LTE/LTE-Advanced, LPWA, Bluetooth, GPS







\* Please inquire for pin counts not listed or outside of the pin count range.

\* Cable size O.D. (1) 0.48 mm, (2) 0.64 mm (3) 0.81 mm

#### Small form factor with big performance through 12 GHz



#### Lowest profile connector of MHF<sup>®</sup> series



#### MHF<sup>®</sup> 5 Plug available cable O.D. (AWG) : 0.81 mm (36), 0.64 mm (36), 0.48 mm (38)

Product na	me	MHF <sup>®</sup> 5	MHF <sup>®</sup> 5L
Mating Hei	ght	1.0 mm max.	1.3 mm max.
	1.13 mm (AWG#32)		
	0.81 mm (AWG#33)		
Coax O.D. (Center Conductor AWG)	0.81 mm (AWG#36)		
	0.64 mm (AWG#36)		
	0.48 mm (AWG#38)		
Receptacl	e	MHF	<sup>®</sup> 5 receptacle





## **Component Parts Details**

#### <u>MHF® 5 plug Au (0.81,0.64)</u>

Recommended F	P/N	20669-		
PART NO.	APPI	ICABLE CABLE	OUTER COND	UCTOR
20669-001R-81	AWO	G#36 (0.64 O.D.)	SPIRAL SHI	IELD
20009-0018-01	AWO	G#36 (0.81 O.D.)	SINGLE BRAIDE	d shield

OFFERED AS HARNESS ONLY.







NOTES 1. APPLICABLE CONNECTOR

20566-001E-01

2. PERMISSIBLE LOAD OF CABLE AT MATING

3. MATING AND UNMATING INSTRUCTION

3-1. MATING

MATE THE CONNECTOR VERTICALY AS MUCH AS POSSIBLE, ADJUSTING THE MATING AXIS OF PLUG AND RECEPTACLE. DO NOT SLANT MATE.

3-2. UNMATING

3-2-1. IN CASE OF UNMATING BY PULLING TOOL (PART NO. 90612-0001)

USE THE PULLING TOOL AS THE FOLLOWING DRAWING, AND PULL PLUG TO VERTICAL DIRECTION AS DIRECTLY AS POSSIBLE.

#### 3-2-2. IN CASE OF UNMATING DIRECTLY BY HAND.

MATING CONDITION


Rev.4

## <u>MHF® 5 plug Au (0.81,0.64)</u>

ITEMS	SPECIFICATION				
APPLICABLE CABLE	AWG#36(0.81 O.D.)	AWG#36(0.64 O.D.)			
RECOMMENDED APPLICABLE CONNECTOR PART No.	20566-001E-01				
RATING VOLTAGE	60 V AC	(R.M.S)			
RATING FREQUENCY	DC~12	2 GHz			
OPERATING TEMPERATURE	233~363 K (-4	40°C∼+90°C)			
VSWR (MATED WITH SMA ADAPTER PART No. 90543- 0001)	1.30 MAX. AT 0.1~3 GHz, 1.50 MAX. AT 3~6 GHz, 1.60 MAX. AT 6~9 GHz, 1.70 MAX. AT 9~12 GHz	1.30 MAX. AT 0.1∼3 GHz, 1.50 MAX. AT 3∼6 GHz, 1.60 MAX. AT 6∼9 GHz, 1.80 MAX. AT 9∼12 GHz			
MAIN CONTACT RESISTANCE	INITIAL: 20 mohm MAX. / AFTER TEST: AR 20 mohm MAX.				
GROUND CONTACT RESISTANCE	INITIAL: 20 mohm MAX. / AFTER TEST: ZR 20 mohm MAX.				
INSULATION RESISTANCE	INITIAL: 500 Mohm MIN. / AF	TER TEST: 100 Mohm MIN.			
DIELECTRIC WITHSTANDING VOLTAGE	200 V AC,	1 MINUTE			
DURABILITY	30 CY(	CLES			
UNMATING FORCE (INITIAL / AFTER TEST)	INITIAL: 4 N MIN. / AF	TER TEST: 2 N MIN.			
CRIMP STRENGTH	7 N MIN.				
PRODUCT SPECIFICATION	PRS-2532 PRS-2782				
TEST REPORT	TR-18089	TR-22018			
INSTRUCTION MANUAL	HIM-16014				
APPEARANCE CRITERIA No. QLS-A***					

#### Rev.4

#### <u>MHF® 5 plug Ni top (0.81,0.64)</u>



#### HATCHED AREA: Ni PLATING AREA






Halogen Free RoHS Compliant

HF





MATE THE CONNECTOR VERTICALY AS MUCH AS POSSIBLE, ADJUSTING THE MATING AXIS OF PLUG AND RECEPTACLE. DO NOT SLANT MATE.

3-2. UNMATING


3-1. MATING


NOTES.


3-2-1. IN CASE OF UNMATING BY PULLING TOOL (PART NO. 90612-0001)


1. APPLICABLE CONNECTOR: 20566-001E-01 2. PERMISSIBLE LOAD OF CABLE AT MATING 3. MATING AND UNMATING INSTRUCTION

> USE THE PULLING TOOL AS THE FOLLOWING DRAWING, AND PULL PLUG TO VERTICAL DIRECTION AS DIRECTLY AS POSSIBLE.










NOTE 3-2-2.





3	GROUND CONTACT	PHOSPHOR BRONZE	ALL OVER Ni 1.00 μ m MIN. CONTACT PART Au 0.02 μ m MIN. [Ni PLATING AREA] Ni ONLY
2	CONTACT	PHOSPHOR BRONZE	ALL OVER Ni 1.00 $\mu$ m MIN. CONTACT PART Au 0.03 $\mu$ m MIN.
1	HOUSING	LCP	UL94V-0, BLACK
NO.	DESCRIPTION	MATERIAL	FINISH , REMARKS

Rev.6



Contact your sales representative for more detailed information. <u>www.i-pex.com</u>


#### <u>MHF® 5 plug Ni top (0.81,0.64)</u>


ITEMS	SPECIFICATION			
APPLICABLE CABLE	AWG#36 (0.81 O.D.) *RECOMMENDED	AWG#36 (0.64 O.D.)		
RECOMMENDED APPLICABLE CONNECTOR PART No.	20566-	001E-01		
RATING VOLTAGE	60 V AC	C (R.M.S)		
RATING FREQUENCY	DC~1	12 GHz		
OPERATING TEMPERATURE	233~363 K (-	-40°C ~+90°C)		
VSWR (MATED WITH SMA ADAPTER PART No. 90543-0001)	1.30 MAX. AT 0.1~3 GHz, 1.50 MAX. AT 3~6 GHz, 1.60 MAX. AT 6~9 GHz, 1.70 MAX. AT 9~12 GHz	1.30 MAX. AT 0.1~3 GHz, 1.50 MAX. AT3 ~6 GHz, 1.60 MAX. AT 6~9 GHz, 1.80 MAX. AT 9~12 GHz		
MAIN CONTACT RESISTANCE	INITIAL: 20 mohm MAX. / AFTER TEST: ZR 20 mohm MAX.			
GROUND CONTACT RESISTANCE	INITIAL: 20 mohm MAX. / AFTER TEST: AR 100 mohm MAX.			
INSULATION RESISTANCE	INITIAL: 500 Mohm MIN. / AFTER TEST: 100 Mohm MIN.			
DIELECTRIC WITHSTANDING VOLTAGE	200 V AC, 1 MINUTE			
DURABILITY	30 CYCLES			
UNMATING FORCE (INITIAL / AFTER TEST)	INITIAL: 4 N MIN. / AFTER TEST: 2 N MIN.			
CRIMP STRENGTH	7 N MIN.			
PRODUCT SPECIFICATION	PRS-2108 PRS-2109			
TEST REPORT	TR-15062	TR-15063		
INSTRUCTION MANUAL	HIM-16013			
APPEARANCE CRITERIA No.	QLS-A***			


### MHF<sup>®</sup> 5 PLUG Ni top (0.48)

Recommended P/N		20615-002R-48				
PART No.		PLATING	APPLICABLE	CABLE	OUTER CONDUCTOR	
20615-001R-48		ALL Au	AWG#38 (0.48 O.D.)		SPIRAL SHIELD	
20615-002R-48 SI		ELECTIVE Ni	AWG#38 (0.4	ю U.D.)	SPIKAL SHIELD	

OFFERED AS HARNESS ONLY.








NOTES

1. APPLICABLE CONNECTOR: 20566-001E-01 2. PERMISSIBLE LOAD OF CABLE AT MATING 3. MATING AND UNMATING INSTRUCTION 3-1. MATING



SELECTIVE Ni TYPE (PART NO. 20615-002R-48)

HATCHED AREA: Ni PLATING AREA

HF

Halogen Free


Retta

**RoHS Compliant** 


MATE THE CONNECTOR VERTICALY AS MUCH AS POSSIBLE, ADJUSTING THE MATING AXIS OF PLUG AND RECEPTACLE. DO NOT SLANT MATE. 3-2. UNMATING


3-2-1. IN CASE OF UNMATING BY PULLING TOOL (PART NO. 90612-0001): USE THE PULLING TOOL AS THE FOLLOWING DRAWING, AND PULL PLUG TO VERTICAL DIRECTION AS DIRECTLY AS POSSIBLE.


3-2-2. IN CASE OF UNMATING DIRECTLY BY HAND: CATCH THE CATCHING AREA OF PLUG, AND PULL PLUG



4. PRECAUTIONS FOR CABLE POSITION THE PLUG SHALL NOT BE PLACED WITHIN 50 DEGREES ANGLE FROM CENTER OF THE SIGNAL CONTACT. TILT THE PLUG AT LEAST 50 DEGREES FROM THE CENTER OF A SIGNAL CONTACT.







3	GROUND CONTACT		ALL OVER Ni 1.00 μ m MIN. CONTACT PART Au 0.05 μ m MIN.
2	CONTACT		ALL OVER Ni 1.00 μ m MIN. CONTACT PART Au 0.05 μ m MIN.
1	HOUSING	LCP	UL94V-0, BLACK
NO.	DESCRIPTION	MATERIAL	FINISH , REMARKS

MATING CONDITION

Rev.7

### MHF<sup>®</sup> 5 PLUG Ni top (0.48)


ITEMS	SPECIFICATION			
PLUG PART No.	20615-001R-48 (ALL Au PLATING TYPE)	20615-002R-48 (SELECTIVE Ni PLATING TYPE)		
RECOMMENDED APPLICABLE CONNECTOR PART No.	20566-0	001E-01		
RATING VOLTAGE	60 V AC	(R.M.S)		
RATING FREQUENCY	DC~1	2 GHz		
OPERATING TEMPERATURE	233∼363 K (-	-40°C~+90°C)		
VSWR (MATED WITH SMA ADAPTER PART No. 90543-0001)	1.30 MAX. AT 0.1 ~ 3 GHz, 1.50 MAX. AT 3 ~ 6 GHz, 1.60 MAX. AT 6 ~ 12 GHz			
MAIN CONTACT RESISTANCE	INITIAL: 20 mohm MAX. / AFTER TEST: ⊿R 20 mohm MAX.			
GROUND CONTACT RESISTANCE	INITIAL: 20 mohm MAX. / AFT	TER TEST: ⊿R 20 mohm MAX.		
INSULATION RESISTANCE	INITIAL: 500 Mohm MIN. / A	FTER TEST: 100 Mohm MIN.		
DIELECTRIC WITHSTANDING VOLTAGE	200 V AC, 1 MINUTE			
DURABILITY	30 CYCLES			
UNMATING FORCE (INITIAL / AFTER TEST)	INITIAL: 4 N MIN. / AFTER TEST: 2 N MIN.			
CRIMP STRENGTH	7 N MIN.			
PRODUCT SPECIFICATION	PRS-1939	PRS-2032		
TEST REPORT	TR-14026	TR-15029		
INSTRUCTION MANUAL	HIM-13003			
APPEARANCE CRITERIA No.	QLS-	-A***		




.







#### **MHF® 5 Receptacle**



2	CONTACT BRASS		ALL OVER Ni 1.00 $\mu$ m MIN. CONTACT PART Au 0.1 $\mu$ m MIN. SOLDERING PART Au 0.03 $\mu$ m MIN.		
1	HOUSING	LCP	UL94V-0, BLACK		
NO.	DESCRIPTION	MATERIAL	FINISH, REMARKS		


#### **MHF<sup>®</sup> 5 Receptacle**


•

ITEMS			SPECIFICATION		
RECOMMENDED APPLICABLE CONNECTOR PART No.	20668-001R-13	20711-001R-81 (CABLE AWG#36 φ0.81)	20714-001R-81	20711-001R-81 (CABLE AWG#36 ¢0.64)	20615-001R-48 (ALL Au PLATING TYPE)
RATING VOLTAGE			60 V AC (R.M.S)		
RATING FREQUENCY			DC~15 GHz		
OPERATING TEMPERATURE			233~363 K (-40°C~+90°	C)	
VSWR (MATED WITH SMA ADAPTER PART No. 90543-0001)			. AT 0.1∼3 GHz, 1.40 MAX . AT 6∼12 GHz, 1.65 MAX. A		
MAIN CONTACT RESISTANCE		INITIAL: 20 m	ohm MAX. / AFTER TEST: 2	⊴R 20 mohm MAX.	
GROUND CONTACT RESISTANCE	INITIAL: 20 mohm MAX. / AFTER TEST: ⊿R 100 mohm MAX. INITIAL: 20 mohm MAX. AFTER TEST: ⊿R 20 moh				
INSULATION RESISTANCE		INITIAL: 50	0 Mohm MIN. / AFTER TEST	: 100 Mohm MIN.	•
DIELECTRIC WITHSTANDING VOLTAGE					
DURABILITY			30 CYCLES	T	
UNMATING FORCE (INITIAL / AFTER TEST)	INITIAL: 5 N MIN. AFTER TEST: 3 N MIN.	INITIAL: 4 N MIN. AFTER TEST: 2 N MIN.	INITIAL: 5 N MIN. AFTER TEST: 3 N MIN.	INITIAL: 4 N MIN. AFTER TEST: 2 N MIN.	INITIAL: 4 N MIN. AFTER TEST: 2 N MIN.
PRODUCT SPECIFICATION	PRS-2192	PRS-2108	PRS-2236	PRS-2109	PRS-1939
TEST REPORT	TR-16003	TR-15062	TR-16049	TR-15063	TR-14026
PACKING STANDARD	PST-12036				
INSTRUCTION MANUAL	HIM-16014	HIM-16013	HIM-16014	HIM-16013	HIM-13003
APPEARANCE CRITERIA No.			QLS-A***		

Rev.8

#### **MHF® 5 Receptacle**





 $2.50 \pm 0.03$ 

1.50 ±0.03

0.<u>40 ±0</u>03

GROUND CONTACT


TIME (s)

CONNECTOR ON RECOMMENDED FOOTPRINT PATTERN


REFLOW TEMPERATURE PROFILE SENJU METAL INDUSTRY CO., LTD. : M705-SHF(Sn96.5 Ag3.0 Cu0.5)

NOTES. 5. CUT OUT PROHIBITION AREA

**Accessories for MHF® 5 Receptacle** 




SMA ADAPTOR FOR MHF 5 PLUG PART NO. 90543-0001 MHF 5 HIGH CYCLE PROBE PART NO. 90690-0001



MHF 5 HIGH CYC ADAP BASE UNIT PART NO. 90684-0001

\* 90690-0001 AND 90684-0001 SHOULD BE USED TOGETHER.



\* 90847-0001 AND 90577-\*\*\*\* SHOULD BE USED TOGETHER.





I-PEX, MHF, CABLINE, NOVASTACK, EVAFLEX, MINIFLEX, ISH, IARPB, IASLP, ESTORQ, ISFIT, i-Fit and ZenShield are registered trademarks of I-PEX Inc. Please note that the contents in the catalog might be changed without prior notification. I-PEX Inc. assumes no responsibility for any inaccuracies or obligation to update Information on these documents. Please be sure to read and understand the latest "Precautions for Use" and "Instruction

> Manual" before you use our products. We shall not be responsible for any defects, damages or troubles in case you use our products without following the precautions for use. Please feel free to contact our sales representatives when you use our products for any applications that require very high reliability and safety, or that relate to human life (ex. nuclear power control, aerospace, transportation, medical equipment, safety equipment etc.).

> > Contact your sales representative or more detailed information.

www.i-pex.com



## C I-PEX Inc. 2022 All rights reserved.