Resistive Product Solutions

Features:

- Small size and light weight
- Reliability and high quality
- Wider terminations provide higher power handling and more robust thermal performance
- Qualified to AEC-Q200
- RoHS compliant, lead free and halogen free
- REACH compliant

| | Electrical Specifications | | | | | | | | | | |
|-----------|----------------------------|---|---------------------------------|-----------------|--|--|--|--|--|--|--|
| Type/Code | Power Rating (W) @ 70°C | Maximum Working Voltage (V) ⁽¹⁾ | Maximum Overload Voltage (V) | TCR (ppm/⁰C) | Ohmic Range (Ω) and Tolerance ⁽²⁾ 1%, 5% | | | | | | |
| RMCW0508 | 0.75 | | | | | | | | | | |
| RMCW0612 | 0.75 | | | | | | | | | | |
| RMCW1020 | 1 | 200 | 400 | ±200 ±100 | 1 - 9.1 10 - 10M | | | | | | |
| RMCW1218 | 1 | | | | | | | | | | |
| RMCW1225 | 2 | | | | | | | | | | |

(1) Lesser of $\sqrt{P^*R}$ or maximum working voltage

(2) E96 resistance values may be available in 1% tolerance but will be subject to a high MOQ's - contact Stackpole

| Electrical Specifications – RMCW-HP | | | | | | | | | |
|-------------------------------------|----------------------------|---|---------------------------------|-----------------|--|--|--|--|--|
| Type/Code | Power Rating (W) @ 70°C | Maximum Working Voltage (V) ⁽¹⁾ | Maximum Overload Voltage (V) | TCR (ppm/⁰C) | Ohmic Range (Ω) and Tolerance ⁽²⁾ 1%, 5% | | | | |
| RMCW0508HP | 1 | | | ± 150 ± 100 | 1 - 9.1 10 - 1M | | | | |
| RMCW0612HP | 1.5 | | | | | | | | |
| RMCW1020HP | 2 | 200 | 400 | ±100 | 1 - 9.1 | | | | |
| RMCW1218HP | 2 | | | ±100 | 10 - 10M | | | | |
| RMCW1225HP | 3 | | | | | | | | |

(1) Lesser of $\sqrt{P^*R}$ or maximum working voltage

(2) E96 resistance values may be available in 1% tolerance but will be subject to a high MOQ's - contact Stackpole

| Electrical Specifications - Jumper | | | | | | | | |
|------------------------------------|--------------------------|---|-------------------------|--|--|--|--|--|
| Type/Code | Jumper Rated Current (A) | Maximum Overload Current (A) < 1 second and 1 time | Jumper Resistance Value | | | | | |
| RMCW0612 | 4 | 15 | | | | | | |
| RMCW1020 | 6 | 22 | 0.02 max. | | | | | |
| RMCW1218 | 6 | 22 | 0.02 Max. | | | | | |
| RMCW1225 | 8 | 30 | | | | | | |



| Wide | Termination | Thick | Film | Chip | Resistor |
|------|--------------------|-------|------|------|----------|
|------|--------------------|-------|------|------|----------|

-

| | Mechanical Specifications | | | | | | | | | |
|------------|---------------------------|-------------------|-------------------|-------------------|-------------------|--------|--|--|--|--|
| | | | | | | | | | | |
| Type/Code | L | W | Н | l1 | 12 | Unit | | | | |
| RMCW0508 | 0.049 ± 0.004 | 0.079 ± 0.004 | 0.022 ± 0.004 | 0.010 ± 0.008 | 0.020 ± 0.008 | inches | | | | |
| | 1.25 ± 0.10 | 2.00 ± 0.10 | 0.55 ± 0.10 | 0.25 ± 0.20 | 0.50 ± 0.20 | mm | | | | |
| RMCW0612 | 0.063 ± 0.008 | 0.126 ± 0.008 | 0.022 ± 0.004 | 0.012 ± 0.008 | 0.020 ± 0.008 | inches | | | | |
| | 1.60 ± 0.20 | 3.20 ± 0.20 | 0.55 ± 0.10 | 0.30 ± 0.20 | 0.50 ± 0.20 | mm | | | | |
| RMCW1020 | 0.098 ± 0.008 | 0.197 ± 0.008 | 0.022 ± 0.004 | 0.016 ± 0.008 | 0.030 ± 0.008 | inches | | | | |
| | 2.50 ± 0.20 | 5.00 ± 0.20 | 0.55 ± 0.10 | 0.40 ± 0.20 | 0.75 ± 0.20 | mm | | | | |
| RMCW1218 | 0.122 ± 0.004 | 0.181 ± 0.004 | 0.022 ± 0.002 | 0.016 ± 0.008 | 0.020 ± 0.008 | inches | | | | |
| | 3.10 ± 0.10 | 4.60 ± 0.10 | 0.55 ± 0.05 | 0.40 ± 0.20 | 0.50 ± 0.20 | mm | | | | |
| RMCW1225 | 0.126 ± 0.008 | 0.256 ± 0.008 | 0.022 ± 0.008 | 0.016 ± 0.008 | 0.030 ± 0.008 | inches | | | | |
| | 3.20 ± 0.20 | 6.50 ± 0.20 | 0.55 ± 0.20 | 0.40 ± 0.20 | 0.75 ± 0.20 | mm | | | | |
| RMCW1225HP | 0.126 ± 0.008 | 0.256 ± 0.008 | 0.026 ± 0.008 | 0.016 ± 0.008 | 0.030 ± 0.008 | inches | | | | |
| | 3.20 ± 0.20 | 6.50 ± 0.20 | 0.65 ± 0.20 | 0.40 ± 0.20 | 0.75 ± 0.20 | mm | | | | |


| | | Performar | ice Character | istics | |
|--|---|-------------------------------|--------------------------------|---|--|
| Test Item | Test Method | Test Spe | ecification | Test Condition | |
| i est item | i est metrioù | 1% | 5% | Test Condition | |
| Temperature Coefficient of Resistance | JIS-C-5201-1 4.8 IEC-60115-1 4.8 | Within the spe | cified tolerance | At 25 / -55°C and 25°C / +155°C, 25°C is the reference temperature | |
| | | ± (1% + 0.05Ω) | ± (2% + 0.1Ω) | 6.25 times rated power or max. overload voltage whicheve is less for 5 seconds, except for high power (-HP). | |
| Short Time Overload | JIS-C-5201-1 4.13 | ± (1% + 0.0322) | ± (2 % + 0.112) | For high power (-HP): 5 times rated power or max. overload voltage whichever is less for 5 seconds | |
| | IEC-60115-1 4.13 | Jumper: max 0 | 0.02 Ω after test | Jumper: overload current for 5 seconds 0612=10A, 1020=15A, 1218=15A, 1225=20A | |
| Leaching | JIS-C-5201-1 4.18 IEC-60068-2-58 8.2.1 | | hing area ≤ 5% g area ≤ 10% | 260 ± 5°C for 30 seconds | |
| Resistance to Soldering Heat | JIS-C-5201-1 4.18 IEC-60115-1 4.18 | ± (0.5% + 0.05Ω) | ± (1% + 0.05Ω) | 260 ± 5°C for 10 seconds | |
| Rapid Change of Temperature | JIS-C-5201-1 4.19 IEC-60115-1 4.19 | ± (0.5% + 0.05Ω) | ± (1% + 0.1Ω) | -55°C to +155°C, 5 cycles | |
| Resistance to Solvent | JIS-C-5201-1 4.29 | ± (0.5% + 0.05Ω) | ± (0.5% + 0.05Ω) | The tested resistor should be immersed into isopropyl alcohol of 20 ~ 25°C for 60 seconds. Then the resistor is left in room temperature for 48 hours | |
| | | Jumper: max 0.02 Ω after test | | | |
| Damp Heat with Load | JIS-C-5201-1 4.24 IEC-60115-1 4.24 | ± (1% + 0.05Ω) | ± (2% + 0.05Ω) | 40 ± 2°C, 90 ~ 95% R.H. RCWV or Max. Working voltage whichever is less for 1000 hours with 1.5 hours "ON" and 0.5 hour "OFF" | |
| | | Jumper: max 0 |).02 Ω after test | | |
| Load Life (Endurance) | JIS-C-5201-1 4.25 IEC-60115-1 4.25.1 | ± (1% + 0.05Ω) | ± (3% + 0.1Ω) | 70 ± 2°C, RCWV or Max. Working voltage whichever is less for 1000 hours with 1.5 hours "ON" and 0.5 hour "OFF" | |
| | | Jumper: max 0 | .02 Ω after test | | |
| Insulation Resistance | JIS-C-5201-1 4.6 IEC-60115-1 4.6 | ≥ 10 |) GΩ | Apply 100 VDC for 1 minute | |
| Bending Strength | JIS-C-5201-1 4.33 IEC-60115-1 4.33 | ± (1% + 0.05Ω) | | Bending once for 5 seconds. D: 0508, 0612, 1020, 1218, 1225 = 2 mm | |


This specification may be changed at any time without prior notice. Please confirm technical specifications before you order and/or use.

Power Derating Curve:

Wide Termination Thick Film Chip Resistor

Stackpole Electronics, Inc. Resistive Product Solutions







Stackpole Electronics, Inc.

Wide Termination Thick Film Chip Resistor

Resistive Product Solutions







Wide Termination Thick Film Chip Resistor

Stackpole Electronics, Inc.

Resistive Product Solutions







Stackpole Electronics, Inc.

Wide Termination Thick Film Chip Resistor

Resistive Product Solutions





1. Resistance value used for each size was at or near critical value.

- 2. Used poor heat conduction PCB.
- 3. Applied full power for 10 minutes prior to measurement.


4. Data for reference only. Actual performance under customer conditions may vary.

Wide Termination Thick Film Chip Resistor

Resistive Product Solutions

| | Recommen | ded Pad Layouts | | | | | | | |
|---------------|----------|-----------------|-------|--------|--|--|--|--|--|
| | | | | | | | | | |
| Type/Code | А | В | С | Unit | | | | | |
| RMCW0508 | 0.016 | 0.071 | 0.079 | inches | | | | | |
| KIVIC VV0508 | 0.40 | 1.80 | 2.00 | mm | | | | | |
| RMCW0612 | 0.024 | 0.114 | 0.126 | inches | | | | | |
| RIVICVV0012 | 0.60 | 2.90 | 3.20 | mm | | | | | |
| RMCW1020 | 0.030 | 0.134 | 0.197 | inches | | | | | |
| RIVIC VV 1020 | 0.75 | 3.40 | 5.00 | mm | | | | | |
| RMCW1218 | 0.080 | 0.167 | 0.189 | inches | | | | | |
| RIVIGVV 1218 | 2.04 | 4.24 | 4.80 | mm | | | | | |
| RMCW1225 | 0.033 | 0.146 | 0.252 | inches | | | | | |
| RIVIGVV 1225 | 0.85 | 3.70 | 6.40 | mm | | | | | |

Recommended Customer Soldering Parameters



Rework temperature (hot air equipment): 350°C, 3 ~ 5 seconds Recommended reflow methods:

- IR, vapor phase oven, hot air oven
- If reflow temperatures exceed the recommended profile, devices may not meet the performance requirements.

Wide Termination Thick Film Chip Resistor

Resistive Product Solutions


| Reel Specifications | | | | | | | | | |
|---------------------|-----------|-----------------|----------------------------------|-------------------------------|-----------------------------------|---------------------------------------|-----------------------------------|--------------------------------|--------------|
| | | | | ¢B | | WØ | | | |
| Type / Code | R Size | eel Quantity | А | В | С | D | W | М | Unit |
| RMCW0508/0612 | | 5000 | 0.079 ± 0.020 2.00 ± 0.50 | 0.531 ± 0.039 13.50 ± 1.00 | 0.827 ± 0.039 21.00 ± 1.00 | 2.362 ± 0.039 60.00 ± 1.00 | 0.453 ± 0.079 11.50 ± 2.00 | 7.008 ± 0.079 178.00 ± 2.00 | inches mm |
| RMCW1020/1218/1225 | 7" | 4000 | 0.079 ± 0.020 2.00 ± 0.50 | 0.531 ± 0.039 13.50 ± 1.00 | 0.827 ± 0.039 21.00 ± 1.00 | 2.362 ± 0.039 60.00 ± 1.00 | 0.630 ± 0.079 16.00 ± 2.00 | 7.008 ± 0.079 178.00 ± 2.00 | inches mm |

Packaging Specifications - Paper Tape Paper Carrier цĽ \oplus \oplus 0 ш Т G W Е F в Unit Type/Code A 0.059 ± 0.006 0.089 ± 0.006 0.315 ± 0.008 0.069 ± 0.004 0.138 ± 0.002 inches 1.50 ± 0.15 2.25 ± 0.15 8.00 ± 0.20 1.75 ± 0.10 3.50 ± 0.05 mm **RMCW0508** G н D Unit 0.030 ± 0.004 0.059 +0.004 / -0 0.157 ± 0.004 0.079 ± 0.002 0.157 ± 0.004 inches 2.00 ± 0.05 4.00 ± 0.10 0.75 ± 0.10 1.50 +0.10 / -0 4.00 ± 0.10 mm Type/Code А В W Е F Unit 0.138 ± 0.002 0.075 ± 0.008 0.138 ± 0.008 0.315 ± 0.008 0.069 ± 0.004 inches 1.9<u>0 ± 0.20</u> 3.50 ± 0.20 8.00 ± 0.20 1.75 ± 0.10 3.50 ± 0.05 mm RMCW0612 G Н D Ρ Unit 0.157 ± 0.004 0.059 +0.004 / -0 0.079 ± 0.002 0.030 ± 0.004 0.157 ± 0.004 inches 2<u>.00 ± 0.05</u> 0.75 ± 0.10 1.50 +0.10 / -0 4.00 ± 0.10 4.00 ± 0.10 mm

Wide Termination Thick Film Chip Resistor

Stackpole Electronics, Inc. Resistive Product Solutions

| | Packaging Specifications – Embossed Tape | | | | | | | | | |
|---|--|-------------------|-------------------|-------------------|-------------------|-------------------|--------|--|--|--|
| $\begin{array}{c} A \\ \hline \\$ | | | | | | | | | | |
| Type/Code | А | В | W | Е | F | G | Unit | | | |
| RMCW1020 | 0.110 ± 0.008 | 0.220 ± 0.008 | 0.472 ± 0.004 | 0.069 ± 0.004 | 0.217 ± 0.002 | 0.157 ± 0.004 | inches | | | |
| | 2.80 ± 0.20 | 5.60 ± 0.20 | 12.00 \pm 0.10 | 1.75 ± 0.10 | 5.50 ± 0.05 | 4.00 ± 0.10 | mm | | | |
| RMCW1225 | 0.134 ± 0.008 | 0.264 ± 0.008 | 0.472 ± 0.004 | 0.069 ± 0.004 | 0.217 ± 0.002 | 0.157 ± 0.004 | inches | | | |
| | 3.40 ± 0.20 | 6.70 ± 0.20 | 12.00 ± 0.10 | 1.75 ± 0.10 | 5.50 ± 0.05 | 4.00 ± 0.10 | mm | | | |
| RMCW1225HP | 0.134 ± 0.008 | 0.264 ± 0.008 | 0.472 ± 0.004 | 0.069 ± 0.004 | 0.217 ± 0.002 | 0.157 ± 0.004 | inches | | | |
| | 3.40 ± 0.20 | 6.70 ± 0.20 | 12.00 ± 0.10 | 1.75 ± 0.10 | 5.50 ± 0.05 | 4.00 ± 0.10 | mm | | | |
| RMCW1218 | 0.130 ± 0.008 | 0.181 ± 0.008 | 0.472 ± 0.004 | 0.069 ± 0.004 | 0.217 ± 0.002 | 0.157 ± 0.004 | inches | | | |
| | 3.30 ± 0.20 | 4.60 ± 0.20 | 12.00 ± 0.10 | 1.75 ± 0.10 | 5.50 ± 0.05 | 4.00 ± 0.10 | mm | | | |
| Type/Code | Н | Т | D | D1 | T1 | Р | Unit | | | |
| RMCW1020 | 0.079 ± 0.002 | 0.009 ± 0.004 | 0.059 +0.004 / -0 | 0.059 ± 0.004 | 0.033 ± 0.006 | 0.157 ± 0.004 | inches | | | |
| | 2.00 \pm 0.05 | 0.23 ± 0.10 | 1.50 +0.10 / -0 | 1.50 ± 0.10 | 0.85 ± 0.15 | 4.00 ± 0.10 | mm | | | |
| RMCW1225 | 0.079 ± 0.002 | 0.009 ± 0.004 | 0.059 +0.004 / -0 | 0.059 ± 0.004 | 0.033 ± 0.006 | 0.157 ± 0.004 | inches | | | |
| | 2.00 \pm 0.05 | 0.23 ± 0.10 | 1.50 +0.10 / -0 | 1.50 ± 0.10 | 0.85 ± 0.15 | 4.00 ± 0.10 | mm | | | |
| RMCW1225HP | 0.079 ± 0.002 | 0.009 ± 0.004 | 0.059 +0.004 / -0 | 0.059 ± 0.004 | 0.039 ± 0.006 | 0.157 ± 0.004 | inches | | | |
| | 2.00 ± 0.05 | 0.23 ± 0.10 | 1.50 +0.10 / -0 | 1.50 ± 0.10 | 1.00 ± 0.15 | 4.00 ± 0.10 | mm | | | |
| RMCW1218 | 0.079 ± 0.002 | 0.009 ± 0.004 | 0.059 +0.004 / -0 | 0.059 ± 0.004 | 0.033 ± 0.006 | 0.157 ± 0.004 | inches | | | |
| | 2.00 ± 0.05 | 0.23 ± 0.10 | 1.50 +0.10 / -0 | 1.50 ± 0.10 | 0.85 ± 0.15 | 4.00 ± 0.10 | mm | | | |



RoHS Compliance

Stackpole Electronics has joined the worldwide effort to reduce the amount of lead in electronic components and to meet the various regulatory requirements now prevalent, such as the European Union's directive regarding "Restrictions on Hazardous Substances" (RoHS 3). As part of this ongoing program, we periodically update this document with the status regarding the availability of our compliant components. All our standard part numbers are compliant to EU Directive 2011/65/EU of the European Parliament as amended by Directive (EU) 2015/863/EU as regards the list of restricted substances.

| | RoHS Compliance Status | | | | | | | | | |
|-------------------------------|---|----------------------------------|---|--------------------------------------|--|--|--|--|--|--|
| Standard Product Series | Description | Package / Termination Type | Standard Series RoHS Compliant | Lead-Free Termination Composition | Lead-Free Mfg. Effective Date (Std Product Series) | Lead-Free Effective Date Code (YY/WW) | | | | |
| RMCW | Wide Termination Thick Film Chip Resistors | SMD | YES ⁽¹⁾ | 100% Matte Sn over Ni | Always | Always | | | | |

Note (1): RoHS compliant by means of exemption 7c-I

"Conflict Metals" Commitment


We at Stackpole Electronics, Inc. are joined with our industry in opposing the use of metals mined in the "conflict region" of the eastern Democratic Republic of the Congo (DRC) in our products. Recognizing that the supply chain for metals used in the electronics industry is very complex, we work closely with our own suppliers to verify to the extent possible that the materials and products we supply do not contain metals sourced from this conflict region. As such, we are in compliance with the requirements of Dodd-Frank Act regarding Conflict Minerals.

Compliance to "REACH"

We certify that all passive components supplied by Stackpole Electronics, Inc. are SVHC (Substances of Very High Concern) free and compliant with the requirements of EU Directive 1907/2006/EC, "The Registration, Evaluation, Authorization and Restriction of Chemicals", otherwise referred to as REACH. Contact us for complete list of REACH Substance Candidate List.

Environmental Policy

It is the policy of Stackpole Electronics, Inc. (SEI) to protect the environment in all localities in which we operate. We continually strive to improve our effect on the environment. We observe all applicable laws and regulations regarding the protection of our environment and all requests related to the environment to which we have agreed. We are committed to the prevention of all forms of pollution.



(*) E96 resistance values may be available in 1% tolerance but will be subject to high MOQ's. Contact Stackpole.