SIEMENS

Data sheet

3RA2110-0CE15-1BB4



Load feeder fuseless, Direct-on-line starting 400 V AC, Size S00 0.18...0.25 A 24 V DC Spring-type terminal for installation on standard mounting rail (also fulfills type of coordination 1) Type of coordination 2, Iq = 150 kA 1 NO (contactor)

product brand name	SIRIUS		
product designation	Direct (on-line) starter		
design of the product	for standard rail or screw mounting		
product type designation	3RA21		
manufacturer's article number			
 of the supplied contactor 	3RT2015-2BB41		
 of the supplied circuit-breakers 	3RV2011-0CA20		
 of the supplied link module 	3RA2911-2AA00		
General technical data			
size of the circuit-breaker	S00		
size of load feeder	S00		
insulation voltage with degree of pollution 3 at AC rated value	690 V		
surge voltage resistance rated value	6 kV		
degree of protection NEMA rating	other		
shock resistance according to IEC 60068-2-27	6g / 11 ms		
mechanical service life (switching cycles) of contactor typical	30 000 000		
type of assignment	2		
type of protection according to ATEX directive 2014/34/EU	Ex II (2) GD		
certificate of suitability according to ATEX directive 2014/34/EU	DMT 02 ATEX F 001		
Substance Prohibitance (Date)	10/01/2009		
Ambient conditions			
ambient temperature			
 during operation 	-20 +60 °C		
 during storage 	-50 +80 °C		
during transport	-50 +80 °C		
temperature compensation	-20 +60 °C		
relative humidity during operation	10 95 %		
Main circuit			
number of poles for main current circuit	3		
design of the switching contact	electromechanical		
adjustable current response value current of the current-dependent overload release	0.18 0.25 A		
operating voltage			
• rated value	690 V		
• at AC-3 rated value maximum	690 V		
operating frequency rated value	50 60 Hz		

	_			
operational current at AC-3 at 400 V rated value	0.2 A			
operating power at AC-3				
 at 400 V rated value 	60 W			
Control circuit/ Control				
type of voltage of the control supply voltage	DC			
control supply voltage at DC				
rated value	24 V			
rated value	24 24 V			
holding power of magnet coil at DC	4 W			
Auxiliary circuit				
product extension auxiliary switch	Yes			
Protective and monitoring functions	103	_	_	
	CLASS 10			
trip class	_			
design of the overload release	thermal (bimetallic)			
UL/CSA ratings				
full-load current (FLA) for 3-phase AC motor				
at 480 V rated value	0.25 A			
Short-circuit protection				
product function short circuit protection	Yes			
design of the short-circuit trip	magnetic			
conditional short-circuit current (Iq)				
 at 400 V according to IEC 60947-4-1 rated value 	150 000 A			
Installation/ mounting/ dimensions				
mounting position	vertical			
fastening method	screw and snap-on mounting	g onto 35 mm standard	mounting rail	
height	198 mm	9		
width	45 mm			
depth	97 mm			
required spacing				
for grounded parts				
— forwards	20 mm			
— backwards	0 mm			
— upwards	50 mm			
— at the side	20 mm			
— downwards	10 mm			
	10 111111			
• for live parts	20			
— forwards	20 mm			
— backwards	0 mm			
— upwards	50 mm			
— downwards	10 mm			
— at the side	20 mm			
Connections/ Terminals				
type of electrical connection				
for main current circuit	spring-loaded terminals			
for auxiliary and control circuit	spring-loaded terminals			
Safety related data				
B10 value with high demand rate according to SN 31920	1 000 000			
proportion of dangerous failures				
with high demand rate according to SN 31920	73 %			
touch protection on the front according to IEC 60529	finger-safe, for vertical conta	finger-safe, for vertical contact from the front		
Communication/ Protocol				
protocol is supported				
PROFINET IO protocol	No			
PROFISafe protocol	No			
protocol is supported AS-Interface protocol	No			
	INO			
Certificates/ approvals				
General Product Approval		For use in hazard- ous locations	Declaration of Conformity	



Confirmation









Declaration of Conformity

Test Certificates

Marine / Shipping



Type Test Certificates/Test Report

Special Test Certific-<u>ate</u>





other



Marine / Shipping







Confirmation

Vibration and Shock

Railway

Dangerous Good

Transport Information

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RA2110-0CE15-1BB4

Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RA2110-0CE15-1BB4

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3RA2110-0CE15-1BB4

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RA2110-0CE15-1BB4&lang=en

Characteristic: Tripping characteristics, I2t, Let-through current

https://support.industry.siemens.com/cs/ww/en/ps/3RA2110-0CE15-1BB4/char

Further characteristics (e.g. electrical endurance, switching frequency)

http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RA2110-0CE15-1BB4&objecttype=14&gridview=view1

last modified:

2/16/2022

