# **SIEMENS**

### **Data sheet**

## 3RA2115-0BA15-1BB4



Fuseless motor starter Direct start 600VAC Size S00 0.14-0.2a 24V DC screw connection For screw mounting Or 35 mm rail-mounting Type of coordination 2 IQ = 150 KA Also full fills type Of coordination 1 1NO+1NC (MSP) 1NO (contactor)

product brand name	SIRIUS
product designation	non-fused motor starter 3RA2
design of the product	direct starter
manufacturer's article number	
<ul> <li>of the supplied contactor</li> </ul>	<u>3RT2015-1BB41</u>
<ul> <li>of the supplied circuit-breakers</li> </ul>	3RV2011-0BA15
<ul> <li>of the supplied link module</li> </ul>	3RA1921-1DA00
General technical data	
size of the circuit-breaker	S00
size of load feeder	S00
product extension auxiliary switch	Yes
insulation voltage with degree of pollution 3 at AC rated value	690 V
degree of pollution	3
surge voltage resistance rated value	6 kV
shock resistance according to IEC 60068-2-27	6g / 11 ms
mechanical service life (switching cycles) of contactor typical	30 000 000
type of assignment	2
Ambient conditions	
ambient temperature	
during operation	-20 +60 °C
during storage	-50 +80 °C
during transport	-55 +80 °C
Main circuit	
number of poles for main current circuit	3
design of the switching contact	electromechanical
adjustable current response value current of the current-dependent overload release	0.14 0.2 A
operating voltage	
rated value	690 V
at AC-3 rated value maximum	690 V
operating frequency rated value	50 60 Hz
operational current at AC-3 at 400 V rated value	0.2 A
operating power at AC-3	
at 400 V rated value	60 W
● at 500 V rated value	60 W
at 690 V rated value	90 W
Control circuit/ Control	

• rated value	24 V			
holding power of magnet coil at DC	4 W			
Auxiliary circuit	4 00			
	1			
number of NC contacts for auxiliary contacts	2			
number of NO contacts for auxiliary contacts	2	_		
Protective and monitoring functions	01.400.40			
trip class	CLASS 10			
design of the overload release	thermal (bimetallic)			
response value current of instantaneous short-circuit trip unit	2.6 A			
Short-circuit protection				
product function short circuit protection	Yes			
design of the short-circuit trip	magnetic			
conditional short-circuit current (Iq)				
<ul> <li>at 690 V according to IEC 60947-4-1 rated value</li> </ul>	100 000 A			
<ul> <li>at 400 V according to IEC 60947-4-1 rated value</li> </ul>	153 000 A			
at 500 V according to IEC 60947-4-1 rated value	100 000 A			
Installation/ mounting/ dimensions				
mounting position	vertical			
fastening method	Snap-mounted to DIN rail or	screw-mounted with a	dditional nush-in lug	
	167.2 mm	Screw-mounted with at	dullorial pusit-ill lug	
height width	45 mm			
depth	97.1 mm			
required spacing				
• for grounded parts	0.7777			
— forwards	0 mm			
— backwards	0 mm			
— upwards	20 mm			
— at the side	9 mm			
— downwards	10 mm			
• for live parts				
— forwards	0 mm			
— backwards	0 mm			
— upwards	20 mm			
— downwards	10 mm			
— at the side	9 mm			
Connections/ Terminals				
type of electrical connection for main current circuit	screw-type terminals			
type of connectable conductor cross-sections				
<ul> <li>for main contacts stranded</li> </ul>	0.5 4 mm², 2x (0.75 2.5 mm²)			
at AWG cables for main contacts	2x (20 16), only for contactor 2x (18 14), 2x 12			
connectable conductor cross-section for main contacts finely stranded with core end processing	0.5 2.5 mm²			
Safety related data				
B10 value with high demand rate according to SN 31920	1 000 000			
proportion of dangerous failures with high demand rate according to SN 31920	73 %			
protection class IP on the front according to IEC 60529	IP20			
touch protection on the front according to IEC 60529	finger-safe, for vertical conta	act from the front		
Certificates/ approvals				
General Product Approval		For use in hazard- ous locations	Declaration of Conformity	
		7	2 cm cmmy	



Confirmation









**Declaration of** Conformity

**Test Certificates** 

Marine / Shipping



Special Test Certific-<u>ate</u>

Type Test Certificates/Test Report







Marine / Shipping

other Railway









Confirmation

Vibration and Shock

#### **Dangerous Good**

**Transport Informa-**<u>tion</u>

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RA2115-0BA15-1BB4

Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RA2115-0BA15-1BB4

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3RA2115-0BA15-1BB4

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) <a href="http://www.automation.siemens.com/bilddb/cax">http://www.automation.siemens.com/bilddb/cax</a> de.aspx?mlfb=3RA2115-0BA15-1BB4&lang=en

Characteristic: Tripping characteristics, I2t, Let-through current

https://support.industry.siemens.com/cs/ww/en/ps/3RA2115-0BA15-1BB4/char

Further characteristics (e.g. electrical endurance, switching frequency)

http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RA2115-0BA15-1BB4&objecttype=14&gridview=view1

last modified: 12/15/2020