SIEMENS

Data sheet

3RA2115-1GA15-1BB4



Fuseless motor starter Direct start 600VAC Size S00 4.5-6.3A 24V DC screw connection For screw mounting Or 35 mm rail-mounting Type of coordination 1 1NO+1NC (MSP) 1NO (contactor)

product brand name	SIRIUS			
product designation	non-fused motor starter 3RA2			
design of the product	direct starter			
manufacturer's article number				
 of the supplied contactor 	<u>3RT2015-1BB41</u>			
 of the supplied circuit-breakers 	<u>3RV2011-1GA15</u>			
 of the supplied link module 	<u>3RA1921-1DA00</u>			
General technical data				
size of the circuit-breaker	S00			
size of load feeder	S00			
product extension auxiliary switch	Yes			
insulation voltage with degree of pollution 3 at AC rated value	690 V			
degree of pollution	3			
surge voltage resistance rated value	6 kV			
shock resistance according to IEC 60068-2-27	6g / 11 ms			
mechanical service life (switching cycles) of contactor typical	30 000 000			
type of assignment	1			
Ambient conditions				
ambient temperature				
 during operation 	-20 +60 °C			
 during storage 	-50 +80 °C			
during transport	-55 +80 °C			
Main circuit				
number of poles for main current circuit	3			
design of the switching contact	electromechanical			
adjustable current response value current of the current-dependent overload release	4.5 6.3 A			
operating voltage				
 rated value 	690 V			
 at AC-3 rated value maximum 	690 V			
operating frequency rated value	50 60 Hz			
operational current at AC-3 at 400 V rated value	4.9 A			
operating power at AC-3				
• at 400 V rated value	2 200 W			
• at 500 V rated value	3 000 W			
Control circuit/ Control				
control supply voltage at DC				
 rated value 	24 V			

holding power of magnet coil at DC	4 W
Auxiliary circuit	
number of NC contacts for auxiliary contacts	1
number of NO contacts for auxiliary contacts	2
Protective and monitoring functions	
trip class	CLASS 10
design of the overload release	thermal (bimetallic)
response value current of instantaneous short-circuit trip	81.9 A
unit	
UL/CSA ratings	
full-load current (FLA) for 3-phase AC motor	
 at 480 V rated value 	4.8 A
• at 600 V rated value	6.1 A
yielded mechanical performance [hp]	
 for single-phase AC motor 	
— at 110/120 V rated value	0.25 hp
— at 230 V rated value	0.5 hp
 for 3-phase AC motor 	
— at 200/208 V rated value	1 hp
— at 220/230 V rated value	1.5 hp
— at 460/480 V rated value	3 hp
— at 575/600 V rated value	5 hp
Short-circuit protection	
product function short circuit protection	Yes
design of the short-circuit trip	magnetic
conditional short-circuit current (Iq)	
• at 400 V according to IEC 60947-4-1 rated value	153 000 A
Installation/ mounting/ dimensions	
mounting position	vertical
fastening method	Snap-mounted to DIN rail or screw-mounted with additional push-in lug
height	167.2 mm
width	45 mm
depth	97.1 mm
required spacing	
for grounded parts	0
— forwards	0 mm
— backwards	0 mm
— upwards — at the side	20 mm
— at the side — downwards	9 mm 10 mm
for live parts	
• for live parts — forwards	0 mm
— backwards	0 mm
— upwards	20 mm
— upwards — downwards	10 mm
— at the side	9 mm
Connections/ Terminals	
type of electrical connection for main current circuit	screw-type terminals
type of connectable conductor cross-sections	solow-type terminalo
for main contacts stranded	0.5 4 mm², 2x (0.75 2.5 mm²)
at AWG cables for main contacts	2x (20 16), only for contactor 2x (18 14), 2x 12
connectable conductor cross-section for main contacts finely stranded with core end processing	0.5 2.5 mm ²
Safety related data	
B10 value with high demand rate according to SN 31920	1 000 000
proportion of dangerous failures with high demand rate according to SN 31920	73 %
protection class IP on the front according to IEC 60529	IP20
touch protection on the front according to IEC 60529	finger-safe, for vertical contact from the front

Certificates/ approva	lls					
General Product A	pproval			For use in hazard- ous locations	Declaration of Conformity	
() M	<u>Confirmation</u>	(UL) UL	EHC	K ATEX	UK CA	
Declaration of Conformity	Test Certificates		Marine / Shipping			
CE EG-Konf.	<u>Special Test Certific-</u> <u>ate</u>	<u>Type Test Certific-</u> ates/Test Report	ABS	BUREAU VERITAS	Lloydis Register uks	
Marine / Shipping				other	Railway	
PRS	RINA	KMRS	DNV-GL DNV-GL	<u>Confirmation</u>	Vibration and Shock	
Dangerous Good						
Further information Information- and Downloadcenter (Catalogs, Brochures,) https://www.siemens.com/ic10						
Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RA2115-1GA15-1BB4 Cax online generator http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RA2115-1GA15-1BB4 Service&Support (Manuals, Certificates, Characteristics, FAQs,)						
https://support.indus Image database (pr http://www.automatic Characteristic: Trip	Manuals, Certificates, C try.siemens.com/cs/ww/e roduct images, 2D dime on.siemens.com/bilddb/ca pping characteristics, I ² t try.siemens.com/cs/ww/e	n/ps/3RA2115-1GA15 nsion drawings, 3D n ax_de.aspx?mlfb=3RA , Let-through current	<u>-1BB4</u> nodels, device circuit 2115-1GA15-1BB4&lan		cros,)	
Further characteristics (e.g. electrical endurance, switching frequency) http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RA2115-1GA15-1BB4&objecttype=14&gridview=view1						

last modified:

12/15/2020 🖸