## **SIEMENS**

## **Data sheet**

## 3RA2210-0AD15-2BB4



Fuseless motor starter Reversing operation 600VAC Size S00 0.11-0.16a 24V DC screw connection For snapping onto 60 mm busbar systems Type of coordination 2 IQ = 150 KA Also full fills type Of coordination 1 1NC (per contactor)

product brand name	SIRIUS	
product designation	non-fused motor starter 3RA2	
design of the product	reversing starter	
manufacturer's article number		
<ul> <li>of the supplied contactor</li> </ul>	3RT2015-1BB42	
<ul> <li>of the supplied circuit-breakers</li> </ul>	3RV2011-0AA10	
<ul> <li>of the supplied RS assembly kit</li> </ul>	3RA2913-1DB1	
<ul> <li>of the supplied busbar adapter</li> </ul>	8US1251-5DS10	
<ul> <li>of the supplied link module</li> </ul>	3RA1921-1DA00	
General technical data		
size of the circuit-breaker	S00	
size of load feeder	S00	
product extension auxiliary switch	Yes	
insulation voltage with degree of pollution 3 at AC rated value	690 V	
degree of pollution	3	
surge voltage resistance rated value	6 kV	
shock resistance according to IEC 60068-2-27	6g / 11 ms	
mechanical service life (switching cycles) of contactor typical	30 000 000	
type of assignment	2	
Substance Prohibitance (Date)	03/01/2017	
Ambient conditions		
ambient temperature		
<ul><li>during operation</li></ul>	-20 +60 °C	
<ul><li>during storage</li></ul>	-50 +80 °C	
<ul> <li>during transport</li> </ul>	-55 +80 °C	
Main circuit		
number of poles for main current circuit	3	
design of the switching contact	electromechanical	
adjustable current response value current of the current-dependent overload release	0.11 0.16 A	
operating voltage		
• rated value	690 V	
at AC-3 rated value maximum	690 V	
operating frequency rated value	50 60 Hz	
operational current at AC-3 at 400 V rated value	0.16 A	
operating power at AC-3		
• at 400 V rated value	40 W	
<ul> <li>at 500 V rated value</li> </ul>	40 W	

at 690 V rated value	60 W	
Control circuit/ Control	30 11	
control supply voltage at DC		
• rated value	24 V	
holding power of magnet coil at DC	4 W	
Auxiliary circuit	+ vv	
	1	
number of NC contacts for auxiliary contacts	0	
number of NO contacts for auxiliary contacts	U	
Protective and monitoring functions	01.4.00.40	
trip class	CLASS 10	
design of the overload release	thermal (bimetallic)	
response value current of instantaneous short-circuit trip unit	2.08 A	
Short-circuit protection		
product function short circuit protection	Yes	
design of the short-circuit trip	magnetic	
conditional short-circuit current (Iq)	magnetic	
• at 690 V according to IEC 60947-4-1 rated value	100 000 A	
• at 400 V according to IEC 60947-4-1 rated value	153 000 A	
• at 500 V according to IEC 60947-4-1 rated value	100 000 A	
Installation/ mounting/ dimensions	100 000 71	
	vertical	
mounting position	vertical	ahar ayatama
fastening method	for snapping onto 60 mm bu	spar systems
height		
width	90 mm	
depth	155.1 mm	
required spacing		
• for grounded parts	0	
— forwards	0 mm	
— backwards	0 mm	
— upwards	20 mm	
— at the side	9 mm	
— downwards	10 mm	
• for live parts	0	
— forwards	0 mm	
— backwards	0 mm 20 mm	
— upwards		
— downwards	10 mm	
— at the side	9 mm	
Connections/ Terminals		
type of electrical connection for main current circuit	screw-type terminals	
type of connectable conductor cross-sections	0.5 4 0.0 12 ==	2)
for main contacts stranded	0.5 4 mm², 2x (0.75 2.5 mm²)	
at AWG cables for main contacts	2x (20 16), only for contactor 2x (18 14), 2x 12	
connectable conductor cross-section for main contacts finely stranded with core end processing	0.5 2.5 mm²	
Safety related data		
B10 value with high demand rate according to SN 31920	1 000 000	
proportion of dangerous failures with high demand rate according to SN 31920	73 %	
protection class IP on the front according to IEC 60529	IP20	
touch protection on the front according to IEC 60529	finger-safe, for vertical conta	act from the front
Certificates/ approvals		
		For use in hazard- Declaration of
General Product Approval		ous locations Conformity



Confirmation









Declaration of Conformity

**Test Certificates** 

Marine / Shipping



Special Test Certificate

Type Test Certificates/Test Report







Marine / Shipping









Confirmation

other

Vibration and Shock

Railway

**Dangerous Good** 

<u>Transport Information</u>

## **Further information**

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RA2210-0AD15-2BB4

Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RA2210-0AD15-2BB4

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3RA2210-0AD15-2BB4

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)


http://www.automation.siemens.com/bilddb/cax\_de.aspx?mlfb=3RA2210-0AD15-2BB4&lang=en


Characteristic: Tripping characteristics, I2t, Let-through current


https://support.industry.siemens.com/cs/ww/en/ps/3RA2210-0AD15-2BB4/char

Further characteristics (e.g. electrical endurance, switching frequency)

http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RA2210-0AD15-2BB4&objecttype=14&gridview=view1







last modified: 12/15/2020 🖸