3RA2210-1AD15-2AK6

Data sheet



FUSELESS LOAD FEEDER REVERSING OPERATION, AC 400V, S00 1.1...1.6A, AC 110/120V 50/60HZ SCREW TERMINAL FOR BUSBAR SYSTEMS 60MM TYPE OF ASSIGNMENT 2, IQ = 150KA (ALSO FULFILLS TYPE OF ASSIGNMENT 1) 1NC (CONTACTOR)

product brand name	SIRIUS
product designation	non-fused load feeders 3RA2
design of the product	reversing starter
manufacturer's article number	
 of the supplied contactor 	3RT2015-1AK62
 of the supplied circuit-breakers 	3RV2011-1AA10
 of the supplied RS assembly kit 	<u>8US1250-5AS10</u>
 of the supplied busbar adapter 	<u>8US1251-5DS10</u>
 of the supplied link module 	3RA1921-1DA00
General technical data	
size of the circuit-breaker	S00
size of load feeder	S00
product extension auxiliary switch	Yes
insulation voltage with degree of pollution 3 at AC rated value	690 V
degree of pollution	3
surge voltage resistance rated value	6 kV
shock resistance according to IEC 60068-2-27	6g / 11 ms
mechanical service life (switching cycles) of contactor typical	30 000 000
type of assignment	2
Substance Prohibitance (Date)	10/01/2009
Ambient conditions	
ambient temperature	
 during operation 	-20 +60 °C
during storage	-50 +80 °C
during transport	-50 +80 °C
Main circuit	
number of poles for main current circuit	3
design of the switching contact	electromechanical
adjustable current response value current of the current-dependent overload release	1.1 1.6 A
operating voltage	
• rated value	690 V
at AC-3 rated value maximum	690 V
operating frequency rated value	50 60 Hz
operational current at AC-3 at 400 V rated value	1.5 A
operating power at AC-3	
 at 400 V rated value 	550 W
• at 500 V rated value	550 W

• at 690 V rated value	1 100 W
Control circuit/ Control	1 100 11
control supply voltage at AC • at 50 Hz rated value	110 V
at 60 Hz rated value at 60 Hz rated value	120 V
apparent holding power of magnet coil at AC	4.2 VA
Protective and monitoring functions	7.4 V/\
	CLASS 10
trip class	CLASS 10
design of the overload release response value current of instantaneous short-circuit trip	thermal (bimetallic) 20.8 A
unit	20.071
UL/CSA ratings	
full-load current (FLA) for 3-phase AC motor	
at 480 V rated value	1.6 A
at 600 V rated value	1.3 A
yielded mechanical performance [hp]	
 for single-phase AC motor 	
— at 230 V rated value	0.1 hp
• for 3-phase AC motor	
— at 460/480 V rated value	0.75 hp
— at 575/600 V rated value	0.75 hp
Short-circuit protection	
product function short circuit protection	Yes
design of the short-circuit trip	magnetic
conditional short-circuit current (Iq)	
 at 690 V according to IEC 60947-4-1 rated value 	100 000 A
at 400 V according to IEC 60947-4-1 rated value	153 000 A
 at 500 V according to IEC 60947-4-1 rated value 	100 000 A
Installation/ mounting/ dimensions	
mounting position	vertical
fastening method	for snapping onto 60 mm busbar systems
height	200 mm
width	90 mm
depth	155.1 mm
required spacing	
for grounded parts	
— forwards	0 mm
— backwards	0 mm
— upwards	20 mm
— at the side	9 mm
— downwards	10 mm
for live parts	
— forwards	0 mm
— backwards	0 mm
— upwards	20 mm
— downwards	10 mm
— at the side	9 mm
Connections/ Terminals	
type of electrical connection for main current circuit	screw-type terminals
type of connectable conductor cross-sections	
for main contacts stranded	0.5 4 mm², 2x (0.75 2.5 mm²)
at AWG cables for main contacts	2x (20 16), only for contactor 2x (18 14), 2x 12
connectable conductor cross-section for main contacts	0.5 2.5 mm ²
finely stranded with core end processing	
Safety related data	
B10 value with high demand rate according to SN 31920	1 000 000
proportion of dangerous failures with high demand rate according to SN 31920	73 %
protection class IP on the front according to IEC 60529	IP20

Certificates/ approvals

General Product Approval

For use in hazardous locations Declaration of Conformity



Confirmation



EAC





Declaration of Conformity

Test Certificates

Marine / Shipping



Special Test Certificate

Type Test Certificates/Test Report







Marine / Shipping

other

Railway









Confirmation

Vibration and Shock

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RA2210-1AD15-2AK6

Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RA2210-1AD15-2AK6

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3RA2210-1AD15-2AK6

 $Image\ database\ (product\ images,\ 2D\ dimension\ drawings,\ 3D\ models,\ device\ circuit\ diagrams,\ EPLAN\ macros,\ ...)$


http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RA2210-1AD15-2AK6&lang=en

Characteristic: Tripping characteristics, I2t, Let-through current

https://support.industry.siemens.com/cs/ww/en/ps/3RA2210-1AD15-2AK6/char

Further characteristics (e.g. electrical endurance, switching frequency)

http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RA2210-1AD15-2AK6&objecttype=14&gridview=view1



last modified: 12/29/2021 🖸