# SIEMENS

### Data sheet

## 3RW5225-3AC05



SIRIUS soft starter 200-600 V 63 A, 24 V AC/DC spring-type terminals Analog output

product brand name	SIRIUS
-	
product category	Hybrid switching devices
product designation	Soft starter
product type designation	3RW52
manufacturer's article number	
of standard HMI module usable	<u>3RW5980-0HS00</u>
of high feature HMI module usable	<u>3RW5980-0HF00</u>
<ul> <li>of communication module PROFINET standard usable</li> </ul>	<u>3RW5980-0CS00</u>
<ul> <li>of communication module PROFIBUS usable</li> </ul>	<u>3RW5980-0CP00</u>
<ul> <li>of communication module Modbus TCP usable</li> </ul>	<u>3RW5980-0CT00</u>
<ul> <li>of communication module Modbus RTU usable</li> </ul>	<u>3RW5980-0CR00</u>
<ul> <li>of communication module Ethernet/IP</li> </ul>	<u>3RW5980-0CE00</u>
<ul> <li>of circuit breaker usable at 400 V</li> </ul>	3VA2163-7MN32-0AA0: Type of coordination 1. lq = 65 kA. CLASS 10
<ul> <li>of circuit breaker usable at 500 V</li> </ul>	3VA2163-7MN32-0AA0; Type of coordination 1, Iq = 20 kA, CLASS 10
<ul> <li>of circuit breaker usable at 400 V at inside-delta circuit</li> </ul>	3VA2110-7MN32-0AA0: Type of coordination 1. Iq = 65 kA. CLASS 10
<ul> <li>of circuit breaker usable at 500 V at inside-delta circuit</li> </ul>	3VA2110-7MN32-0AA0; Type of coordination 1, Iq = 20 kA, CLASS 10
<ul> <li>of the gG fuse usable up to 690 V</li> </ul>	3NA3830-6; Type of coordination 1, Iq = 65 kA
<ul> <li>of the gG fuse usable at inside-delta circuit up to 500 V</li> </ul>	<u>3NA3830-6; Type of coordination 1, Iq = 65 kA</u>
<ul> <li>of full range R fuse link for semiconductor protection usable up to 690 V</li> </ul>	<u>3NE1022-0; Type of coordination 2, Iq = 65 kA</u>
<ul> <li>of back-up R fuse link for semiconductor protection usable up to 690 V</li> </ul>	<u>3NE8024-1; Type of coordination 2, Iq = 65 kA</u>
eneral technical data	
starting voltage [%]	30 100 %
stopping voltage [%]	50 %; non-adjustable
start-up ramp time of soft starter	0 20 s
current limiting value [%] adjustable	130 700 %
certificate of suitability	
CE marking	Yes
UL approval	Yes
	Yes
<ul> <li>CSA approval</li> </ul>	100
	No
product component	
<pre>product component</pre>	No
<ul><li>product component</li><li>HMI-High Feature</li><li>is supported HMI-Standard</li></ul>	No Yes

trin class	CLASS 104 (default) / 10E / 20E: acc. to IEC 60047.4.2
trip class	CLASS 10A (default) / 10E / 20E; acc. to IEC 60947-4-2
<ul> <li>buffering time in the event of power failure</li> <li>for main current circuit</li> </ul>	100 ms
for control circuit	100 ms
	600 V
insulation voltage rated value	
degree of pollution	3, acc. to IEC 60947-4-2
impulse voltage rated value	6 kV 1 800 V
blocking voltage of the thyristor maximum	
service factor	16 kV
surge voltage resistance rated value	O KV
<ul> <li>maximum permissible voltage for safe isolation</li> <li>between main and auxiliary circuit</li> </ul>	600 V
shock resistance	
vibration resistance	15 g / 11 ms, from 12 g / 11 ms with potential contact lifting
	15 mm to 6 Hz; 2g to 500 Hz AC 53a
utilization category according to IEC 60947-4-2 reference code according to IEC 81346-2	
	Q 02/15/2018
Substance Prohibitance (Date)	02/15/2018
product function	Ven
ramp-up (soft starting)     ramp down (coff start)	Yes
ramp-down (soft stop)	Yes
Soft Torque	Yes
adjustable current limitation	Yes
pump ramp down     intrineig dowing protection	Yes
intrinsic device protection	Yes
motor overload protection	Yes; Electronic motor overload protection
evaluation of thermistor motor protection	No
inside-delta circuit	Yes
auto-RESET	Yes
manual RESET	Yes
remote reset	Yes; By turning off the control supply voltage
communication function	Yes
<ul> <li>operating measured value display</li> </ul>	Yes; Only in conjunction with special accessories
• error logbook	Yes; Only in conjunction with special accessories
• via software parameterizable	No
• via software configurable	Yes
PROFlenergy	Yes; in connection with the PROFINET Standard communication module
• firmware update	Yes
removable terminal for control circuit	Yes
torque control	No
analog output	Yes; 4 20 mA (default) / 0 10 V (parameterizable with High Feature
	HMI)
Power Electronics	
operational current	
<ul> <li>at 40 °C rated value</li> </ul>	63 A
• at 50 °C rated value	56 A
• at 60 °C rated value	51 A
operational current at inside-delta circuit	
• at 40 °C rated value	109 A
• at 50 °C rated value	96 A
• at 60 °C rated value	87.5 A
operating voltage	
rated value	200 600 V
• at inside-delta circuit rated value	200 600 V
relative negative tolerance of the operating voltage	-15 %
relative positive tolerance of the operating voltage	10 %
relative negative tolerance of the operating voltage at inside-delta circuit	-15 %
relative positive tolerance of the operating voltage at inside-delta circuit	10 %
operating power for 3-phase motors	
-F	

• at 230 V at 40 °C rated value	18.5 kW
<ul> <li>at 230 V at inside-delta circuit at 40 °C rated value</li> </ul>	30 kW
<ul> <li>at 250 V at Inside-delta circuit at 40 °C rated value</li> <li>at 400 V at 40 °C rated value</li> </ul>	30 kW
<ul> <li>at 400 V at 40 °C rated value</li> <li>at 400 V at inside-delta circuit at 40 °C rated value</li> </ul>	55 kW
<ul> <li>at 500 V at 40 °C rated value</li> </ul>	37 kW
<ul> <li>at 500 V at 40° C rated value</li> <li>at 500 V at inside-delta circuit at 40 °C rated value</li> </ul>	57 kW
Operating frequency 1 rated value	50 Hz
Operating frequency 2 rated value	60 Hz
relative negative tolerance of the operating frequency	-10 %
relative positive tolerance of the operating frequency	10 %
adjustable motor current	
<ul> <li>at rotary coding switch on switch position 1</li> </ul>	25.5 A
<ul> <li>at rotary coding switch on switch position 2</li> </ul>	28 A
<ul> <li>at rotary coding switch on switch position 3</li> </ul>	30.5 A
<ul> <li>at rotary coding switch on switch position 4</li> </ul>	33 A
<ul> <li>at rotary coding switch on switch position 5</li> </ul>	35.5 A
<ul> <li>at rotary coding switch on switch position 6</li> </ul>	38 A
<ul> <li>at rotary coding switch on switch position 7</li> </ul>	40.5 A
<ul> <li>at rotary coding switch on switch position 8</li> </ul>	43 A
<ul> <li>at rotary coding switch on switch position 9</li> </ul>	45.5 A
<ul> <li>at rotary coding switch on switch position 10</li> </ul>	48 A
<ul> <li>at rotary coding switch on switch position 11</li> </ul>	50.5 A
<ul> <li>at rotary coding switch on switch position 12</li> </ul>	53 A
<ul> <li>at rotary coding switch on switch position 13</li> </ul>	55.5 A
<ul> <li>at rotary coding switch on switch position 14</li> </ul>	58 A
<ul> <li>at rotary coding switch on switch position 15</li> </ul>	60.5 A
<ul> <li>at rotary coding switch on switch position 16</li> </ul>	63 A
• minimum	25.5 A
adjustable motor current	
<ul> <li>for inside-delta circuit at rotary coding switch on switch position 1</li> </ul>	44.2 A
<ul> <li>for inside-delta circuit at rotary coding switch on switch position 2</li> </ul>	48.5 A
<ul> <li>for inside-delta circuit at rotary coding switch on switch position 3</li> </ul>	52.8 A
<ul> <li>for inside-delta circuit at rotary coding switch on switch position 4</li> </ul>	57.2 A
<ul> <li>for inside-delta circuit at rotary coding switch on switch position 5</li> </ul>	61.5 A
<ul> <li>for inside-delta circuit at rotary coding switch on switch position 6</li> </ul>	65.8 A
<ul> <li>for inside-delta circuit at rotary coding switch on switch position 7</li> </ul>	70.1 A
<ul> <li>for inside-delta circuit at rotary coding switch on switch position 8</li> </ul>	74.5 A
<ul> <li>for inside-delta circuit at rotary coding switch on switch position 9</li> </ul>	78.8 A
<ul> <li>for inside-delta circuit at rotary coding switch on switch position 10</li> <li>for inside delta circuit at rotary coding switch on</li> </ul>	83.1 A 87.5 A
<ul> <li>for inside-delta circuit at rotary coding switch on switch position 11</li> <li>for inside-delta circuit at rotary coding switch on</li> </ul>	91.8 A
<ul> <li>for inside-delta circuit at rotary coding switch on switch position 12</li> <li>for inside-delta circuit at rotary coding switch on</li> </ul>	96.1 A
<ul> <li>for inside-delta circuit at rotary coding switch on switch position 13</li> <li>for inside-delta circuit at rotary coding switch on</li> </ul>	90. TA 100 A
<ul> <li>for inside-delta circuit at rotary coding switch on switch position 14</li> <li>for inside-delta circuit at rotary coding switch on</li> </ul>	105 A
<ul> <li>for inside-delta circuit at rotary coding switch on</li> <li>for inside-delta circuit at rotary coding switch on</li> </ul>	109 A
<ul> <li>switch position 16</li> <li>at inside-delta circuit minimum</li> </ul>	44.2 A
minimum load [%]	15 %; Relative to smallest settable le
power loss [W] for rated value of the current at AC	
pomor 1035 [11] for rated value of the current at AC	

<ul> <li>at 40 °C after startup</li> </ul>	31 W
• at 50 °C after startup	29 W
at 60 °C after startup	27 W
power loss [W] at AC at current limitation 350 %	
• at 40 °C during startup	882 W
<ul> <li>at 50 °C during startup</li> </ul>	744 W
• at 60 °C during startup	659 W
Control circuit/ Control	
type of voltage of the control supply voltage	AC/DC
control supply voltage at AC	
<ul> <li>at 50 Hz rated value</li> </ul>	24 V
at 60 Hz rated value	24 V
relative negative tolerance of the control supply voltage at AC at 50 Hz	-20 %
relative positive tolerance of the control supply voltage at AC at 50 Hz	20 %
relative negative tolerance of the control supply voltage at AC at 60 Hz	-20 %
relative positive tolerance of the control supply voltage at AC at 60 Hz	20 %
control supply voltage frequency	50 60 Hz
relative negative tolerance of the control supply voltage frequency	-10 %
relative positive tolerance of the control supply voltage frequency	10 %
control supply voltage	
<ul> <li>at DC rated value</li> </ul>	24 V
relative negative tolerance of the control supply voltage at DC	-20 %
relative positive tolerance of the control supply voltage at DC	20 %
control supply current in standby mode rated value	160 mA
holding current in bypass operation rated value	380 mA
locked-rotor current at close of bypass contact maximum	7.6 A
inrush current peak at application of control supply voltage maximum	3.3 A
duration of inrush current peak at application of control supply voltage	12.1 ms
design of the overvoltage protection	Varistor
design of short-circuit protection for control circuit	4 A gG fuse (Icu=1 kA), 6 A quick-acting fuse (Icu=1 kA), C1 miniature circuit breaker (Icu= 600 A), C6 miniature circuit breaker (Icu= 300 A); Is not part of scope of supply
Inputs/ Outputs	
number of digital inputs	1
number of digital outputs	3
not parameterizable	2
digital output version	2 normally-open contacts (NO) / 1 changeover contact (CO)
number of analog outputs	1
switching capacity current of the relay outputs	
• at AC-15 at 250 V rated value	3 A
• at DC-13 at 24 V rated value	1 A
Installation/ mounting/ dimensions	
mounting position	+/- 10° rotation possible and can be tilted forward or backward on vertical mounting surface
fastening method	screw fixing
height	306 mm
width	185 mm
depth	203 mm
required spacing with side-by-side mounting	10
• forwards	10 mm
backwards	0 mm
<ul> <li>upwards</li> </ul>	100 mm

downwards	75 mm
advinwards     at the side	75 mm 5 mm
weight without packaging	5.6 kg
Connections/ Terminals	
type of electrical connection	
for main current circuit	box terminal
<ul> <li>for control circuit</li> </ul>	spring-loaded terminals
width of connection bar maximum	25 mm
type of connectable conductor cross-sections	
<ul> <li>for main contacts for box terminal using the front clamping point solid</li> </ul>	1x (2.5 16 mm²)
<ul> <li>for main contacts for box terminal using the front clamping point finely stranded with core end processing</li> </ul>	1x (2.5 50 mm²)
<ul> <li>for main contacts for box terminal using the front clamping point stranded</li> </ul>	1x (10 70 mm²)
<ul> <li>at AWG cables for main contacts for box terminal using the front clamping point</li> </ul>	1x (10 2/0)
<ul> <li>for main contacts for box terminal using the back clamping point solid</li> </ul>	1x (2.5 16 mm²)
<ul> <li>at AWG cables for main contacts for box terminal using the back clamping point</li> </ul>	1x (10 2/0)
<ul> <li>for main contacts for box terminal using both clamping points solid</li> </ul>	2x (2.5 16 mm²)
<ul> <li>for main contacts for box terminal using both clamping points finely stranded with core end processing</li> </ul>	2x (2.5 35 mm²)
<ul> <li>for main contacts for box terminal using both clamping points stranded</li> </ul>	2x (6 16 mm²), 2x (10 50 mm²)
<ul> <li>for main contacts for box terminal using the back clamping point finely stranded with core end processing</li> </ul>	1x (2.5 50 mm²)
<ul> <li>for main contacts for box terminal using the back clamping point stranded</li> </ul>	1x (10 70 mm²)
type of connectable conductor cross-sections	
for control circuit solid	2x (0.25 1.5 mm <sup>2</sup> )
for control circuit finely stranded with core end processing	2x (0.25 1.5 mm <sup>2</sup> )
<ul> <li>at AWG cables for control circuit solid</li> <li>at AWG cables for control circuit finally stranded with</li> </ul>	2x (24 16) 2x (24 16)
<ul> <li>at AWG cables for control circuit finely stranded with core end processing</li> </ul>	2x (24 10)
wire length	
between soft starter and motor maximum	800 m
at the digital inputs at AC maximum	100 m
at the digital inputs at DC maximum	1 000 m
<ul> <li>tightening torque</li> <li>for main contacts with screw-type terminals</li> </ul>	4.5 6 N·m
<ul> <li>for auxiliary and control contacts with screw-type terminals</li> </ul>	0.8 1.2 N·m
tightening torque [lbf·in]	
for main contacts with screw-type terminals	40 53 lbf·in
<ul> <li>for auxiliary and control contacts with screw-type terminals</li> </ul>	7 10.3 lbf·in
Ambient conditions	
installation altitude at height above sea level maximum	5 000 m; Derating as of 1000 m, see catalog
ambient temperature	
<ul> <li>during operation</li> </ul>	-25 +60 °C; Please observe derating at temperatures of 40 °C or above
during storage and transport	-40 +80 °C
environmental category	
during operation according to IEC 60721	3K6 (no ice formation, only occasional condensation), 3C3 (no salt mist), 3S2 (sand must not get into the devices), 3M6 1K6 (only occasional condensation), 1C2 (no salt mist), 1S2 (sand must
<ul> <li>during storage according to IEC 60721</li> <li>during transport according to IEC 60721</li> </ul>	1K6 (only occasional condensation), 1C2 (no salt mist), 1S2 (sand must not get inside the devices), 1M4 2K2, 2C1, 2S1, 2M2 (max. fall height 0.3 m)
	202, 201, 201, 201, 2012 (max. fail fiely $0.0  m$ )

EMC emitted interference	acc. to IEC 60947-4-2: Class A
Communication/ Protocol	
communication module is supported	
PROFINET standard	Yes
EtherNet/IP	Yes
Modbus RTU	Yes
Modbus TCP	Yes
PROFIBUS	Yes
UL/CSA ratings	
manufacturer's article number	
<ul> <li>of circuit breaker</li> </ul>	
<ul> <li>— usable for Standard Faults at 460/480 V according to UL</li> </ul>	Siemens type: 3RV2742, max. 70 A or 3VA51, max. 125 A; lq = 10 kA
<ul> <li>— usable for High Faults at 460/480 V according to UL</li> </ul>	Siemens type: 3VA51, max. 125 A; lq max = 65 kA
<ul> <li>— usable for Standard Faults at 460/480 V at inside-delta circuit according to UL</li> </ul>	Siemens type: 3VA51, max. 125 A; Iq = 10 kA
<ul> <li>— usable for High Faults at 460/480 V at inside- delta circuit according to UL</li> </ul>	Siemens type: 3VA51, max. 125 A; lq max = 65 kA
<ul> <li>— usable for Standard Faults at 575/600 V according to UL</li> </ul>	Siemens type: 3RV2742, max. 70 A or 3VA51, max. 125 A; lq = 10 kA
<ul> <li>— usable for Standard Faults at 575/600 V at inside-delta circuit according to UL</li> </ul>	Siemens type: 3VA51, max. 125 A; lq = 10 kA
of the fuse	
<ul> <li>— usable for Standard Faults up to 575/600 V according to UL</li> </ul>	Type: Class RK5 / K5, max. 200 A; lq = 10 kA
<ul> <li>— usable for High Faults up to 575/600 V according to UL</li> </ul>	Type: Class J / L, max. 225 A; lq = 100 kA
<ul> <li>— usable for Standard Faults at inside-delta circuit up to 575/600 V according to UL</li> </ul>	Type: Class RK5 / K5, max. 200 A; lq = 10 kA
<ul> <li>usable for High Faults at inside-delta circuit up to 575/600 V according to UL</li> </ul>	Type: Class J / L, max. 225 A; Iq = 100 kA
operating power [hp] for 3-phase motors	
• at 200/208 V at 50 °C rated value	15 hp
• at 220/230 V at 50 °C rated value	20 hp
• at 460/480 V at 50 °C rated value	40 hp
• at 575/600 V at 50 °C rated value	50 hp
at 200/208 V at inside-delta circuit at 50 °C rated value	30 hp
• at 220/230 V at inside-delta circuit at 50 °C rated value	30 hp
at 460/480 V at inside-delta circuit at 50 °C rated value	75 hp
at 575/600 V at inside-delta circuit at 50 °C rated value	75 hp
contact rating of auxiliary contacts according to UL	R300-B300
Safety related data	
protection class IP on the front according to IEC 60529	IP00; IP20 with cover
touch protection on the front according to IEC 60529	finger-safe, for vertical contact from the front with cover
electromagnetic compatibility	in accordance with IEC 60947-4-2
Certificates/ approvals	
General Product Approval	EMC
Declaration of Conformity Test Certification	ates Marine / Shipping
rest definition	and a suppling





Type Test Certificates/Test Report







#### Marine / Shipping





**Confirmation** 

other

#### Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RW5225-3AC05

Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RW5225-3AC05

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3RW5225-3AC05

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax\_de.aspx?mlfb=3RW5225-3AC05&lang=en


Characteristic: Tripping characteristics, I<sup>2</sup>t, Let-through current


https://support.industry.siemens.com/cs/ww/en/ps/3RW5225-3AC05/char

Characteristic: Installation altitude

http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RW5225-3AC05&objecttype=14&gridview=view1 Simulation Tool for Soft Starters (STS)

https://support.industry.siemens.com/cs/ww/en/view/101494917





last modified: