# Product data sheet Characteristics

# RXG12BD

Device short name

Contacts type and composition

Harmony, Interface plug-in relay, 10 A, 1 CO, with LED, with lockable test button, 24 V DC





Main	
Range of Product	Harmony Electromechanical Relays
Series name	Interface relay
Product or Component Type	Plug-in relay

RXG 1 C/O

Complementary

Status LED	With
Contacts material	Silver alloy (AgSnO2In2O3)
Maximum contact resistance	100 mOhm
[Ithe] conventional enclosed thermal current	10 A -40131 °F (-4055 °C)
[le] rated operational current	10 A 30 V DC) UL 10 A 30 V DC) IEC 10 A 250 V AC) IEC 10 A 250 V AC) UL
Maximum switching voltage	250 V AC 30 V DC
Load current	10 A 250 V AC
Maximum switching capacity	2500 VA
Minimum switching capacity	500 mW at 100 mA, 5 V DC
Operating rate	<= 1800 cycles/hour under load <= 18000 cycles/hour no-load
Utilisation coefficient	20 %
Mechanical durability	10000000 cycles
Electrical durability	100000 Cycles NO resistive at 55 °C 100000 cycles NC resistive at 55 °C
[Ui] rated insulation voltage	250 V IEC 300 V CSA 300 V UL
[Uimp] rated impulse withstand voltage	6 kV 1.2/50 μs
Dielectric strength	1000 V AC between contacts with micro disconnection 5000 V AC between coil and contact with reinforced insulation
Coil resistance	1100 Ohm +/- 10 %
Insulation resistance	1000 MOhm at 500 V DC
Test levels	Level A
Mounting position	Any position
Drop-out voltage threshold	>= 0.1 Uc DC
Coil insulation class	Class F
Operate time	20 ms
Release time	20 ms
[Uc] control circuit voltage	24 V DC
Safety reliability data	B10d = 100000
Colour of cover	Standard

Control Type	Lockable test button	
Local signalling	Flag	
Torque Value	7.08 lbf.in (0.8 N.m)	
Net Weight	0.04 lb(US) (0.02 kg)	
Device presentation	Complete product	

## Environment

Vibration resistance	3 gn +/- 0.75 mm 10150 Hz)in operation
	5 gn +/- 0.75 mm 10150 Hz)not in operation
IP Degree of Protection	IP40
Shock resistance	20 gn in operation
	100 gn not in operation
Protection category	RT I
Standards	IEC 61810-1
	CSA C22.2 No 14
	UL 508
Product Certifications	EAC
	CSA
	CE
	UL
Pollution degree	2
Overvoltage category	III
Ambient Air Temperature for Storage	-40185 °F (-4085 °C)
Ambient air temperature for operation	-40158 °F (-4070 °C)
Relative humidity	1085 %

# Ordering and shipping details

Category	21127 - ZELIO ICE CUBE RELAYS
Discount Schedule	CP2
GTIN	3606480688737
Nbr. of units in pkg.	1
Package weight(Lbs)	0.74 oz (20.87 g)
Returnability	Yes
Country of origin	CN


## **Packing Units**


racking units	
Unit Type of Package 1	PCE
Package 1 Height	1.14 in (28.9 mm)
Package 1 width	0.50 in (12.7 mm)
Package 1 Length	1.36 in (34.52 mm)
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	14.42 oz (408.7 g)
Package 2 Height	1.36 in (3.45 cm)
Package 2 width	3.60 in (9.15 cm)
Package 2 Length	3.23 in (8.2 cm)
Unit Type of Package 3	S01
Number of Units in Package 3	200
Package 3 Weight	9.76 lb(US) (4.426 kg)
Package 3 Height	5.91 in (15 cm)
Package 3 width	5.91 in (15 cm)
Package 3 Length	15.75 in (40 cm)


# Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACh Regulation	☑ REACh Declaration
REACh free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	₫Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile


## **Dimensions**







# Wiring Diagram




# Product data sheet Performance Curves

# RXG12BD

### **Performance Curves**


## Maximum Switching Capacity



- X : Switching voltage (V)
- Y: Switching current (A)
- (1) AC Resistive Load
- (2) AC Inductive Load cos(Ø)=0.4
- (3) DC Resistive Load
- (4) DC Inductive Load (L/R=7ms)

## Life Expectancy


### Resistive Load



- X : Contact Current (A)
- Y: Operating Cycle Number

### Life Expectancy

## Inductive Load




- X : Contact Current (A)
- Y: Operating Cycle Number

NOTE: These are typical curves, actual durability depends on load, environment, duty cycle, etc.

## Coil Operating Range

## DC Coil Operating Range VS Ambient Temperature



X : Ambient temperature (°C)

Y : Coil voltage (U/Uc)

(1) Permitted operating range area