SIEMENS

Data sheet

3RA2115-1AA15-1AP6



Fuseless motor starter Direct start 600VAC Size S00 1.1-1.6A 220/240VAC 50/60HZ screw connection For screw mounting Or 35 mm rail-mounting Type of coordination 2 IQ = 150 KA Also full fills type Of coordination 1 1NO+1NC (MSP) 1NO (contactor)

number of burned in succession	
product brand name	SIRIUS non-fused motor starter 3RA2
product designation	
design of the product	direct starter
manufacturer's article number	
of the supplied contactor	<u>3RT2015-1AP61</u>
 of the supplied circuit-breakers 	<u>3RV2011-1AA15</u>
 of the supplied link module 	<u>3RA1921-1DA00</u>
General technical data	
size of the circuit-breaker	S00
size of load feeder	S00
product extension auxiliary switch	Yes
insulation voltage with degree of pollution 3 at AC rated value	690 V
degree of pollution	3
surge voltage resistance rated value	6 kV
shock resistance according to IEC 60068-2-27	6g / 11 ms
mechanical service life (switching cycles) of contactor typical	30 000 000
type of assignment	2
Ambient conditions	
ambient temperature	
 during operation 	-20 +60 °C
 during storage 	-50 +80 °C
during transport	-55 +80 °C
Main circuit	
number of poles for main current circuit	3
design of the switching contact	electromechanical
adjustable current response value current of the current-dependent overload release	1.1 1.6 A
operating voltage	
rated value	690 V
 at AC-3 rated value maximum 	690 V
operating frequency rated value	50 60 Hz
operational current at AC-3 at 400 V rated value	1.5 A
operating power at AC-3	
• at 400 V rated value	550 W
• at 500 V rated value	550 W
• at 690 V rated value	1 100 W
Control circuit/ Control	

● at 50 Hz rated value	220 V
at 50 Hz rated value at 50 Hz rated value	220 V 187 242 V
at 50 Hz rated value at 60 Hz rated value	187 242 V 240 V
at 60 Hz rated value	240 V 192 264 V
apparent holding power of magnet coil at AC	4.8 VA
inductive power factor with the holding power of the	0.25
coil	0.20
Auxiliary circuit	
number of NC contacts for auxiliary contacts	1
number of NO contacts for auxiliary contacts	2
Protective and monitoring functions	
trip class	CLASS 10
design of the overload release	thermal (bimetallic)
response value current of instantaneous short-circuit trip unit	20.8 A
UL/CSA ratings	
full-load current (FLA) for 3-phase AC motor	
• at 480 V rated value	1.6 A
• at 600 V rated value	1.3 A
yielded mechanical performance [hp]	
 for single-phase AC motor 	
— at 230 V rated value	0.1 hp
 for 3-phase AC motor 	
— at 460/480 V rated value	0.75 hp
— at 575/600 V rated value	0.75 hp
Short-circuit protection	
product function short circuit protection	Yes
design of the short-circuit trip	magnetic
conditional short-circuit current (Iq)	
 at 690 V according to IEC 60947-4-1 rated value 	100 000 A
 at 400 V according to IEC 60947-4-1 rated value 	153 000 A
at 500 V according to IEC 60947-4-1 rated value	100 000 A
Installation/ mounting/ dimensions	
mounting position	vertical
fastening method	Snap-mounted to DIN rail or screw-mounted with additional push-in lug
height	167.2 mm
width	45 mm
depth	97.1 mm
required spacing	
 for grounded parts forwards 	0 mm
— lorwards — backwards	0 mm
— upwards	20 mm
— upwards — at the side	9 mm
— downwards	10 mm
• for live parts	
— forwards	0 mm
— backwards	0 mm
— upwards	20 mm
— downwards	10 mm
— at the side	9 mm
	5 1111
Connections/ Terminals	
Connections/ Terminals type of electrical connection for main current circuit	screw-type terminals
type of electrical connection for main current circuit	
type of electrical connection for main current circuit type of connectable conductor cross-sections	screw-type terminals
type of electrical connection for main current circuit type of connectable conductor cross-sections • for main contacts stranded	screw-type terminals 0.5 4 mm², 2x (0.75 2.5 mm²)
type of electrical connection for main current circuit type of connectable conductor cross-sections • for main contacts stranded • at AWG cables for main contacts connectable conductor cross-section for main contacts	screw-type terminals 0.5 4 mm ² , 2x (0.75 2.5 mm ²) 2x (20 16), only for contactor 2x (18 14), 2x 12
type of electrical connection for main current circuit type of connectable conductor cross-sections • for main contacts stranded • at AWG cables for main contacts connectable conductor cross-section for main contacts finely stranded with core end processing	screw-type terminals 0.5 4 mm², 2x (0.75 2.5 mm²) 2x (20 16), only for contactor 2x (18 14), 2x 12

proportion of dange	rous failures with high der	nand rate 73	%		
proportion of dangerous failures with high demand rate according to SN 31920					
protection class IP on the front according to IEC 60529		to IEC IP2	20		
touch protection on the front according to IEC 60529			finger-safe, for vertical contact from the front		
ertificates/ approv	als				
General Product A	Approval			For use in hazard- ous locations	Declaration of Conformity
(SP)	<u>Confirmation</u>		EHC	K ATEX	UK CA
Declaration of Conformity	Test Certificates		Marine / Shipping		
CE EG-Konf.	<u>Special Test Certific-</u> <u>ate</u>	<u>Type Test Certific-</u> ates/Test Report	ABS	BUREAU	Llovd's Register us
Marine / Shipping				other	Railway
PRS	RINA	RMRS	DNV-GL	<u>Confirmation</u>	Vibration and Shock
urther information	ownloadcenter (Catalog	e Brochuros			
https://mall.industry Cax online general http://support.autom Service&Support (https://support.indus Image database (p http://www.automati Characteristic: Trij	ne ordering system) .siemens.com/mall/en/en/	CAXorder/default.asp haracteristics, FAQ n/ps/3RA2115-1AA1 nsion drawings, 3D ax_de.aspx?mlfb=3R , Let-through curren	<u>x?lang=en&mlfb=3RA211</u> s,) <u>5-1AP6</u> models, device circuit (A2115-1AA15-1AP6⟨ nt	<u>15-1AA15-1AP6</u> diagrams, EPLAN ma	cros,)
<u>nttps://support.indus</u>					

last modified:

12/15/2020 🖸