SIEMENS

Data sheet

3RA2210-0CE15-2BB4



Load feeder fuseless, Reversing duty 400 V AC, Size S00 0.18...0.25 A 24 V DC Spring-type terminal for installation on standard mounting rail (also fulfills type of coordination 1) Type of coordination 2, Iq = 150 kA 1 NC (contactor)

product brand name	SIRIUS
product designation	Reversing starter
design of the product	for standard rail or screw mounting
product type designation	3RA22
manufacturer's article number	
 of the supplied contactor 	<u>3RT2015-2BB42</u>
 of the supplied circuit-breakers 	<u>3RV2011-0CA20</u>
 of the supplied link module 	<u>3RA2911-2AA00</u>
General technical data	
size of the circuit-breaker	S00
size of load feeder	S00
insulation voltage with degree of pollution 3 at AC rated value	690 V
surge voltage resistance rated value	6 kV
degree of protection NEMA rating	other
shock resistance according to IEC 60068-2-27	6g / 11 ms
mechanical service life (switching cycles) of contactor typical	30 000 000
type of assignment	2
type of protection according to ATEX directive 2014/34/EU	Ex II (2) GD
certificate of suitability according to ATEX directive 2014/34/EU	DMT 02 ATEX F 001
Substance Prohibitance (Date)	10/01/2009
Ambient conditions	_
ambient temperature	
 during operation 	-20 +60 °C
 during storage 	-50 +80 °C
 during transport 	-50 +80 °C
temperature compensation	-20 +60 °C
relative humidity during operation	10 95 %
Main circuit	
number of poles for main current circuit	3
design of the switching contact	electromechanical
adjustable current response value current of the current-dependent overload release	0.18 0.25 A
operating voltage	
 rated value 	690 V
 at AC-3 rated value maximum 	690 V
operating frequency rated value	50 60 Hz

	_		
operational current at AC-3 at 400 V rated value	0.2 A		
operating power at AC-3			
at 400 V rated value	60 W		
Control circuit/ Control			
type of voltage of the control supply voltage	DC		
control supply voltage at DC			
 rated value 	24 V		
rated value	24 24 V		
holding power of magnet coil at DC	4 W		
Auxiliary circuit			
product extension auxiliary switch	Yes		
Protective and monitoring functions			
trip class	CLASS 10		
design of the overload release	thermal (bimetallic)		
UL/CSA ratings			
full-load current (FLA) for 3-phase AC motor			
• at 480 V rated value	0.25 A		
Short-circuit protection			
product function short circuit protection	Yes		
design of the short-circuit trip	magnetic		
conditional short-circuit current (lq)			
• at 400 V according to IEC 60947-4-1 rated value	150 000 A		
Installation/ mounting/ dimensions			
mounting position	vertical		
fastening method	screw and snap-on mountin	a onto 35 mm standard	mounting rail
height	204 mm	5	
width	90 mm		
depth	97 mm		
required spacing	_		
for grounded parts			
— forwards	32 mm		
— backwards	0 mm		
— upwards	50 mm		
— at the side	10 mm		
— downwards	10 mm		
• for live parts	10 1111		
— forwards	32 mm		
— backwards	0 mm		
— upwards	50 mm		
— downwards	10 mm		
— at the side	10 mm		
Connections/ Terminals			
type of electrical connection			
• for main current circuit	spring-loaded terminals		
	spring-loaded terminals		
for auxiliary and control circuit	spring-loaded terminals		
Safety related data	1 000 000		
B10 value with high demand rate according to SN 31920	1 000 000		
proportion of dangerous failures	70.0/		
with high demand rate according to SN 31920	73 %	and forces the force	
touch protection on the front according to IEC 60529	finger-safe, for vertical conta	act from the front	
Communication/ Protocol			
protocol is supported			
PROFINET IO protocol	No		
PROFIsafe protocol	No		
protocol is supported AS-Interface protocol	No		
Certificates/ approvals			
General Product Approval		For use in hazard- ous locations	Declaration of Conformity

	<u>Confirmation</u>		EHC	KEx ATEX	UK CA
Declaration of Conformity	Test Certificates		Marine / Shipping		
CE EG-Konf.	<u>Type Test Certific-</u> ates/Test Report	<u>Special Test Certific-</u> <u>ate</u>	ABS	BUREAU VERITAS	Lloyd's Register uis
Marine / Shipping				other	Railway
PRS	RINA	KMRS	DIVIGE DIVISION	<u>Confirmation</u>	Vibration and Shock
Dangerous Good					
<u>Transport Informa-</u> <u>tion</u>					
Further information					
https://www.siemens. Industry Mall (Online https://mall.industry.s Cax online generato http://support.automa Service&Support (M https://support.industr Image database (pro http://www.automation	e ordering system) iemens.com/mall/en/en r tion.siemens.com/WW/ anuals, Certificates, C y.siemens.com/cs/ww/ oduct images, 2D dime	gs, Brochures,) //Catalog/product?mlfb=: //CAXorder/default.aspx? Characteristics, FAQs,. /en/ps/3RA2210-0CE15- ension drawings, 3D m cax_de.aspx?mlfb=3RA2	<u>Plang=en&mlfb=3RA22</u>) <u>2BB4</u> iodels, device circuit (1 <u>0-0CE15-2BB4</u> diagrams, EPLAN m	acros,)

last modified:

2/16/2022 🖸