## 3RA2210-0HA03-0SB4

**Data sheet** 



Load feeder fuseless, Reversing duty 400 V AC, Size S00 0.55...0.80 A 24 V DC screw terminal for installation on standard mounting rail Type of coordination 1, Iq = 50 kA

product brand name	SIRIUS		
product designation	Reversing starter		
design of the product	for standard rail or screw mounting		
product type designation	3RA22		
manufacturer's article number			
<ul> <li>of the supplied contactor</li> </ul>	3RF3403-1BD04		
<ul> <li>of the supplied circuit-breakers</li> </ul>	3RV2011-0HA10		
<ul> <li>of the supplied link module</li> </ul>	3RA1921-1DA00		
General technical data			
size of the circuit-breaker	S00		
size of load feeder	S00		
insulation voltage with degree of pollution 3 at AC rated value	690 V		
surge voltage resistance rated value	6 kV		
degree of protection NEMA rating	other		
shock resistance according to IEC 60068-2-27	6g / 11 ms		
mechanical service life (switching cycles) of contactor typical	30 000 000		
type of assignment	1		
type of protection according to ATEX directive 2014/34/EU	Ex II (2) GD		
certificate of suitability according to ATEX directive 2014/34/EU	DMT 02 ATEX F 001		
Substance Prohibitance (Date)	10/01/2009		
Ambient conditions			
ambient temperature			
<ul> <li>during operation</li> </ul>	-20 +60 °C		
<ul> <li>during storage</li> </ul>	-50 +80 °C		
during transport	-50 +80 °C		
temperature compensation	-20 +60 °C		
relative humidity during operation	10 95 %		
Main circuit			
number of poles for main current circuit	3		
design of the switching contact	electromechanical		
adjustable current response value current of the current-dependent overload release	0.55 0.8 A		
operating voltage			
rated value	690 V		
at AC-3 rated value maximum	690 V		
operating frequency rated value	50 60 Hz		

		0.0.4			
operational current at AC-3 at 400 V rated va	ilue	0.6 A			
operating power at AC-3		400 1	<b>N</b>		
at 400 V rated value		180 V	V		
Control circuit/ Control		D.O.			
type of voltage of the control supply volta	ige	DC			
control supply voltage at DC		0414			
• rated value		24 V			
holding power of magnet coil at DC		4 W			
Auxiliary circuit					
product extension auxiliary switch		Yes			
Protective and monitoring functions					
trip class		CLASS 10			
design of the overload release		therm	al (bimetallic)		
UL/CSA ratings					
full-load current (FLA) for 3-phase AC mo	tor				
at 480 V rated value		0.8 A			
Short-circuit protection					
product function short circuit protection		Yes			
design of the short-circuit trip		magn	etic		
conditional short-circuit current (Iq)					
• at 400 V according to IEC 60947-4-1 ra	ated value	50 00	0 A		
Installation/ mounting/ dimensions					
mounting position		vertic			
fastening method				g onto 35 mm standard mounting rail	
height		260 n			
width		90 mr			
depth		97 mr	n		
required spacing					
for grounded parts					
— forwards		32 mr			
— backwards		0 mm			
— upwards		50 mm			
— at the side		10 mm			
— downwards		10 mr	11		
<ul><li>for live parts</li><li>forwards</li></ul>		32 mr	m		
— lorwards — backwards					
		0 mm 50 mm			
— upwards — downwards		10 mi			
— at the side		10 mi			
Connections/ Terminals		70 1111			
type of electrical connection  • for main current circuit			screw-type terminals		
for main current circuit     for auxiliary and control circuit			screw-type terminals screw-type terminals		
Safety related data		30101	type terminals		
	CN 24020	1 000	000		
	0 0				
proportion of dangerous failures		73 %			
with high demand rate according to SN 31920  touch protection on the front according to IEC 60529		finger-safe, for vertical contact from the front			
Communication/ Protocol	, ILC 00323	-saie, for vertical collic	det nom the nom		
protocol is supported		No			
PROFINET IO protocol     PROFINET Protocol		No			
PROFIsafe protocol      protocol is supported AS Interface protocol		No No			
protocol is supported AS-Interface protocol		INU			
Certificates/ approvals					
General Product Approval	For use in ha		Declaration of Conformity	other	





## Confirmation

## **Further information**

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RA2210-0HA03-0SB4

Cax online generator

 $\underline{\text{http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en\&mlfb=3RA2210-0HA03-0SB4}$ 

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3RA2210-0HA03-0SB4

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax\_de.aspx?mlfb=3RA2210-0HA03-0SB4&lang=en

Characteristic: Tripping characteristics, I2t, Let-through current

https://support.industry.siemens.com/cs/ww/en/ps/3RA2210-0HA03-0SB4/char

Further characteristics (e.g. electrical endurance, switching frequency)

http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RA2210-0HA03-0SB4&objecttype=14&gridview=view1

last modified:	2/16/2022 🖸
----------------	-------------