SIEMENS

Data sheet for SINAMICS G120X

Article No. :

6SL3220-2YE32-0AF0



Figure similar

Client order no. :
Order no. :
Offer no. :
Remarks :

Rated data		
Input		
Number of phases	3 AC	
Line voltage	380 480 V +10 %	6 -20 %
Line frequency	47 63 Hz	
Rated voltage	400V IEC	480V NEC
Rated current (LO)	42.00 A	37.00 A
Rated current (HO)	38.00 A	35.00 A
Output		
Number of phases	3 AC	
Rated voltage	400V IEC	480V NEC ¹⁾
Rated power (LO)	22.00 kW	30.00 hp
Rated power (HO)	18.50 kW	25.00 hp
Rated current (LO)	45.00 A	40.00 A
Rated current (HO)	38.00 A	34.00 A
Rated current (IN)	47.00 A	
Max. output current	61.00 A	
Pulse frequency	4 kHz	
Output frequency for vector control	0 200 Hz	
Output frequency for V/f control	0 550 Hz	

Overload capability

Low Overload (LO)

110% base load current IL for 60 s in a 300 s cycle time

High Overload (HO)

150% x base load current IH for 60 s within a 600 s cycle time

General tech. specifications		
Power factor λ	0.90 0.95	
Offset factor $\cos \phi$	0.99	
Efficiency η	0.97	
Sound pressure level (1m)	70 dB	
Power loss 3)	0.732 kW	
Filter class (integrated)	RFI suppression filter for Category C2	
EMC category (with accessories)	Category C2	
Safety function "Safe Torque Off"	without	

Communication

Communication

PROFINET, EtherNet/IP

ltem no. : Consignment no. : Project :

Standard digital inputs Number Switching level: $0 \rightarrow 1$ Switching level: $1 \rightarrow 0$	6 11 V 5 V	
Switching level: $0 \rightarrow 1$	11 V	
5		
Switching level: $1 \rightarrow 0$	5 V	
j		
Max. inrush current	15 mA	
Fail-safe digital inputs		
Number	1	
Digital outputs		
Number as relay changeover contact	2	
Output (resistive load)	DC 30 V, 5.0 A	
Number as transistor	0	
Analog / digital inputs		
Number	2 (Differential input)	
Resolution	10 bit	
Switching threshold as digital input		
0 → 1	4 V	
$1 \rightarrow 0$	1.6 V	
Analog outputs		
Number	1 (Non-isolated output)	
PTC/ KTY interface		
1 motor temperature sensor input, sensors that can be connected PTC, KTY and Thermo-Click, accuracy $\pm 5~^\circ\text{C}$		

Closed-loop cor	ntrol techniques
V/f linear / square-law / parameterizable	Yes
V/f with flux current control (FCC)	Yes
V/f ECO linear / square-law	Yes
Sensorless vector control	Yes
Vector control, with sensor	No
Encoderless torque control	No
Torque control, with encoder	No

SIEMENS

Data sheet for SINAMICS G120X

Article No. :

6SL3220-2YE32-0AF0

Ambient conditions		
Standard board coating type	Class 3C2, according to IEC 60721-3-3: 2002	
Cooling	Air cooling using an integrated fan	
Cooling air requirement	0.055 m³/s (1.942 ft³/s)	
Installation altitude	1,000 m (3,280.84 ft)	
Ambient temperature		
Operation	-20 45 °C (-4 113 °F)	
Transport	-40 70 °C (-40 158 °F)	
Storage	-25 55 °C (-13 131 °F)	
Relative humidity		
Max. operation	95 % At 40 °C (104 °F), condensation and icing not permissible	
Connections		
Signal cable		
Conductor cross-section	0.15 1.50 mm² (AWG 24 AWG 16)	
Conductor cross-section		
Line side	(AWG 24 AWG 16)	
Line side Version	(AWG 24 AWG 16) screw-type terminal 10.00 35.00 mm ²	
Line side Version Conductor cross-section	(AWG 24 AWG 16) screw-type terminal 10.00 35.00 mm ²	
Line side Version Conductor cross-section Motor end	(AWG 24 AWG 16) screw-type terminal 10.00 35.00 mm ² (AWG 8 AWG 2)	
Line side Version Conductor cross-section Motor end Version	(AWG 24 AWG 16) screw-type terminal 10.00 35.00 mm ² (AWG 8 AWG 2) Screw-type terminals 10.00 35.00 mm ²	
Line side Version Conductor cross-section Motor end Version Conductor cross-section	(AWG 24 AWG 16) screw-type terminal 10.00 35.00 mm ² (AWG 8 AWG 2) Screw-type terminals 10.00 35.00 mm ²	
Line side Version Conductor cross-section Motor end Version Conductor cross-section DC link (for braking resistor)	(AWG 24 AWG 16) screw-type terminal 10.00 35.00 mm ² (AWG 8 AWG 2) Screw-type terminals 10.00 35.00 mm ² (AWG 8 AWG 2)	

	Me	chanical data	
Degree	e of protection	IP20 / UL open	type
Frame	e size	FSD	
Net we	eight	18 kg (39.68 l	o)
Dimer	nsions		
Wid	th	200 mm (7.87	in)
Heig	ght	472 mm (18.5	8 in)
Dep	th	248 mm (9.76	in)
		Standards	
Compliance with standards UL, cUL, CE, C-Tick (RCM), EAC, KCC, SEMI F47, REACH			
CE ma	rking		2004/108/EC, Low- ve 2006/95/EC
	Converter lo	osses to IEC61800-	9-2*
Efficie	ncy class	IE2	
	arison with the reference rter (90% / 100%)	48.2 %	
I 100%	483.0 W (1.6 %)	573.0 W (1.8%)	732.0 W (2.4 %)
50%	296.0 W (1.0 %)	327.0 W (1.1 %)	376.0 W (1.2 %)
	234.0 W (0.8 %)	246.0 W (0.8 %)	

The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

*converted values

¹⁾The output current and HP ratings are valid for the voltage range 440V-480V

³⁾Typical value. More information can be found in the element group "Converter losses to IEC 61800-9-2" in this datasheet.

SIEMENS

Data sheet for SINAMICS G120X

Article No. :

6SL3220-2YE32-0AF0

Operator panel: Basic Operator Panel (BOP-2)

[
	Screen	
Display design	LCD, monochrome	
[
Mechanical data		
Degree of protection	IP55 / UL type 12	
Net weight	0.140 kg (0.31 lb)	
Dimensions		
Width	70.00 mm (2.76 in)	
Height	106.85 mm (4.21 in)	
Depth	19.60 mm (0.77 in)	

Ambient conditions		
Ambient temperature		
Operation	0 50 °C (32 122 °F)	
Storage	-40 70 °C (-40 158 °F)	
Transport	-40 70 °C (-40 158 °F)	
Relative humidity at 25°C during		
Max. operation	95 %	
Approvals		
Certificate of suitability	CE, cULus, EAC, KCC, RCM	