SIEMENS

Data sheet for SINAMICS G120X

Article No. :

6SL3220-2YH28-0UB0



Figure similar

Client order no. :
Order no. :
Offer no. :
Remarks :

Rate	ed data	
Input		
Number of phases	3 AC	
Line voltage	500 690 V +10	% -20 %
Line frequency	47 63 Hz	
Rated voltage	690V IEC	600V NEC
Rated current (LO)	18.00 A	18.00 A
Rated current (HO)	14.60 A	14.60 A
Output		
Number of phases	3 AC	
Rated voltage	690V IEC	600V NEC ¹⁾
Rated power (LO)	15.00 kW	15.00 hp
Rated power (HO)	11.00 kW	10.00 hp
Rated current (LO)	19.00 A	19.00 A
Rated current (HO)	14.00 A	14.00 A
Rated current (IN)	20.00 A	
Max. output current	26.00 A	
Pulse frequency	2 kHz	
Output frequency for vector control	0 200 Hz	
Output frequency for V/f control	0 550 Hz	
Overload capability		

Overload capability

Low Overload (LO)

110% base load current IL for 60 s in a 300 s cycle time

High Overload (HO)

150% x base load current IH for 60 s within a 600 s cycle time

General tech. specifications		
Power factor λ	0.90 0.95	
Offset factor $\cos \phi$	0.99	
Efficiency η	0.98	
Sound pressure level (1m)	70 dB	
Power loss 3)	0.453 kW	
Filter class (integrated)	Unfiltered	
EMC category (with accessories)	without	
Safety function "Safe Torque Off"	without SIRIUS device (e.g. via S7- 1500F)	
Communication		

Communication

USS, Modbus RTU, BACnet MS/TP

ltem no. : Consignment no. : Project :

Standard digital inputs Number Switching level: $0 \rightarrow 1$	6 11 V 5 V	
	11 V	
Switching level: $0 \rightarrow 1$		
5	5 V	
Switching level: $1 \rightarrow 0$		
Max. inrush current	15 mA	
Fail-safe digital inputs		
Number	1	
Digital outputs		
Number as relay changeover contact	2	
Output (resistive load)	DC 30 V, 5.0 A	
Number as transistor	0	
Analog / digital inputs		
Number	2 (Differential input)	
Resolution	10 bit	
Switching threshold as digital input		
0 → 1	4 V	
1 → 0	1.6 V	
Analog outputs		
Number	1 (Non-isolated output)	
PTC/ KTY interface		
1 motor temperature sensor input, sensors that can be connected PTC, KTY and Thermo-Click, accuracy $\pm 5~^\circ\text{C}$		

Closed-loop control techniques	
V/f linear / square-law / parameterizable	Yes
V/f with flux current control (FCC)	Yes
V/f ECO linear / square-law	Yes
Sensorless vector control	Yes
Vector control, with sensor	No
Encoderless torque control	No
Torque control, with encoder	No

SIEMENS


Data sheet for SINAMICS G120X

Article No. :

6SL3220-2YH28-0UB0

Ambient conditions		
Standard board coating type	Class 3C2, according to IEC 60721-3-3: 2002	
Cooling	Air cooling using an integrated fan	
Cooling air requirement	0.055 m³/s (1.942 ft³/s)	
Installation altitude	1,000 m (3,280.84 ft)	
Ambient temperature		
Operation	-20 45 °C (-4 113 °F)	
Transport	-40 70 °C (-40 158 °F)	
Storage	-25 55 °C (-13 131 °F)	
Relative humidity		
Max. operation	95 % At 40 °C (104 °F), condensation and icing not permissible	
Con	inections	
Signal cable		
Conductor cross-section	0.15 1.50 mm² (AWG 24 AWG 16)	
Line side		
Version	screw-type terminal	
Conductor cross-section	10.00 35.00 mm² (AWG 8 AWG 2)	
Motor end		
Version	Screw-type terminals	
Conductor cross-section	10.00 35.00 mm² (AWG 8 AWG 2)	
DC link (for braking resistor)		
PE connection	Screw-type terminals	
Max. motor cable length		
Shielded	200 m (656.17 ft)	
Unshielded	300 m (984.25 ft)	

Me	echanical data	
Degree of protection	IP20 / UL open	type
Frame size	FSD	
Net weight	16.6 kg (36.60) lb)
Dimensions		
Width	200 mm (7.87	in)
Height	472 mm (18.5	8 in)
Depth	248 mm (9.76	in)
	Standards	
Compliance with standards	UL, cUL, CE, C- SEMI F47, REA	Tick (RCM), EAC, KCC, CH
CE marking		2004/108/EC, Low- ive 2006/95/EC
Converter l	osses to IEC61800-	9-2*
Efficiency class	IE2	
Comparison with the reference converter (90% / 100%)	39.4 %	
I ▲ 385.0 W (1.7 %)	411.0 W (1.8 %)	452.0 W (2.0 %)
100% •	•	•
278.0 W (1.2 %)	289.0 W (1.3 %)	303.0 W (1.3 %)



The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

*converted values

¹⁾The output current and HP ratings are valid for the voltage range 550V-600V

³⁾ Typical value. More information can be found in the element group "Converter losses to IEC 61800-9-2" in this datasheet.

SIEMENS

Data sheet for SINAMICS G120X

Article No. :

6SL3220-2YH28-0UB0

Operator panel: Basic Operator Panel (BOP-2)

Screen		
Display design	LCD, monochrome	
Mechanical data		
Degree of protection	IP55 / UL type 12	
Net weight	0.140 kg (0.31 lb)	
Dimensions		
Width	70.00 mm (2.76 in)	
Height	106.85 mm (4.21 in)	
Depth	19.60 mm (0.77 in)	

Ambient conditions		
Ambient temperature		
Operation	0 50 °C (32 122 °F)	
Storage	-40 70 °C (-40 158 °F)	
Transport	-40 70 °C (-40 158 °F)	
Relative humidity at 25°C during	9	
Max. operation	95 %	
Approvals		
	Approvais	
Certificate of suitability	CE, cULus, EAC, KCC, RCM	