SIEMENS

Data sheet US2:87GUG6MG



Pump control panel, Size 2 1/2, Three phase full voltage, Solid-state overload relay, OLR amp range 25-100A, 190-220/220-240V 50/60Hz coil, Standard type contactor, 100A circuit breaker, HOA Sel Sw. <(>&<)> Start P.B., Enclosure NEMA type 3/3R, Weather proof outdoor use

| product brand name | Class 87 |
|---|---|
| design of the product | Pump control panel with MCP |
| special product feature | Half-size controller; ESP200 overload relay |
| General technical data | |
| weight [lb] | 48 lb |
| Height x Width x Depth [in] | 29 × 20 × 8 in |
| touch protection against electrical shock | NA for enclosed products |
| | |

| touch protection against electrical shock | NA for enclosed products |
|--|--------------------------|
| installation altitude [ft] at height above sea level maximum | 6560 ft |
| ambient temperature [°F] | |
| during storage | -22 +149 °F |
| during operation | -4 +104 °F |
| ambient temperature | |
| during storage | -30 +65 °C |
| | 00 |

| during storage | -30 +65 °C |
|--|------------|
| during operation | -20 +40 °C |
| country of origin | USA |
| Horsepower ratings | |
| yielded mechanical performance [hp] for 3-phase AC motor | |

| • | |
|--|-------|
| vielded mechanical performance [hp] for 3-phase AC motor | |
| at 200/208 V rated value | 15 hp |
| at 220/230 V rated value | 20 hp |
| at 460/480 V rated value | 30 hp |
| ■ at 575/600 V rated value | 30 hn |

| at 220/230 V rated value | 20 hp |
|---|-------------------------------------|
| at 460/480 V rated value | 30 hp |
| at 575/600 V rated value | 30 hp |
| Contactor | |
| size of contactor | Controller half size 2 1/2 |
| number of NO contacts for main contacts | 3 |
| operating voltage for main current circuit at AC at 60 Hz maximum | 600 V |
| operational current at AC at 600 V rated value | 60 A |
| mechanical service life (switching cycles) of the main contacts typical | 10000000 |
| Auxiliary contact | |
| number of NC contacts at contactor for auxiliary contacts | 0 |
| number of NO contacts at contactor for auxiliary contacts | 1 |
| number of total auxiliary contacts maximum | 7 |
| contact rating of auxiliary contacts of contactor according to UL | 10A@600VAC (A600), 5A@600VDC (P600) |
| Coil | |
| type of voltage of the control supply voltage | AC |

control supply voltage

| 100 1 1 | 0 01/ |
|---|--|
| at DC rated value | 0 0 V |
| at AC at 50 Hz rated value | 190 220 V |
| at AC at 60 Hz rated value | 220 240 V |
| holding power at AC minimum | 8.6 W |
| apparent pick-up power of magnet coil at AC | 218 VA |
| apparent holding power of magnet coil at AC | 25 VA |
| operating range factor control supply voltage rated value of magnet coil | 0.85 1.1 |
| percental drop-out voltage of magnet coil related to the input voltage | 50 % |
| ON-delay time | 19 29 ms |
| OFF-delay time | 10 24 ms |
| Overload relay | |
| product function | |
| overload protection | Yes |
| phase failure detection | Yes |
| asymmetry detection | Yes |
| ground fault detection | Yes |
| test function | Yes |
| external reset | Yes |
| reset function | Manual, automatic and remote |
| trip class | CLASS 5 / 10 (factory set) / 20 / 30 |
| adjustable current response value current of the current- dependent overload release | 25 100 A |
| tripping time at phase-loss maximum | 3 s |
| relative repeat accuracy | 1 % |
| product feature protective coating on printed-circuit board | Yes |
| number of NC contacts of auxiliary contacts of overload relay | 1 |
| number of NO contacts of auxiliary contacts of overload relay | 1 |
| operational current of auxiliary contacts of overload relay | |
| at AC at 600 V | 5 A |
| • at DC at 250 V | 1 A |
| contact rating of auxiliary contacts of overload relay according to UL | 5A@600VAC (B600), 1A@250VDC (R300) |
| insulation voltage (Ui) | |
| with single-phase operation at AC rated value | 600 V |
| with multi-phase operation at AC rated value | 300 V |
| Enclosure | |
| degree of protection NEMA rating of the enclosure | NEMA Type 3R |
| design of the housing | Weather proof for outdoor use |
| Standard Control Devices | |
| product component Hand-Off-Auto selector switch | Yes |
| type of Hand-Off-Auto selector switch | 30mm metal housing with matte finish |
| product component start push button | Yes |
| type of start push button | 30mm metal housing with matte finish |
| Circuit Breaker | |
| type of the motor protection | Motor circuit protector (magnetic trip only) |
| operational current of motor circuit breaker rated value | 100 A |
| adjustable current response value current of instantaneous short-circuit trip unit | 315 1000 A |
| Mounting/wiring | |
| mounting position | Vertical |
| fastening method | Surface mounting and installation |
| type of electrical connection for supply voltage line-side | Box lug |
| type of connectable conductor cross-sections at line-side | 1x (10 AWG 1/0 AWG) |
| | , |
| at AWG cables single or multi-stranded | 75 °C |
| temperature of the conductor for supply maximum permissible | 75 °C |
| temperature of the conductor for supply maximum | 75 °C AL or CU Box lug |

| tightening torque [lbf·in] for load-side outgoing feeder | 45 45 lbf·in |
|--|---|
| | |
| type of connectable conductor cross-sections at AWG cables for load-side outgoing feeder single or multi-stranded | 1x (14 2 AWG) |
| temperature of the conductor for load-side outgoing feeder maximum permissible | 75 °C |
| material of the conductor for load-side outgoing feeder | AL or CU |
| type of electrical connection of magnet coil | Screw-type terminals |
| tightening torque [lbf·in] at magnet coil | 5 12 lbf·in |
| type of connectable conductor cross-sections of magnet coil at AWG cables single or multi-stranded | 2x (16 12 AWG) |
| temperature of the conductor at magnet coil maximum permissible | 75 °C |
| material of the conductor at magnet coil | CU |
| type of electrical connection at contactor for auxiliary contacts | Screw-type terminals |
| tightening torque [lbf·in] at contactor for auxiliary contacts | 10 15 lbf·in |
| type of connectable conductor cross-sections at contactor at AWG cables for auxiliary contacts single or multi-stranded | 1x (12 AWG), 2x (16 14 AWG), 2x (18 16 AWG) |
| temperature of the conductor at contactor for auxiliary contacts maximum permissible | 75 °C |
| material of the conductor at contactor for auxiliary contacts | CU |
| type of electrical connection at overload relay for auxiliary contacts | Screw-type terminals |
| tightening torque [lbf·in] at overload relay for auxiliary contacts | 7 10 lbf·in |
| type of connectable conductor cross-sections at overload relay at AWG cables for auxiliary contacts single or multi-stranded | 2x (20 14 AWG) |
| temperature of the conductor at overload relay for auxiliary contacts maximum permissible | 75 °C |
| material of the conductor at overload relay for auxiliary contacts | CU |
| Short-circuit current rating | |
| design of the short-circuit trip | Instantaneous trip circuit breaker |
| breaking capacity maximum short-circuit current (lcu) | |
| ● at 240 V | 100 kA |
| ● at 480 V | 100 kA |
| ● at 600 V | 25 kA |
| certificate of suitability | NEMA ICS 2; UL 508 |
| | |

Industrial Controls - Product Overview (Catalogs, Brochures,...)

www.usa.siemens.com/iccatalog

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:87GUG6MG

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/US/en/ps/US2:87GUG6MG

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:87GUG6MG&lang=en

Certificates/approvals

https://support.industry.siemens.com/cs/US/en/ps/US2:87GUG6MG/certificate

| | _ | |
|---------------|------------|---|
| ast modified: | 1/8/2022 (| 7 |