


Data sheet for SINAMICS G120X

6SL3230-3YE34-0UP0 Article No.:

Client order no. : Order no.: Offer no. : Remarks :



Over	load	capa	bi	litv

Low Overload (LO)

110% base load current IL for 60 s in a 300 s cycle time

High Overload (HO)

150% x base load current IH for 60 s within a 600 s cycle time

General tech. specifications		
Power factor λ	0.90 0.95	
Offset factor $\cos\phi$	0.99	
Efficiency η	0.97	
Sound pressure level (1m)	70 dB	
Power loss 3)	0.841 kW	
Filter class (integrated)	Unfiltered	
EMC category (with accessories)	without	
Safety function "Safe Torque Off"	without	

_				•
1 ^	mm	III	cat	เกท
CU		um	cat	U

PROFIBUS DP Communication



Item no.: Consignment no. : Project :

Inputs /	Inputs / outputs		
Standard digital inputs			
Number	6		
Switching level: $0 \rightarrow 1$	11 V		
Switching level: $1 \rightarrow 0$	5 V		
Max. inrush current	15 mA		
Fail-safe digital inputs			
Number	1		
Digital outputs			
Number as relay changeover contact	2		
Output (resistive load)	DC 30 V, 5.0 A		
Number as transistor	0		
Analog / digital inputs			
Number	2 (Differential input)		
Resolution	10 bit		
Switching threshold as digital input			
0 → 1	4 V		
1 → 0	1.6 V		
Analog outputs			
Number	1 (Non-isolated output)		

PTC/ KTY interface

1 motor temperature sensor input, sensors that can be connected PTC, KTY and Thermo-Click, accuracy ±5 °C

Closed-loop control techniques		
V/f linear / square-law / parameterizable	Yes	
V/f with flux current control (FCC)	Yes	
V/f ECO linear / square-law	Yes	
Sensorless vector control	Yes	
Vector control, with sensor	No	
Encoderless torque control	No	
Torque control, with encoder	No	




Data sheet for SINAMICS G120X

Article No.: 6SL3230-3YE34-0UP0

Ambient conditions			
Standard board coating type	Class 3C3, according to IEC 60721-3-3: 2002		
Cooling	Air cooling using an integrated fan		
Cooling air requirement	0.055 m³/s (1.942 ft³/s)		
Installation altitude	1,000 m (3,280.84 ft)		
Ambient temperature			
Operation	-20 45 °C (-4 113 °F)		
Transport	-40 70 °C (-40 158 °F)		
Storage	-25 55 °C (-13 131 °F)		
Relative humidity			
Max. operation	95 % At 40 °C (104 °F), condensation and icing not permissible		
Conn	ections		
Signal cable			
Conductor cross-section	0.15 1.50 mm ² (AWG 24 AWG 16)		
Line side			
Version	screw-type terminal		
Conductor cross-section	10.00 35.00 mm ² (AWG 8 AWG 2)		
Motor end			
Version	Screw-type terminals		
Conductor cross-section	10.00 35.00 mm ² (AWG 8 AWG 2)		
DC link (for braking resistor)			
PE connection	Screw-type terminals		
Max. motor cable length			
Shielded	200 m (656.17 ft)		
Unshielded	300 m (984.25 ft)		

Mechanical data			
D	egree of protection	IP20 / UL open type	
F	rame size	FSD	
Net weight		17 kg (37.48 lb)	
D	imensions		
	Width	200 mm (7.87 in)	
	Height	472 mm (18.58 in)	
	Depth	248 mm (9.76 in)	
	Stand	dards	
C	ompliance with standards	UL, cUL, CE, C-Tick (RCM), EAC, KCC, SEMI F47, REACH	
C	E marking	EMC Directive 2004/108/EC, Low- Voltage Directive 2006/95/EC	

Converter losses	to IEC61800-9-2*
Efficiency class	IE2
Comparison with the reference converter (90% / 100%)	41.9 %



The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

*converted values

 $^{^{1)}}$ The output current and HP ratings are valid for the voltage range 440V-480V

³⁾Typical value. More information can be found in the element group "Converter losses to IEC 61800-9-2" in this datasheet.



Data sheet for SINAMICS G120X

Article No.: 6SL3230-3YE34-0UP0

	Operator panel: I	ntelligent Operator Panel (IOP-2)
	Screen	
Display design	LCD color	Ambient temperature
Screen resolution	320 x 240 Pixel	Operation
	Mechanical data	Storage
Degree of protection	IP55 / UL type 12	Transport
Net weight	0.134 kg (0.30 lb)	Relative humidity at 25°C
Dimensions		Max. operation
Width	70.00 mm (2.76 in)	operation
Height	106.85 mm (4.21 in)	
Depth	19.65 mm (0.77 in)	Certificate of suitability

Ambient conditions			
Ambient temperature			
Operation	0 50 °C (32 122 °F)		
	55 °C only with door installation kit		
Storage	-40 70 °C (-40 158 °F)		
Transport	-40 70 °C (-40 158 °F)		
elative humidity at 25°C durir	ng		
Max. operation	95 %		
	Approvals		
Certificate of suitability CE, cULus, EAC, KCC, RCM			