
	REVISIONS							
REV	ECO	DESCRIPTION	DATE	BY	APPR			
A1	-	RELEASE NEW DRAWING	16/JUL/20	VITO	TOMMY			



17.2 8.5 8.5 (14 PLACES)

50.8±0.5 Ø38.1 Ø33.8

RECOMMENDED TORQUE VALUES: 1.9-2.2 N.m

NOTES: UNLESS OTHERWISE SPECIFIED

MATERIAL:

HOUSING: THERMOPLASTIC; BLACK

SEAL: SILICONE RUBBER

THREADED INSERT: STAINLESS STEEL


2. MODIFICATIONS: WIDE THREAD ADAPTER (WTA); REDUCED DIA. WIRE SEAL; SEALED PANEL MOUNT

SEALED PA

- 3. SPECIFICATIONS:
 - 3.1 OPERATING TEMPERATURE: -55°C TO +125°C.
 - 3.2 DIELECTRIC WITHSTANDING VOLTAGE: LESS THAN 2 MILLIAMPS CURRENT LEAKAGE @ 1500 VOLTS AC.
 - 3.3 INSULATION RESISTANCE: 1000 MEGOHM MIN @ 25°C.
 - 3.4 MOISTURE RESISTANCE: IP67&IP69K (MATED CONDITION).
 - 3.5 MATING CYCLE DURABILITY: 100 CYCLES
 - 3.6 RoHS COMPLIANT
- 4. MATING PART: AHDP06-18-14S* (* = SEAL TYPE)
- 5. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.


6 CONTACT SIZE AND WIRE RANGE:

CONTACT	MIN. INSUL	MAX. INSUL	TYPICAL	CURRENT
SIZE	O.D.	O.D.	WIRE RANGE	RATING
16	1.35 mm (.053in)	3.05 mm (.120 in)	14-20 AWG (2.0-0.5mm²)	



RECOMMENDED PANEL MOUNTING HOLE

RECOMMENDED PANEL THICKNESS:1.6 TO 4.7MM



	PART N	IUMBER				DE	SCRIP
QUANTITY		ı	MAT	ERI	ALS	3 LI	ST
	UNLESS OTHERWISE SPECIFIED			DATE			
1) All dimensions a 2) Tolerances are 1 PL DEC ±0.30		DRAWN:	VITO	16/JUL/20		_	m
2 PL DEC ±0.15 3 PL DEC ±0.08	Angles ±1°	CHECKED:	ORION	17/JUL/20	_	Sir	ne Systen
3) Note reference	- 📐	ENGINEER:					44724 M
MATERIAL SPECIFICA	TIONS:	APPROVAL:	TOMMY	20/JUL/20			Clinton
		CUSTOMER:				14 PC	S, REC
PROOFES SPECIFICA	TIONIO	INFORMATION	S IS SUPPLIED F ONLY. DESIGN	FEATURES,			AHDP S
PROCESS SPECIFICA	SHOWN HERE THE AMPHENO OF REPRODUC	NS AND PERFOI ON ARE THE PR OL CORPORATIO CTION ARE IMPL ARE SUBJECT TO	ROPERTY OF DN. NO RIGHTS LIED. ALL	B	C-	AH[

MANUFACTURING VARIATIONS

AHDP02-18-14PR-WTA

Amphenol
Sine Systems - www.amphenol-sine.com
44724 Morley Drive
Clinton Township. MI 48036

DESCRIPTION

AHDP02-18-14PR-WTA

REV: A1

ITEM

14 POS, RECEPTACLE, PIN, PANELMATE AHDP SIZE 18, RD SEAL, WTA



AT Series™ - Contact Size 16 Options

Machined Contacts, Sockets & Pins						
Part Number	Description		AWG	Туре		
AT60-215-1631	Male Contact - Pin, Gold-plated	16	14	Machined		
AT62-209-1631	Female Contact - Socket, Gold-plated	16	14	Machined		
AT60-215-16141	Male Contact - Pin, Nickel-plated	16	14	Machined		
AT62-209-16141	Female Contact - Socket, Nickel-plated		14	Machined		
AT60-202-1631	Male Contact - Pin, Gold-plated	16	16-20	Machined		
AT62-201-1631	Female Contact - Socket, Gold-plated		16-20	Machined		
AT60-202-16141 Male Contact - Pin, Nickel-plated		16	16-20	Machined		
AT62-201-16141	Female Contact - Socket, Nickel-plated	16	16-20	Machined		
AT60-202-1631-22	Male Contact - Pin, Gold-plated	16	22-24	Machined		
AT62-201-1631-22	Female Contact - Socket, Gold-plated	16	22-24	Machined		
AT60-202-16141-22	Male Contact - Pin, Nickel-plated	16	22-24	Machined		
AT62-201-16141-22	Female Contact - Socket, Nickel-plated	16	22-24	Machined		

Tooling - Machined Contacts					
Part	Part Part Number Description				
	CA-5D12	Universal Hand Crimp Tool, Size 12/16/20 (Machined contacts only)			
3	CA-5E12	Pneumatic Crimp Tool, Size 12/16/20 (Machined contacts only)			

Contact Removal Tools						
Part	Part Number	Description				
3	ATRT-100	Used for removal of contacts for A Series™ products				
	AT11-310-1605	Contact Removal Tool, Plastic, Size 16				
	A114017	Sealing Plug, Size 16, White				

Stamped & Formed Contacts, Sockets & Pins						
Part Number	Description	Size	AWG	Туре		
AT60-14-0144	Male Contact - Pin, Gold-plated	16	14-16	Stamped & Formed		
AT62-14-0144	Female Contact - Socket, Gold-plated	16	14-16	Stamped & Formed		
AT60-14-0122	Male Contact - Pin, Nickel-plated	16	14-16	Stamped & Formed		
AT62-14-0122	Female Contact - Socket, Nickel-plated	16	14-16	Stamped & Formed		
AT60-16-0144	Male Contact - Pin, Gold-plated	16	16-18	Stamped & Formed		
AT62-16-0144	Female Contact - Socket, Gold-plated	16	16-18	Stamped & Formed		
AT60-16-0122	Male Contact - Pin, Nickel-plated	16	16-18	Stamped & Formed		
AT62-16-0122	Female Contact - Socket, Nickel-plated	16	16-18	Stamped & Formed		
AT60-16-0644	Male Contact - Pin, Gold-plated	16	18-20	Stamped & Formed		
AT62-16-0644	Female Contact - Socket, Gold-plated	16	18-20	Stamped & Formed		
AT60-16-0622	Male Contact - Pin, Nickel-plated	16	18-20	Stamped & Formed		
AT62-16-0622	Female Contact - Socket, Nickel-plated	16	18-20	Stamped & Formed		
AT60-16-0844	Male Contact - Pin, Gold-plated	16	20-22	Stamped & Formed		
AT62-16-0844	Female Contact - Socket, Gold-plated	16	20-22	Stamped & Formed		
AT60-16-0822	Male Contact - Pin, Nickel-plated	16	20-22	Stamped & Formed		
AT62-16-0822	Female Contact - Socket, Nickel-plated	16	20-22	Stamped & Formed		

Tooling - Stamped & Formed Contacts					
Part	Part Number	Description			
	MFX-3950	Crimp Die - Size 16, 18-20AWG (S&F contacts only)			
	MFX-3953	Crimp Die - Size 16, 16-18AWG (S&F contacts only)			
	MFX-3975	Crimp Die - Size 16, 14-16AWG (S&F contacts only)			
	MFX-3990	Crimp Die - Size 16, 20-22AWG (S&F contacts only)			
	ATT-16-00	Hand Crimp Tool - Size 16, 14-16AWG (S&F contacts only)			
	ATT-16-01	Hand Crimp Tool - Size 16, 18-20AWG (S&F contacts only)			
	ATT-1612-03	Hand Crimp Tool - Size 16, 20-22AWG (S&F contacts only)			

Amphenol Sine Systems 44724 Morley Drive Clinton Township, MI 48036 USA www.amphenol-sine.com 09/2021