ALPHA & OMEGA SEMICONDUCTOR

AOTF7N60FD

600V, 7A N-Channel MOSFET with Fast Recovery Diode

General Description

The AOTF7N60FD has been fabricated using an advanced high voltage MOSFET process that is designed to deliver high levels of performance and robustness in popular AC-DC applications. By providing low $R_{DS(on)}$, C_{iss} and C_{rss} along with guaranteed avalanche capability this part can be adopted quickly into new and existing offline power supply designs.

Product Summary

V_{DS}	700V@150℃
I_D (at V_{GS}=10V)	7A
$R_{DS(ON)}$ (at V_{GS}=10V)	< 1.45Ω

100% UIS Tested
100% R_g Tested

Green Product

Top View
TO-220F



AOTF7N60FD



Absolute Maximum Ratings T_A=25°C unless otherwise noted

Parameter		Symbol	AOTF7N60FD	Units
Drain-Source Voltage		V_{DS}	600	V
Gate-Source Voltage		V_{GS}	±30	V
Continuous Drain Current	T_C=25°C	I_D	7*	A
	T_C=100°C		4.7*	
Pulsed Drain Current [C]		I_{DM}	24	
Avalanche Current [C]		I_{AR}	3.5	A
Repetitive avalanche energy [C]		E_{AR}	184	mJ
Single pulsed avalanche energy [G]		E_{AS}	368	mJ
Peak diode recovery dv/dt		dv/dt	5	V/ns
Power Dissipation [B]	T_C=25°C	P_D	39	W
	Derate above 25°C		0.3	W/ °C
Junction and Storage Temperature Range		T_J, T_{STG}	-55 to 150	°C
Maximum lead temperature for soldering purpose, 1/8" from case for 5 seconds		T_L	300	°C

Thermal Characteristics

Parameter	Symbol	AOTF7N60FD	Units
Maximum Junction-to-Ambient [A,D]	$R_{\theta JA}$	65	°C/W
Maximum Junction-to-Case	$R_{\theta JC}$	3.25	°C/W

* Drain current limited by maximum junction temperature.

Electrical Characteristics (T_J=25°C unless otherwise noted)

Symbol	Parameter	Conditions	Min	Typ	Max	Units
STATIC PARAMETERS						
BV_{DSS}	Drain-Source Breakdown Voltage	I_D=10mA, V_{GS}=0V, T_J=25°C	600			V
		I_D=10mA, V_{GS}=0V, T_J=150°C		700		
BV_{DSS} /ΔTJ	Breakdown Voltage Temperature Coefficient	I_D=10mA, V_{GS}=0V		0.68		V/°C
I_{DSS}	Zero Gate Voltage Drain Current	V_{DS}=600V, V_{GS}=0V			10	μA
		V_{DS}=480V, T_J=125°C			100	
I_{GSS}	Gate-Body leakage current	V_{DS}=0V, V_{GS}=±30V			±100	nA
$V_{GS(th)}$	Gate Threshold Voltage	V_{DS}=5V, I_D=250μA	2.5	3.3	4.2	V
$R_{DS(ON)}$	Static Drain-Source On-Resistance	V_{GS}=10V, I_D=3.5A		1.2	1.45	Ω
g_{FS}	Forward Transconductance	V_{DS}=40V, I_D=3.5A		7		S
V_{SD}	Diode Forward Voltage	I_S=7A,V_{GS}=0V		1.03	1.6	V
I_S	Maximum Body-Diode Continuous Current				7	A
I_{SM}	Maximum Body-Diode Pulsed Current				24	A
DYNAMIC PARAMETERS						
C_{iss}	Input Capacitance	V_{GS}=0V, V_{DS}=25V, f=1MHz	600	826	995	pF
C_{oss}	Output Capacitance		60	86	115	pF
C_{rss}	Reverse Transfer Capacitance		4.5	7.9	11.5	pF
R_g	Gate resistance	V_{GS}=0V, V_{DS}=0V, f=1MHz	2	4	6	Ω
SWITCHING PARAMETERS						
Q_g	Total Gate Charge	V_{GS}=10V, V_{DS}=480V, I_D=7A	15	20	25	nC
Q_{gs}	Gate Source Charge			3.6		nC
Q_{gd}	Gate Drain Charge			7.7		nC
$t_{D(on)}$	Turn-On DelayTime	V_{GS}=10V, V_{DS}=300V, I_D=7A, R_G=25Ω		24		ns
t_r	Turn-On Rise Time			55		ns
$t_{D(off)}$	Turn-Off DelayTime			56		ns
t_f	Turn-Off Fall Time			42		ns
t_{rr}	Body Diode Reverse Recovery Time	I_F=7A,dI/dt=100A/μs,V_{DS}=100V		76	130	ns
Q_{rr}	Body Diode Reverse Recovery Charge	I_F=7A,dI/dt=100A/μs,V_{DS}=100V		0.3	0.5	μC

A. The value of $R_{\theta JA}$ is measured with the device in a still air environment with T_A=25° C.
B. The power dissipation P_D is based on $T_{J(MAX)}$=150° C, using junction-to-case thermal resistance, and is more useful in setting the upper dissipation limit for cases where additional heatsinking is used.
C. Repetitive rating, pulse width limited by junction temperature $T_{J(MAX)}$=150° C, Ratings are based on low frequency and duty cycles to keep initial T_J =25° C.
D. The $R_{\theta JA}$ is the sum of the thermal impedance from junction to case $R_{\theta JC}$ and case to ambient.
E. The static characteristics in Figures 1 to 6 are obtained using <300 μs pulses, duty cycle 0.5% max.
F. These curves are based on the junction-to-case thermal impedance which is measured with the device mounted to a large heatsink, assuming a maximum junction temperature of $T_{J(MAX)}$=150° C. The SOA curve provides a single pulse rating.
G. L=60mH, I_{AS}=3.5A, V_{DD}=150V, R_G=25Ω, Starting T_J=25° C

TYPICAL ELECTRICAL AND THERMAL CHARACTERISTICS



Figure 1: On-Region Characteristics



Figure 2: Transfer Characteristics



Figure 3: On-Resistance vs. Drain Current and Gate Voltage



Figure 4: On-Resistance vs. Junction Temperature



Figure 5: Break Down vs. Junction Temperature



Figure 6: Body-Diode Characteristics (Note E)

TYPICAL ELECTRICAL AND THERMAL CHARACTERISTICS



Figure 7: Gate-Charge Characteristics



Figure 8: Capacitance Characteristics



Figure 9: Maximum Forward Biased Safe Operating Area for AOTF7N60FD (Note F)



Figure 10: Current De-rating (Note B)



Figure 11: Normalized Maximum Transient Thermal Impedance for AOTF7N60FD (Note F)

TYPICAL ELECTRICAL AND THERMAL CHARACTERISTICS



Figure 12: Diode Recovery Characteristics

Gate Charge Test Circuit & Waveform



Resistive Switching Test Circuit & Waveforms



Unclamped Inductive Switching (UIS) Test Circuit & Waveforms



Diode Recovery Test Circuit & Waveforms