







300CMQ035/300CMQ040/300CMQ045 SCHOTTKY RECTIFIER



Features

- 150℃ T_J operation
- · Center tap module
- High purity, high temperature epoxy encapsulation for
- enhanced mechanical strength and moisture resistance
- Low forward voltage drop
- High frequency operation
- Guard ring for enhanced ruggedness and long term reliability
- Base plate: Nickel plated; Terminals: Nickel plated
- This is a Pb Free Device
- . All SMC parts are traceable to the wafer lot
- Additional testing can be offered upon request

Circuit Diagram



Applications

- · High current switching power supply
- Plating power supply
- Free-Wheeling diodes
- Reverse battery protection
- Converters
- UPS System
- Welding

Maximum Ratings(limiting values, at 25 °C unless otherwise specified)

Characteristics	Symbol	Condition	Max.		Units
Peak Repetitive Reverse Voltage	V_{RRM}	-	35	300CMQ035	
Working Peak Reverse Voltage	V_{RWM}		40 300CMQ040		V
DC Blocking Voltage	V_R		45	300CMQ045	
Average Rectified Forward Current	I _{F(AV)}	50% duty cycle @T _C =104°C,	150(Per Leg)		А
Average Rectilled Forward Current		rectangular wave form	300(Per Device)		
Peak One Cycle Non-Repetitive	Irou	8.3 ms, half Sine pulse	2880		Α
Surge Current (Per Leg)	IFSM	I _{FSM} 8.3 ms, half Sine pulse		2000	
Non-Repetitive Avalanche	E _{AS}	T _J =25°C,I _{AS} =30A,L=0.67mH 150		150	mJ
Energy(Peg Leg)	, ,		100		0
Repetitive Avalanche Current		Current decaying linearly to zero			
(Peg Leg)	I _{AR}	in 1 µsec Frequency limited by		30	Α
		T _J max. V _A =1.5×V _R typical			

- China Germany Korea Singapore United States
 - http://www.smc-diodes.com sales@ smc-diodes.com •









Electrical Characteristics:

Characteristics	Symbol	Condition	Тур.	Max.	Units
Forward Voltage Drop(Per Leg)*	V _{F1}	@ 150A, Pulse, T _J = 25 °C @ 300A, Pulse, T _J = 25 °C	0.55 0.69	0.61 0.77	V
	V _{F2}	@ 150A, Pulse, T _J = 125 °C @ 300A, Pulse, T _J = 125 °C	0.52 0.64	0.62 0.75	V
Reverse Current(Per Leg)*	I _{R1}	$@V_R = \text{rated } V_{R_s} T_J = 25 ^{\circ}\text{C}$	0.5	15	mA
	I _{R2}	$@V_R = \text{rated } V_{R,} T_J = 125 ^{\circ}\text{C}$	99	750	mA
Junction Capacitance(Per leg)	Ст	$@V_R = 5V, T_C = 25 °C$ $f_{SIG} = 1MHz$	6500	7750	pF
Voltage Rate of Change	dv/dt	-	-	10,000	V/μs

^{*} Pulse width < 300 µs, duty cycle < 2%

Thermal-Mechanical Specifications:


Characteristics	Symbol	Condition	Specification		Units
Junction Temperature	ΤJ	-	-55 to +150		°C
Storage Temperature	T _{stg}	-	-55 to +150		°C
Typical Thermal Resistance Junction to Case(Per leg)	R _θ JC	DC operation	0.30		°C/W
Typical Thermal Resistance Junction to Case(Per package)	$R_{ heta JC}$	DC operation	0.15		°C/W
Typical Thermal Resistance, case to Heat Sink	$R_{ heta cs}$	Mounting surface, smooth and greased	0.05		°C/W
Mounting Torque	т		Mounting Torque	24(min) 35(max)	Va om
Mounting Torque	T_M	-	Terminal Torque	35(min) 46(max)	- Kg-cm
Approximate Weight	wt	-	110		g
Case Style	PRM4 Isolated				







Ratings and Characteristics Curves













Mechanical Dimensions PRM4 Isolated(Millimeters/Inches)



SYMBOL	Millimeters		Inches	
STIVIBUL	Min.	Max.	Min.	Max.
А	78.74	81.28	3.100	3.200
В	37.47	42.55	1.475	1.675
С	6.89	7.69	0.271	0.303
D	19.51	24.59	0.768	0.968
E	33.02	38.10	1.300	1.500
F	17.78	20.32	0.700	0.800
G	60.96	64.77	2.400	2.550
Н	17.56	23.55	0.691	0.927
I	90.17	92.71	3.550	3.650
J	3.02	3.68	0.119	0.145
K	15.75	17.50	0.620	0.689

Please Note: Suffix "R" Denotes For Reversed Polarity

Marking Diagram



Where XXXX is YYWW

300CMQ035 = Part name SS = SS YY = Year WW = Week

Cautions: Molding resin

Epoxy resin UL:94V-0

Ordering Information

Device	Package	Shipping	
300CMQ SERIES	PRM4 Isolated (Pb-Free)	9 pcs/box	









DISCLAIMER:

- 1- The information given herein, including the specifications and dimensions, is subject to change without prior notice to improve product characteristics. Before ordering, purchasers are advised to contact the SMC Diode Solutions sales department for the latest version of the datasheet(s).
- 2- In cases where extremely high reliability is required (such as use in nuclear power control, aerospace and aviation, traffic equipment, medical equipment, and safety equipment), safety should be ensured by using semiconductor devices that feature assured safety or by means of users' fail-safe precautions or other arrangement.
- 3- In no event shall SMC Diode Solutions be liable for any damages that may result from an accident or any other cause during operation of the user's units according to the datasheet(s). SMC Diode Solution assumes no responsibility for any intellectual property claims or any other problems that may result from applications of information, products or circuits described in the datasheets.
- 4- In no event shall SMC Diode Solutions be liable for any failure in a semiconductor device or any secondary damage resulting from use at a value exceeding the absolute maximum rating.
- 5- No license is granted by the datasheet(s) under any patents or other rights of any third party or SMC Diode Solutions.
- 6- The datasheet(s) may not be reproduced or duplicated, in any form, in whole or part, without the expressed written permission of SMC Diode Solutions.
- 7- The products (technologies) described in the datasheet(s) are not to be provided to any party whose purpose in their application will hinder maintenance of international peace and safety nor are they to be applied to that purpose by their direct purchasers or any third party. When exporting these products (technologies), the necessary procedures are to be taken in accordance with related laws and regulations..