

26.5 to 40 GHz, 17 dBi

*Withwave's Standard Gain Horn Antenna* operates in the frequency range from 26.5 GHz to 40 GHz. This gain horn antenna have nominal gain of 17.0 dBi and Horizontal 3 dB beam width of 27.4 degrees and Vertical 3 dB beam width of 22.1 degrees. This antenna can be rotated to the desired angle by pulling and rotating it.



#### Features

- Rectangular Waveguide Interface
- Freq. range : 26.5 to 40 GHz
- Nominal Gain : 17 dBi

#### Configuration

- Design : Standard Gain Horn
- Pattern : Directional
- Polarization : Linear
- Coaxial interface : 2.92 mm(Female)


### Specification

Scope	Specification	WAKH-01
Electrical	Freq. Range	26.5 to 40 GHz
	Impedance	50 Ohm
	Gain	17~19 dBi
	Horizontal 3 dB beam width	$20 \pm 5^{\circ}$
	Vertical 3 dB beam width	$16 \pm 5^{\circ}$
	Input VSWR	1.5 : 1
Mechanical	Connector type	2.92 mm(Female)
	Wave guide Size	91.4 x 40 x 40 (with bracket)
	Flange type	Square Cover
	Weight	60 g



26.5 to 40 GHz, 17 dBi

#### Gain Graph



#### Gain Table


Frequency(GHz)	Gain (dB)
26.5	17.12
27.0	17.35
28.0	16.82
29.0	17.66
30.0	18.04
31.0	17.86
32.0	18.31
33.0	18.78
34.0	18.71
35.0	18.58
36.0	19.49
37.0	19.04
38.0	19.26
39.0	19.61
40.0	19.62




26.5 to 40 GHz, 17 dBi

#### Pattern


### **Horizontal Patterns**




#### 32.5 to 35 GHz




38.5 to 40 GHz





35.5 to 38 GHz







26.5 to 40 GHz, 17 dBi

#### Pattern


### **Vertical Patterns**




32.5 to 35 GHz








35.5 to 38 GHz





26.5 to 40 GHz, 17 dBi

#### VSWR





### Freq. range: 26.5 to 40 GHz



26.5 to 40 GHz, 17 dBi

Drawing







www.with-wave.com 220601\_Ver1.0




26.5 to 40 GHz, 17 dBi

Instrument design



\*Antenna can be rotated to the desired angle by pulling and rotating it



\*\* Depending on the size of the tripod, installation may not be possible. Please check the drawing dimensions.



26.5 to 40 GHz, 17 dBi

### Revision History

Revision	Date	Changes
Ver 1.0	2022-06-01	Released Standard Gain Horn Antenna