т	Q	н <b>п</b>		0







LAYOUT SHOWN AS

Keying Shown as example

## CHARACTERISTICS

ယ

 $\sim$ 

-Mass

BASIC SERIES:

SHELL SIZE : 17

Н

SHELL TYPE : Square Flange Receptacle

CONTACT TYPE : Standard Crimp Contact

PLATING : J = Olive drab Cadmium

-Standard : Based on MIL-DTL-38999 Series III

ł	-Shell Material	: Composite		
	-Shell Plating	: Olive drab Cadmium		
	-Insulator	: Thermoplastic		
	-Contacts	: Copper Alloy		
	-Seals & Grommet	: Silicon Elastomer		
	-Contact Plating	: Gold over copper Alloy $0.8 \mu m$ minimum		
	-Durability	: 500 Mating cycles		
	-Delivered without Sou	vered without Souriau contacts		
	-Temperature Range	: -65°C to +175°C		
	-Salt Spray	: 2000 hours		

: 19.2 g ± 10%

8D 0

G

17

J

06

Ρ

F

N L

Connector dimension					
Dim	Nominal				
Р	3.25±0.2				
PP	4.93±0.2				
R1	26.97				
R2	24.61				
S	33.3±0.3				
۷'	19.5+1.4/-0				
W'	2.1/3.65				
Ζ'	32 Max				
VV THREAD	M25x1-6g				

Delivered W/O Contacts


CONTACT LAYOUT : 17-06

CONTACT TYPE : PIN(500 Matings)

Е

**ORIENTATION : N** 

SOURIAU shall not be liable for a due to a use of the Products the Specifications issued by either (professional recommend



	Φ		A				
					4		
	AMPLE				3		
whic er of t	any non-conformity or damage which does not comply with r of the Parties or by a third party dation, technical notice.)						
Intry R	/ Jurisdiction & Control List Not Listed						
7J06PNL							
				MOD N°			
		CUSTOME	R DRAWING				
	e Receptacle 8D series						
ar	NPRDS / PROJECT 859						
	.COM This document is the property of SOURIAU it must not be reproduced or communicated without permission						
			SHEET				
106	PNL-C		A	1/2	J		

