

т	۵	н <b>т</b>	m	0







LAYOUT SHOWN AS

Keying Shown as example

Connector dimension

Dim

Nominal

CONTACT LAYOUT : 19-11

D

Е

## CHARACTERISTICS

ω

-Standard : Based on MIL-DTL-38999 Series III

	-Shell Material	: Composite						Р		3.25±0.2	
								PP		4.93±0.2	
	-Shell Plating	: Nickel						R1		29.36	
	-Insulator	: Thermoplastic						R2		26.97	
	-Contacts	: Copper Alloy						S		36.5±0.3	
								V'		9.5+1.4/-0	
	-Seals & Grommet	: Silicon Elastomer						W'		2.1/3.65	
N	-Contact Plating	: Gold over copper Alloy 0.8µm	minim	num				Z'		32 Max	
	-Durability	: 500 Mating cycles						VV THREAD		M28x1-6g	
	-Delivered without Sou										
	-Delivered without Sol										
	-Temperature Range	-65°C to +200°C									
	-Salt Spray	: 2000 hours									
_	-Mass	: 22.7 g ± 10%									
	BASIC SERIES:	8D 0 -	19	М	11	Р	А	L			
<b>_</b>	SHELL TYPE : Square	Flange Receptacle								Delivered W/0	O Contacts
		ndard Crimp Contact									
	CONTACT TYPE : Sta		J							ORIEN	TATION : A
	SHELL SIZE : 19								CONTACT	T TYPE : PIN(50	0 Matings)
				1							


F

G

PLATING : M = Nickel

Н

SOURIAU shall not be liable for due to a use of the Products the Specifications issued by either (professional recomment



σ		A			
R			4		
S EXAMPLE			3		
any non-conformit which does not co or of the Parties or b adation, technical no intry Jurisd R OM11PAL	mply with by a third party	List	2		
	CUSTOMER D	RAWING			
ite Receptacle 8D series					
ar	NPRDS / PR <b>859</b>	ROJECT	1		
J.COM This document is the property of SOURIAU it must not be reproduced or communicated without permission					
U DRG N° M11PAL-C		SHE			
B		Α			

