

COAXIAL TERMINATION N FEMALE


4 GHZ 1W Z50

R404.132.000

Series: TERMINATION







All dimensions are in mm.



COMPONENTS	MATERIALS	PLATING(μm)
BODY CENTER CONTACT OUTER CONTACT INSULATOR GASKET SUBSTRATE RESISTOR OTHERS PARTS	BRASS BERYLLIUM COPPER PTFE SILICONE ALUMINA THICK FILM	NICKEL 2 GOLD 0.7 to 1 over NICKEL 2

Issue: 0850 A

In the effort to improve our products, we reserve the right to make changes judged to be necessary.



COAXIAL TERMINATION N FEMALE

4 GHZ 1W Z50

R404.132.000

Series: TERMINATION

ELECTRICAL CHARACTERISTICS

Frequency (GHz)	DC - 1	1 - 4
V.S.W.R (≤)	1.08	1.20

DC - 4	GHz
50	Ω
50	$\Omega \pm 2\%$
500	W
1	W (Free Air Cooled)
	W (Conduction Cooled)
	50 50


MECHANICAL CHARACTERISTICS

Connectors	N	Female	MIL C39012
Weight	33,2900 g		

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range	-55 /+125 °C
Storage temperature range	-55 /+125 °C

Power derating Versus temperature



SPECIFICATION

OTHER CHARACTERISTICS

