
	<del>ال</del>	т			0	Δ		
Z'	ØS							
	Keying Shown a				LAYOUT	SHOWN AS EXAMPLE		
CHARACTERISTICS -Standard : Based on MIL-DTL-38999 Series III -Shell Material : Composite -Shell Plating : Olive drab Cadmium -Insulator : Thermoplastic -Contacts : Copper Alloy -Seals & Grommet : Silicon Elastomer -Contact Plating : Gold over copper Alloy 0.8µm minimum		Connector dimensionDimNominalØS21.8 MaxZ'31.5 MaxVV THREADM12x1-6g			due to a use of th he Specifications issue	e liable for any non-conformit e Products which does not cor ed by either of the Parties or b recommendation, technical no Country Jurisd FR	nply with y a third party	
-Durability : 500 Mating cycles -Delivered with Souriau contacts and Accessories -Temperature Range : -65°C to +175°C -Salt Spray : 2000 hours -Mass : 9.8 g ± 10%			A IS	S DATE La	t Release atest modification - b	8D509J98BN		MOD N°
			Des	igned By: TITLE	Date:	Composite Plug 8	CUSTOMER DRAWING	
BASIC SERIES: 8D 5 - 09 J SHELL TYPE : Plug with RFI Shielding CONTACT TYPE : Standard Crimp Contact SHELL SIZE : 09	98 B N	ORIE CONTACT TYPE : SOCKET(		SCALE NA OURIAU		ieneral linear Tolerances: ±	NPRDS / PROJECT 859 This document is the pro SOURIAU it must not be reprodu communicated without p	uced or
				ORMAT	S	OURIAU DRG N°		SHEET

r	Ŧ	۵	т	m		0
		Contact Layout				
4	-X	$ \begin{array}{c}                                     $				
	Shell Arrangement Numb size no. cont 9 -98 3	+ 065 (1.65) + 038 (0.97) + 000 (0.00) - 075 (1.91) - 065 (1.65) + 038 (0.97) - 065 (1.65) + 038 (0.97) - 065 (1.65) + 038 (0.97) - 065 (1.65) + 038 (0.97)				
ω						
	-					SOURIAU shall not be liable for an due to a use of the Products wl the Specifications issued by either o (professional recommenda
N						PN: 8D509
					A 14-10-20 ISS DATE Designed By:	16 First Release
					TITLE SCALE NA	General linear Tolerances:
					SOURIA	
					FORMAT A3	SOURIAU 8D509J9
L	Н	G	F	E	D	C



ω