
ר בר			0			
	ØS					
	Keying Shown as example		LAYOUT SH	HOWN AS EXAMPLE		
CHARACTERISTICS	Connector dimensio					
-Standard : Based on MIL-DTL-38999 Series III -Shell Material : Composite -Shell Plating : Olive drab Cadmium -Insulator : Thermoplastic -Contacts : Copper Alloy -Seals & Grommet : Silicon Elastomer -Contact Plating : Gold over copper Alloy 0.8μm minimum	ØS 25 Z' 31.5	hinal Max Max k1-6g	SOURIAU shall not be liable for any non-conformity or damage due to a use of the Products which does not comply with the Specifications issued by either of the Parties or by a third party (professional recommendation, technical notice.) Country Jurisdiction & Control List FR Not Listed			
-Durability : 500 Mating cycles -Delivered with Souriau contacts and Accessories			PN: 8D511J98BC			
-Temperature Range : -65°C to +175°C						
-Salt Spray : 2000 hours			A 16-10-2016 First Release			
Mass : 15.3 g ± 10%		ISS Designed By	DATE Latest modification - by : Date:			MOD N°
		тіт	LE	Composite Plug 8D	series	
BASIC SERIES: 8D 5 - 11 J SHELL TYPE : Plug with RFI Shielding	98 B C	SCALE		eral linear lerances: ±	NPRDS / PROJECT 859	
CONTACT TYPE : Standard Crimp Contact		ORIENTATION : C SOUP	RIAU WWW.SOU	RIAU.COM	This document is the property SOURIAU it must not be reproduced or	r
SHELL SIZE : 11		OCKET(500 Matings)			communicated without permiss	sion
PLATING : J = Olive drab Cadmium	CON	TACT LAYOUT : 11-98		URIAU DRG N° D511J98BC-C		SHEET 1/2
						-/-

	т	۵	п –	— п		O
						<u> </u>
		Contact Layout				
	-×					
4						
	Cont					
	posii IE A B C	+.000 (0.00) +.130 (3.30) 3 +.130 (3.30)				
		130 (3.30) +.000 (0.00) +.000 (0.00) +.000 (0.00)	_			
	Sheli Arrangement no. Numb conta 11 -98 6	acts contacts rating location				
ω						
-	-					
						SOURIAU shall not be liable for ar due to a use of the Products w the Specifications issued by either o (professional recommenda
\sim						Count
						PN: 8D511
					A 16-10-20	016 First Release
					ISS DATE Designed By:	Latest modification - by Date:
					TITLE	Comp
					SCALE	General linear Tolerances:
<u> </u>					NA	±
					SOURIA	
					FORMAT A3	SOURIAU 8D511J
l	Н	G	F	E	D	C



 \triangleright

σ