
⊥	۵	П	m			0		A	
		ØS							
ω						LAYOU	JT SHOWN AS EXAMPLE		
-Insulator : Thermo -Contacts : Copper -Seals & Grommet : Silicon E -Contact Plating : Gold over	ite ab Cadmium plastic Alloy lastomer er copper Alloy 0.8μm minimum ting cycles and Accessories	Keying Shown a	Connector dimension Dim Nominal ØS 29.4 Max Z' 31.5 Max VV THREAD M18x1-6g		A 17-10-2016	due to a use of t the Specifications iss (professiona PN	be liable for any non-conforr the Products which does not ued by either of the Parties o I recommendation, technical Country Jun FR I: 8D513J04BA	comply with r by a third party	
-Salt Spray : 2000 ho 					ISS DATE Designed By:	Latest modification - Date:	by	CUSTOMER DRAWING	MOD N°
BASIC SERIES:	8D 5 - 13 J	04 B A			SCALE		Composite Plug General linear Tolerances:	NPRDS / PROJECT	
SHELL TYPE : Plug with RFI Shield CONTACT TYPE : Standard Crim SHELL SIZE : 13	p Contact		CONTACT TYPE : SOCKE		NA SOURIAU		± OURIAU.COM	859 This document is the pro SOURIAU it must not be reproduc communicated without pe	ced or
PLATING : J = Olive drab	Laomium	1	CONTACT	AYOUT : 13-04	A3		SOURIAU DRG N 8D513J04BA-C		1/2

-		ര	н г	m	D	0
		Contact Layout				
4	×	$ \begin{array}{c} $				
	Conta position A B C D Shell Arrangement N size no. c 13 -4	+.000 (0.00) +.150 (3.81) +.146 (3.71) +.035 (0.89) +.000 (0.00)083 (2.11) 146 (3.71) +.035 (0.89)				
ω						
	1					
						SOURIAU shall not be liable for an due to a use of the Products wi the Specifications issued by either o (professional recommenda
N						Count FR
						PN: 8D513
					A 17-10-20	016 First Release
_					ISS DATE Designed By:	Latest modification - by Date:
					TITLE	Compo
<u> </u>					SCALE NA	General linear Tolerances:
					SOURIA	U WWW.SOURIAU.C
					FORMAT A3	SOURIAU 8D513J
L	Н	G	F	E	D	C



ω