
## **Technical Data Sheet**

SMA ATTENUATOR 3 DB 8 GHZ 15W





This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.

## **Technical Data Sheet**

SMA ATTENUATOR 3 DB 8 GHZ 15W



PAGE <b>2/2</b>		SUE 1337E	SERIES ATTENUATOR	PART NUMBER <b>R415303000</b>	
			ELECT	RICAL CHARACTERISTICS	
Fraguasa			4.0	7	
		DC - 4 1.15	4 - 8 1.25	_	
V.S.W.R (≤) Deviation(±dB)		0.30	0.30	_	
Doviation	ub)				
	Onenatio	- Francisco - Dav			
		g Frequency Rar	ige	DC - 8 50	GHz Ω
Impedance Nominal Attenu				3	dB
Peak power at 25°C			1% 0)	250	W
Average power at 25°C		15		W (Free Air Cooled)	
					W (Conduction Cooled)
			MECHA	NICAL CHARACTERISTICS	
onnectors /eight		SMA 19,7700	g	Male Female	MIL-C 39012
			erating temperature		C
			rage temperature ra		С С
			Pow	r derating Versus temperature	
			Pow	er derating Versus temperature	
			Pow	r derating Versus temperature 15 25 /+125 r derating Versus temperature 15 25 75 125 Temperature (°C)	

This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.