







Ultra Low Profile 0603 RF Crossover

Description

The (patent pending) is an ultra-small low profile crossover that enables the transition of two intersecting RF traces in an easy to use industry standard SMT package. The 0603 crossover is ideal for any critical applications where layout and available space are a premium and resorting to addition PWB layers and larger overall footprints are unacceptable. With low insertion loss and high isolation packaged with cost in mind, this novel component delivers.

The X0060L7575AHF is available on tape and reel for pick and place high volume manufacturing. All of the Xinger components are constructed from ceramic filled PTFE composites which possess excellent electrical and mechanical stability. All parts have been subjected to rigorous qualification testing and units are 100% RF tested.


Detailed Electrical Specifications*: Specifications subject to change without notice.

Features:

- 0 2500 MHz.
- 0.7mm Height Profile
- 75 Ohm RF-RF Crossover
- All Wireless Frequencies
- Low Insertion Loss
- · High Isolation
- Surface Mountable
- Tape & Reel
- Non-conductive Surface
- RoHS Compliant
- Halogen Free

	R	ROOM (25°C)		
Parameter	Min.	Тур.	Max	Unit
Frequency	0		2500	MHz
Port Impedance		75		Ω
Return Loss	19	21		dB
Insertion Loss		0.1	0.15	dB
Isolation (cross-talk)				
0 – 700 MHz	44	52		dB
700 - 1700 MHz	40	47		dB
1700 - 2500 MHz	38	43		dB
Power Handling			2	Watts
Operating Temperature	-55		+85	°C


Outline Drawing



Dimensions are in mm



PIN	DESIGNATION	
1	INPUT/OUTPUT	
2	INPUT/OUTPUT	
3	OUTPUT / INPUT	
4	GROUND	
.5	OUTPUT / INPUT	
6	GROUND	



Tolerances are Non-Cumulative





Visit us at www.anaren.com



Typical Broadband Performance: 0 GHz. to 3.0 GHz.












Mounting Configuration:

In order for Xinger surface mount components to work optimally, the proper impedance transmission lines must be used to connect to the RF ports. If this condition is not satisfied, insertion loss, Isolation and VSWR may not meet published specifications.

All of the Xinger components are constructed from organic PTFE based composites which possess excellent electrical and mechanical stability. Xinger components are compliant to a variety of ROHS and Green standards and ready for Pbfree soldering processes. Pads are Gold plated with a Nickel barrier.

An example of the PCB footprint used in the testing of these parts is shown below. In specific designs, the transmission line widths need to be adjusted to the unique dielectric coefficients and thicknesses as well as varying pick and place equipment tolerances.








Visit us at www.anaren.com


Rev C



Packaging and Ordering Information

Parts are available in reel and are packaged per EIA 481-2. Parts are oriented in tape and reel as shown below. Minimum order quantities are 4000 per reel. See Model Numbers below for further ordering information.








TABLE 1					
QUANTITY/REEL	REEL DIMENSIONS mm				
4000	ØΑ	177.80			
	В	8.00			
	øС	50.80			
	ØD	13.00			



Visit us at www.anaren.com