



Multi- Channel NB IoT – Cat-M1 Low Power Transmission Interface for Industrial Applications

- Compatible with most standard communication Protocols (UDP, LwM2M, MQTT, NIDD, etc.)
- Wide range of industrial applications
- Designed to meet outdoor applications
- Long-term durable performance in harsh environment
- Ultra-low power

# **TECHNICAL SPECIFICATION**

## **Sensor Interface**



| <ul> <li>Interface options:<br/>(RM1-N has option of up to 5 channels for<br/>industrial sensor interface. Unique design of the<br/>interface gives ultimate flexibility of choosing up to<br/>5 sensor interfaces with different choices for each<br/>channel)</li> </ul> | <ul> <li>Ch 1: I2C</li> <li>Ch 2: Pulse (Reed Switch)</li> <li>Ch 3: mV / 4-20mA / 0-10V</li> <li>Ch 4: Pt temperature (Pt100 2wire, Pt100 3 wire, Pt100</li> <li>Ch 5: RS232/ RS485/ Modbus/ HART/ SDI12/ TTL /UA 0-5V / 0-10V/ 4-20mA (or other customised options on request)</li> </ul> |     |  |  |  |  |
|--|---|-----|--|--|--|--|
| Electric Connection:   | 1m cable, pin connection (or other options on request)<br>-10 ~ + 70 °C   |     |  |  |  |  |
| <ul> <li>Operating temperature range:</li> </ul>   | -10 ~ + 70 °C   |     |  |  |  |  |
| Power  |   |     |  |  |  |  |
| Power Supply:  | Built-in Replaceable Lithium Battery, External Power (optio   | n)  |  |  |  |  |
| Rated Voltage  | 3.6 V   |     |  |  |  |  |
| Battery Lifetime:  | Typ. 50,000+ readings and 10,000+ transmission<br>(With UDP protocol/ More than 10 years for most applications)   |     |  |  |  |  |
| Physical Specification   |   |     |  |  |  |  |
| Materials:   | ASA or POM  |     |  |  |  |  |
| Weight:  | 350 g   |     |  |  |  |  |
| <ul> <li>Protection Rate:</li> </ul>   | IP66 /IP68, UV Protected -  |     |  |  |  |  |
| Communication  |   |     |  |  |  |  |
| SIM Card Type  | 4FF Nano-SIM, from any Network Provider   |     |  |  |  |  |
| Firmware Update:   | Over The Air, Locally via Wireless Connectivity   |     |  |  |  |  |
| Sampling Period:   | Configurable via downlink (default 4 hours)   |     |  |  |  |  |
| Power Consumption:   | Power Saving: < 5uA, Transmission: < 220mA  |     |  |  |  |  |
| <ul> <li>Communication Standards</li> </ul>  | Cat-NB1 (NB-IoT)  |     |  |  |  |  |
|  | Cat-M1  |     |  |  |  |  |
| Communication Bands  | (option of back support by GPRS)<br>B1/B2/B3/B4/B5/B8/B12/B13/B18/B19/B20/B26/B28 and B   | 220 |  |  |  |  |
|  |   | 09  |  |  |  |  |
| Data Rates:  | Cat-M1: 375Kbps (DL)/375Kbps (UL)<br>NB-IoT: 32Kbps (DL)/70Kbps (UL)  |     |  |  |  |  |
| TX Power:  | 23dBm   |     |  |  |  |  |



 Min Receiver Sensitivity: Cat-M1: -107dBm NB-IoT: -113dBm
 Antenna: Internal (Default)/ External (customised options available)
 Optional Features: Attach without PDN (Packet Data Network)
 Support for IPV6
 SMS communication
 Mobility support (Cat-M1 only)

# **NETWORK CONNECTION AND VISUALISATION**

### **Network Integration**


Pre-configured or configurable to all main narrow band networks (3, A1, AT&T, China Mobile, DU, Etisalat, KPN, M1 Singapore, Optus, Orange, Proximus, Spark, Sprint, Swisscom, Telefonica, Telstra, T-Mobile, Verizon, Vodafone, 1NCE, Emnify and any other network)

## **Visualisation and Data Management**

Ellenex white label microservice platform and Integratable to all main IIoT platforms directly or through the API(AWS, Azure, PTC ThingWorx, Bosch IoT, Cisco Jasper & Kinetic, Sierra Numerex, MathWorks ThingSpeak, GE Digital Predix, LandisGyr, Siemens MindSphere, Cumulocity, myDevices, Ubidots, TagoIO, AllThingsTalk Maker, HPE IoT and any other major IoT platform).

## **Ellenex Platform Main Features**

- Encrypted ultra-low power communication protocol
- Advanced device inventory
- Integration APIs for enterprise systems
- Multi-tenant role-based access control
- Data export and import
- White-label platform for enterprise runs on private account
- · Variable alarm setting for high and low thresholds and multi-channel alerting
- Sampling and transmission interval configuration
- Transmission condition configuration
- Other configurations and customisation available on request





# **MODEL GUIDE**

| C Model: |                        |  | E Model:                 |  |   |  |  |  |
|----------|------------------------|--|--------------------------|--|---|--|--|--|
| aller    | et.                    | <b>C model</b> comes with<br>cylindrical shape housing<br>suitable for battery<br>operated applications with<br>IP68 rate, 2 or 3 channel<br>interfaces and clamp<br>mounting. This model has<br>2 option of wire cable<br>connection and the 12pin<br>connection. | Colored and the second   | rectangula<br>suitable fo<br>external pe<br>application<br>up to 5 ch<br>and wall m<br>model has | comes with<br>ar shape housing<br>r battery or<br>ower operated<br>as with IP66 rate,<br>annel interfaces<br>nounting. This<br>a 2 option of wire<br>nection and up to<br>on. |  |  |  |
|          | Water &                |  | Agriculture &            |  | Oil &   |  |  |  |
|          | Environment            |  | Farming                  |  | Gas   |  |  |  |
|          | Marine&<br>Oceanograph |  | Mining &<br>Construction |  | Smart Building<br>& HVAC  |  |  |  |
|          | Transport & Logistics  |  | Food &<br>Beverage       |  | Hydraulics and<br>Compressed<br>Air Systems   |  |  |  |

## **APPLICATIONS**

- Pump Performance Monitoring
- Water Pipeline Pressure Monitoring
- Pressurised System Monitoring
- Chiller and Cooling System Monitoring
- Hydraulic and Pneumatic Systems Monitoring
- Liquid Storage Level Monitoring
- Spraying System Monitoring
- Air Compressor Monitoring



# **ORDERING CODE**

| RM1-N |     |           |        |                                      |    |              |                   |            |                             |                  |             |                           |  |
|-------|-----|-----------|--------|--------------------------------------|----|--------------|-------------------|------------|-----------------------------|------------------|-------------|---------------------------|--|
|       |     | Communi   | cation | Туре                                 |    |              |                   |            |                             |                  |             |                           |  |
|       |     | B: NB-loT |        | <b>C:</b> Cat-M1                     |    |              |                   |            |                             |                  |             |                           |  |
|       |     |           | Inte   | Interface Options                    |    |              |                   |            |                             |                  |             |                           |  |
|       |     |           | Ch     | <b>Ch 1:</b> I2C <b>A1</b> : I2C     |    |              |                   |            |                             |                  |             |                           |  |
|       |     |           | Ch     | Ch 2: Pulse B1: Pulse (R             |    |              |                   |            | (Reed Switch)               |                  |             |                           |  |
|       |     |           | Ch     | Ch 3: Analogue C1: mV or MV/V        |    |              |                   |            |                             |                  |             |                           |  |
|       |     |           | Ch     | Ch 4: Pt temperature                 |    |              | D1:Pt100 (2 wire) |            | <b>D2</b> : Pt1000 (2 wire) |                  | Others      |                           |  |
|       |     |           | Ch     | Ch 5: Digital                        |    | <b>E1</b> :R | S232              | E2         | :RS485                      | E3: SDI1         | 2           | E4: TTL UART              |  |
|       |     |           |        | or Analog                            | ue | E5: N        | Nodbus            | <b>E</b> 6 | : 4-20mA                    | <b>E7</b> : 0-5V |             | <b>E8</b> : 0-10V         |  |
|       |     |           | Oth    | Other customised options on request  |    |              |                   |            |                             |                  |             |                           |  |
|       |     |           |        | Electric Connection                  |    |              |                   |            |                             |                  |             |                           |  |
|       |     |           |        | P (pin connector) 3m (3m wire cable) |    |              |                   |            |                             |                  |             | vire cable)               |  |
|       |     |           |        | Others as specified                  |    |              |                   |            |                             |                  |             |                           |  |
|       |     |           |        | Enclosure                            |    |              |                   |            |                             |                  |             |                           |  |
|       |     |           |        |                                      |    |              |                   |            |                             | (only board)     |             |                           |  |
|       |     |           |        |                                      |    | Others       |                   |            |                             |                  |             |                           |  |
|       |     |           |        |                                      |    |              | Device Activation |            |                             |                  |             |                           |  |
|       |     |           |        |                                      |    |              |                   |            | S: on/of                    | ff switch        | <b>X:</b> N | o switch (always on)      |  |
|       |     |           |        |                                      |    |              |                   |            |                             | Ante             | nna         |                           |  |
|       |     |           |        |                                      |    |              |                   |            |                             | l: In            | ternal      | E: External               |  |
|       |     |           |        |                                      |    |              |                   |            |                             |                  | Opt         | ions                      |  |
|       |     |           |        |                                      |    |              |                   |            |                             |                  |             | (On request) <sup>1</sup> |  |
| RM1-  | NI  | В         | D      | 1D2E6                                | -  | D            | E                 |            | S                           |                  |             |                           |  |
|       | NI. | D         | В      | ID2E0                                |    |              | <b>C</b>          |            | 3                           |                  | 1           |                           |  |

#### Sample Product Code:

#### • RM1-N-B-B1D1E6-P-E-S-I

Multi-channel NB-IoT sensor interface with 3 x 4pin connection (1x pulse sensor, 1x 2-wire Pt100 temperature sensor and 1x 4-20mA sensor), with rectangular housing, activated by on-off switch and internal antenna.

#### <sup>1)</sup> Product Options:

- **G:** GPS tracker (only for E type enclosure)
- EP: sensor with external power supply connector for 12V supply (only for E type enclosure, adaptor is not included)
- EPB: connector for 12V supply with internal battery backup (only for E type enclosure)
- HG: high-gain external antenna
- **WF**: Active WiFi module on device for communication/ firmware update through Mobile phone NFC module (only for E type enclosure)
- HCB: high-capacity battery (only for E type enclosure)

All details are subject to change without prior notice © All Rights Reserved for Ellenex

Ver. 6.7-07/22

