


SPECIFICATIONS **CDTA56R2W**

OUTLINES DIMENSIONS



The technical drawings show the following dimensions:

- Top View:** Total width 37.60 mm, distance between chip centers $12.7 \times 2 = 25.40$ mm, total height 19.00 mm, chip height 6.38 mm, and chip width 4.65 mm. A PIN1 is indicated on the right side.
- Side View:** Total height 15.24 mm, mounting tab height 1.88 mm, and mounting tab width 4.0 ± 0.5 mm.
- Bottom View:** Mounting tab height 8.00 mm, tab width $\phi 0.50$, chip width $2.54 \times 5 = 12.70$ mm, and distance from chip center to tab edge 12.45 mm. The package contains a chip with a diameter of $\phi 1.70$ mm and a radius of $R1.00$ mm. Other dimensions include 8.10 mm, 1.35 mm, 8 mm, and 1.45 mm.

Additional markings on the bottom view include "PART NO.", "DATE", and "CODE".

Notes:



1. All Dimensions are in millimeters (inches).
2. Tolerance is ± 0.25 mm (0.01") unless otherwise noted.
3. Specifications are subject to change without notice.

Part Number	Chip Material	Color of Emission	Lens Type	Description
CDTA56R2W	InGaAlP	Red	White Segment	Common Anode



ChromeLED Corp. reserves the right to make changes at any time in order to supply the best product possible. The most current version of this document will always be available at: www.chromeled.com

TYPICAL INTERNAL EQUIVALENT CIRCUIT



ChromeLED Corp. reserves the right to make changes at any time in order to supply the best product possible. The most current version of this document will always be available at: www.chromeled.com

ABSOLUTE MAXIMUM RATINGS
(TA=25°C)

Parameter	Symbol	Max Rating	Unit
Power Dissipation	PD	70	mW
Pulse Forward Current	IFP	90	mA
Continuous Forward Current	IF	25	mA
Reverse Voltage Segment	VR	5	V
Operating Temperature Range	TOPR	-25~+85	°C
Storage Temperature Range	TSTG	-25~+85	°C
IFP = Pulse Width ≤ 10 ms, Duty Ratio ≤ 1/10. Soldering Condition: 260 °C/ 5sec			

OPTICAL-ELECTRICAL CHARACTERISTICS
(TA=25°C)

Parameter	Symbol	Test Condition	Value			Unit
			Min	Typ	Max	
Luminous Intensity	IV	IF = 20mA	-	30	-	mcd
Forward Voltage	VF	IF = 20mA	-	2.0	2.6	V
Reverse Leakage Current	IR	VR = 5V	-	-	10	μA
Peak Wavelength	λP	IF = 20mA	-	632	-	nm
Dominant Wavelength	λD	IF = 20mA	619	624	629	nm
Spectral Radiation Bandwidth	Δλ	IF = 20mA	-	20	-	nm



ChromeLED Corp. reserves the right to make changes at any time in order to supply the best product possible. The most current version of this document will always be available at: www.chromeled.com

OPTICAL CHARACTERISTIC CURVES

(25 °C Free Air Temperature Unless Otherwise Specified)




Fig.1 FORWARD CURRENT VS. FORWARD VOLTAGE




Fig.2 RELATIVE INTENSITY VS. FORWARD CURRENT




Fig.3 FORWARD VOLTAGE VS. TEMPERATURE




Fig.4 RELATIVE INTENSITY VS. TEMPERATURE




Fig.5 RELATIVE INTENSITY VS. WAVELENGTH





Fig.6 MAX. ALLOWABLE DC CURRENT VS. AMBIENT TEMPERATURE



ChromeLED Corp. reserves the right to make changes at any time in order to supply the best product possible. The most current version of this document will always be available at: www.chromeled.com

SOLDERING CONDITIONS – DISPLAY TYPE LED

● RECOMMEND SOLDERING PROFILE



● Note:

- Recommend pre-heat temperature of 105°C or less (as measured with a thermocouple attached to the LED pins) prior to immersion in the solder wave with a maximum solder bath temperature of 260°C
- Peak wave soldering temperature between 245°C ~ 225°C for 3 sec (5 sec max)
- No more than one wave soldering pass

● SOLDERING IRON

Basic spec is ≤ 4 sec when 260°C. If temperature is higher, time should be shorter (+10°C → 1 sec). Power dissipation of Iron should be smaller than 15W, and temperature should be controllable. Surface temperature of the device should be under 230°C.

● REWORK

Customer must finish rework within ≤ 3 sec under 350°C. The head of soldering iron cannot touch copper foil.



ChromeLED Corp. reserves the right to make changes at any time in order to supply the best product possible. The most current version of this document will always be available at: www.chromeled.com