


CT0603HPF Series

From 1.8nH to 390nH



SPECIFICATIONS

Please specify tolerance code when ordering.
CT0603HPF-4N3 ← H = ±3%, J = ±5%

Part Number	Inductance (nH)	L/Q Test Freq. (MHz)	Q Typ.	SRF Typ. (GHz)	DCR Max. (Ω)	Irms Max. (mA)	Available Tolerance
CT0603HPF-1N8J	1.8	250/250	23	16.0	0.033	2100	J
CT0603HPF-2N2J	2.2	250/250	13	15.0	0.182	900	J
CT0603HPF-3N9J	3.9	250/250	26	7.50	0.062	1600	J
CT0603HPF-4N3	4.3	250/250	26	7.50	0.088	1300	H, J
CT0603HPF-4N7	4.7	250/250	25	7.90	0.130	1100	H, J
CT0603HPF-6N8	6.8	250/250	40	5.80	0.065	1400	H, J
CT0603HPF-7N2	7.2	250/250	32	5.40	0.100	1400	H, J
CT0603HPF-7N5	7.5	250/250	32	5.30	0.100	1300	H, J
CT0603HPF-11N	11	250/250	41	4.10	0.086	1400	H, J
CT0603HPF-15N	15	250/250	42	3.60	0.110	1200	H, J
CT0603HPF-16N	16	250/250	40	3.50	0.125	1100	H, J
CT0603HPF-22N	22	250/250	40	3.15	0.195	850	H, J
CT0603HPF-23N	23	250/250	40	3.00	0.150	850	H, J
CT0603HPF-24N	24	250/250	42	2.95	0.125	1100	H, J
CT0603HPF-27N	27	250/250	42	2.80	0.200	780	H, J
CT0603HPF-30N	30	250/250	49	2.80	0.130	920	H, J
CT0603HPF-33N	33	250/250	45	2.70	0.170	680	H, J
CT0603HPF-36N	36	250/250	44	2.50	0.225	720	H, J
CT0603HPF-39N	39	250/250	48	2.45	0.190	680	H, J
CT0603HPF-43N	43	250/250	45	2.45	0.225	810	H, J
CT0603HPF-47N	47	200/250	43	2.30	0.240	680	H, J
CT0603HPF-51N	51	200/250	42	2.30	0.280	660	H, J
CT0603HPF-56N	56	200/250	43	2.20	0.300	610	H, J
CT0603HPF-68N	68	200/250	43	2.00	0.330	600	H, J
CT0603HPF-72N	72	150/250	37	1.90	0.420	550	H, J
CT0603HPF-75N	75	150/250	37	1.90	0.520	500	H, J
CT0603HPF-82N	82	150/250	38	1.80	0.460	510	H, J
CT0603HPF-91N	91	150/250	45	1.65	0.580	440	H, J
CT0603HPF-R10	100	150/250	49	1.70	0.540	470	H, J
CT0603HPF-R11	110	150/250	47	1.60	0.620	440	H, J
CT0603HPF-R12	120	150/250	47	1.55	0.720	420	H, J
CT0603HPF-R15	150	150/250	47	1.35	1.150	390	H, J
CT0603HPF-R18	180	100/250	48	1.30	1.500	310	H, J
CT0603HPF-R20	200	100/250	47	1.25	2.000	280	H, J
CT0603HPF-R21	210	100/250	48	1.20	2.000	280	H, J
CT0603HPF-R22	220	100/250	47	1.10	2.000	280	H, J
CT0603HPF-R25	250	100/250	45	1.05	3.000	240	H, J
CT0603HPF-R27	270	100/250	46	1.05	2.250	260	H, J
CT0603HPF-R30	300	100/250	47	0.99	2.800	220	H, J
CT0603HPF-R33	330	100/250	46	0.93	3.600	180	H, J
CT0603HPF-R36	360	100/250	47	0.93	4.000	170	H, J
CT0603HPF-R39	390	100/250	47	0.88	4.000	170	H, J

CHARACTERISTICS

Description: SMD ceramic core wire-wound chip inductor.

Applications: Cellular phone, cordless phone, remote control, security systems, wireless PDA, wireless LAN, mouse, keyboard, GPS receiver, set top box, base station, repeater, etc.

Operating Temperature: -40°C to +125°C (Including self - temperature rise)

Irms: For a 15°C temp. rise from 25°C ambient with current

Inductance Tolerance: ±3%, ±5%

Testing: Inductance and Q are tested on an HP4287A at specified frequency.

Packaging: Tape & Reel.


Miscellaneous: RoHS Compliant.

Additional Information: Additional electrical & physical information available upon request.

Samples available. See website for ordering information.

PHYSICAL DIMENSIONS

Size	A	B	C	D	E	F	G
				Ref.			
mm	1.6 ^{+0.2} _{-0.1}	1.00±0.1	0.82 ^{+0.2} _{-0.1}	0.30	0.70	0.30	0.95
inches	0.063 ^{+0.008} _{-0.004}	0.039±0.004	0.032 ^{+0.008} _{-0.004}	0.012	0.028	0.012	0.037



PAD LAYOUT

