



NOTES:

1. MATES WITH INDUSTRY STANDARD
2. WIRING POLARIZATION & SEQUENCE PER EIA 568B.
3. COMPATIBLE WITH SOLID AND STRANDED COPPER CONDUCTORS.
4. CONDUCTOR RANGES ARE 22-26AWG WITH A MAX OF 7 STRANDS PER CONDUCTOR BUNDLE. LIMITING O.D. IS 0.55"
5. CAN BE RETERMINATED UP TO 200 TIMES.
6. ASSEMBLY IS RoHS COMPLIANT

ITEM	QTY.	DESCRIPTION	MATERIAL	FINISH
8	2	STUFFER CAP (MPN #201-345)	THERMOPLASTIC	WHITE
7	1	PUNCHDOWN BLOCK (BROWN/GREEN)	THERMOPLASTIC	WHITE
6	1	PUNCHDOWN BLOCK (BLUE/ORANGE)	THERMOPLASTIC	WHITE
5	1	PCB	FR-4	BLUE
4	1	PANEL GASKET	NEOPRENE	BLACK
3	1	RJ-45 JACK W/PCB MTG	POLYESTER	BLACK
2	1	LOCK NUT	POLYESTER	BLACK
1	1	RECEPTACLE HOUSING	POYESTER	BLACK

ADDED CIRCUIT LYT. EC NO: MNA2009-0377 DRAWN BY: DRWINSTONE 2008/12/11 CHKD BY: WOODMAN APPR: J. MURPHY 2009/01/19	DESCRIPTION
REV	A1

QUALITY SYMBOLS	▽=0
▽=0	
GENERAL TOLERANCES (UNLESS SPECIFIED)	
	mm
	INCH
4 PLACES	± .005
3 PLACES	± .005
2 PLACES	± .01
1 PLACE	± .01
ANGULAR ± 2 °	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	

DIMENSION STYLE		SCALE	DESIGN UNITS
IN/MM		1:1	INCH
DRAWN BY	DATE	TITLE	
R. STONE	2008/08/26	PANEL MTG. RECEPTACLE	
CHECKED BY	DATE	RJ-45 PUNCHDOWN WITH	
B. WOODMAN	2008/08/28	100 OHM RESISTORS	
APPROVED BY	DATE	MATERIAL NO.	
J. MURPHY	2008/09/05	847020009	
DOCUMENT NO.		SHEET NO.	
SD-84702-017		1 OF 1	

THIRD ANGLE PROJECTION	
MOLEX INCORPORATED	
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	