

Sep. 1. 2023 Copyright 2023 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	Δ -40 °C TO 105 °C	STORAGE TEMPERATURE RANGE	-10 °C TO 50 °C (PACKED CONDITION)	
	VOLTAGE	50 V AC / DC	OPERATING OR STORAGE HUMIDITY RANGE	RELATIVE HUMIDITY 90 % MAX (NOT DEWED)	
	CURRENT	0.5 A (note 1)	APPLICABLE CABLE	t=0.3±0.05mm, GOLD PLATING	
SPECIFICATIONS					
ITEM	TEST METHOD		REQUIREMENTS	QT	AT
CONSTRUCTION					
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	x	x
MARKING	CONFIRMED VISUALLY.			x	x
ELECTRIC CHARACTERISTICS					
CONTACT RESISTANCE	1mA(DC OR 1000Hz).		50 mΩ MAX. INCLUDING FPC,FFC BULK RESISTANCE (L=8mm)	x	x
INSULATION RESISTANCE	100 V DC.		500 MΩ MIN.	x	x
VOLTAGE PROOF	150 V AC FOR 1 min.		NO FLASHOVER OR BREAKDOWN.	x	x
MECHANICAL CHARACTERISTICS					
MECHANICAL OPERATION	20 TIMES INSERTIONS AND EXTRACTIONS.		① CONTACT RESISTANCE: 50 mΩ MAX. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	—
VIBRATION	FREQUENCY 10 TO 55 Hz, HALF AMPLITUDE 0.75 mm, FOR 10 CYCLES IN 3 AXIAL DIRECTIONS.		① NO ELECTRICAL DISCONTINUITY OF 1 μs. ② CONTACT RESISTANCE: 50 mΩ MAX.	x	—
SHOCK	981 m/s ² , DURATION OF PULSE 6 ms AT 3 TIMES IN 3 BOTH AXIAL DIRECTIONS.		③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	—
FPC RETENTION FORCE	MEASURED BY APPLICABLE FPC. (CONNECTOR,FPC AT INITIAL CONDITION. THICKNESS OF FPC SHALL BE t=0.30mm)		DIRECTION OF INSERTION: 0.4xn N MIN (n : NUMBER OF CONTACTS).	x	—
ENVIRONMENTAL CHARACTERISTICS					
Δ RAPID CHANGE OF TEMPERATURE	TEMPERATURE -40→+15T ₀ +35→+105→+15T ₀ +35°C TIME 30→ 2 TO 3 → 30→ 2 TO 3 min. UNDER 5 CYCLES.		① CONTACT RESISTANCE: 50 mΩ MAX. ② INSULATION RESISTANCE: 50 MΩ MIN. ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	—
DAMP HEAT (STEADY STATE)	EXPOSED AT 40±2 °C, RELATIVE HUMIDITY 90 TO 95 %, 96 h.			x	—
DAMP HEAT,CYCLIC	EXPOSED AT -10 TO +65 °C, RELATIVE HUMIDITY 90 TO 96 %, 10 CYCLES,TOTAL 240 h.		① CONTACT RESISTANCE: 50 mΩ MAX. ② INSULATION RESISTANCE: 1 MΩ MIN. (AT HIGH HUMIDITY) ③ INSULATION RESISTANCE: 50 MΩ MIN. (AT DRY) ④ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	—
Δ DRY HEAT	EXPOSED AT 105±2 °C, 96 h.		① CONTACT RESISTANCE: 50 mΩ MAX.	x	—
COLD	EXPOSED AT -40±3°C, 96 h.		② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	x	—
CORROSION SALT MIST	EXPOSED AT 35±2 °C 5% SALT WATER SPRAY FOR 96 h.		① CONTACT RESISTANCE: 50 mΩ MAX. ② NO EVIDENCE OF CORROSION WHICH AFFECTS TO OPERATION OF CONNECTOR.	x	—
SULPHUR DIOXIDE [JIS C 60068-2-42]	EXPOSED AT 40±2 °C , RELATIVE HUMIDITY 80±5% , 25±5 ppm FOR 96 h.			x	—
HYDROGEN SULPHIDE [JIS C 60068-2-43]	EXPOSED AT 40±2 °C , RELATIVE HUMIDITY 80±5% , 10 TO 15 ppm FOR 96 h.			x	—
COUNT	DESCRIPTION OF REVISIONS		DESIGNED	CHECKED	DATE
Δ 4	DIS-F-00000491		SG. MASAKI	HS. SAKAMOTO	15. 07. 25
REMARK				APPROVED	MO. ISHIDA 12. 11. 08
Δ				CHECKED	HS. SAKAMOTO 12. 11. 08
Unless otherwise specified, refer to IEC 60512.				DESIGNED	SG. MASAKI 12. 11. 08
				DRAWN	SS. NABAE 12. 11. 08
Note	QT:Qualification Test AT:Assurance Test X:Applicable Test		DRAWING NO.	ELC4-347552-01	
HRS	SPECIFICATION SHEET		PART NO.	FH52E-**S-0. 5SH	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL580	Δ 1/2

Sep. 1. 2023 Copyright 2023 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

SPECIFICATIONS

ITEM	TEST METHOD	REQUIREMENTS	QT	AT
RESISTANCE TO SOLDERING HEAT	1) REFLOW SOLDERING (TO BE 2 TIMES MAX.) PEAK TMP. 250 °C MAX REFLOW TMP. OVER 230 °C WITHIN 60 sec. PRE-HEATING. 150 TO 200°C 90 TO 120 sec. 2) SOLDERING IRONS : 350 ± 10 °C, FOR 5 ± 1 sec .	NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.	X	—
SOLDERABILITY	SOLDERED AT SOLDER TEMPERATURE, 245±3 °C FOR IMMERSION DURATION, 3±0.3 sec.	A NEW UNIFORM COATING OF SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMersed.	X	—

(note 1)

WHEN THE SAME VALUE OF CURRENT ARE APPLIED TO ALL CONTACTS AT THE SAME TIME IN ONCE, SET THE CURRENT TO THE 70 % OF THE RATED CURRENT VALUE.

Note QT:Qualification Test AT:Assurance Test X:Applicable Test		DRAWING NO.		ELC4-347552-01	
HRS	SPECIFICATION SHEET		PART NO.	FH52E-**S-0. 5SH	
	HIROSE ELECTRIC CO., LTD.		CODE NO	CL580	△ 2/2