



PCB Layout(Top View)

N = Number of poles  $\Delta$   
 Dim A =  $N \times 6.35 + 1.00$   
 Dim B =  $(N - 1) \times 6.35$

Poles	Tol.	Dim A & B
2-5p		$\pm 0.20$
6-10p		$\pm 0.25$
11-16p		$\pm 0.35$
17-24p		$\pm 0.40$
25-30p		$\pm 0.50$

SIGN	DATE	DESCRIPTION	APPROVER
$\Delta$	10/20'08	Add APPROVAL: : CQC	Kind
$\Delta$	12/05'12	Change the screw plating specification	Jacky
$\Delta$	12/05'12	Change the dimensional tolerance	Jacky
$\Delta$	12/12'13	Add the view	Jacky
$\Delta$	12/12'13	Change the withatand voltage and current	Jacky

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

MATERIALS ELECTRICAL: cULus CQC  
 RATED VOLTAGE & CURRENT: 250 V, 10 A / 250 V, 9 A  $\Delta 5$   
 WITHSTAND VOLTAGE: AC 2000 V/Min  
 INSULATION RESISTANCE: 1000 M $\Omega$  OR MORE AT DC 500 V  
 OPERATING TEMPERATURE RANG: -40  $^{\circ}$ C ~ +115  $^{\circ}$ C  
 SCREW TORQUE VALUE: 5.3 Lb-In.  
 WIRE RANGE: 22 - 18 AWG  
 1) MOLDED PARTS: Thermoplastic, UL 94 V-0 BLACK  
 2) TERMINAL: BRASS, 0.8t, Tin PLATED  
 3) TERMINAL SCREWS: STEEL, M3  
 APPROVAL:  $\Delta$   
 PART NO.:  
 Critical dimension:  $\nabla$

YK 222 xx 0 x x 00G

NO. OF POLES  
 02: 2 POLES  
 03: 3 POLES  
 04: 4 POLES

30: 30 POLES

G: RoHS compliant (lead<4%) In copper Alloy  
 MARK  
 0: "@" MARK  
 1: "ANY" MARK  
 TERMINAL & SCREW PLATED  
 0: TERMINAL & SCREW: G/F  
 $\Delta$  1: TERMINAL: G/F, SCREW: Zinc  
 2: TERMINAL: Sn, SCREW: G/F  
 $\Delta$  3: TERMINAL: Sn, SCREW: Zinc

<b>ANYTEK</b>				<b>CUSTOMER COPY</b>			
ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD							
TITLE		YK-222 Series		DWG NO.		8YK001-222	
PART NO.		YK222xx0xx00G		CUST NO.			
APPROVED		DESIGNED		DRAWN		Tolerance	
		Jacky 2013.12.12		Jacky 2013.12.12		X. $\pm 0.50$	
						X.X $\pm 0.30$	
						X.XX $\pm 0.10$	
						X $^{\circ}$ $\pm 1^{\circ}$	
				SHEET: 01/01		REV.: G	