

TITLE

698~4000MHZ FLEXIBLE ANTENNA

TABLE OF CONTENTS

- 1. SCOPE
- 2. PRODUCT DESCRIPTION
- 3. APPLICABLE DOCUMENTS
- 4. GENERAL SPECIFICATION
- 5. ANTENNA SPECIFICATION
- 6. MECHANICAL SPECIFICATION
- 7. ENVIRONMENTAL SPECIFICATION
- 8. PACKING
- 9. OTHER MOLEX ANTENNA PRODUCTS
- 10. CHANGE HISTORY

PS-2091420180		Kang Cheng	Horace Ma		on Hung
DOCUMENT NUMBER:		CREATED / REVISED BY:	CHECKED BY:	APPR	OVED BY:
C	DATE: 2022/12/12	Pro	1 of 8		
	EC No: 731790	698~4000MHz Flexible Antenna			
REVISION:	LECR/ECN INFORMATION:	TITLE:			SHEET No.



698~4000MHz FLEXIBLE ANTENNA

1.0 SCOPE

This Product Specification covers the mechanical, electrical and environmental performances specification for 698~4000MHz Flexible Antenna.

2.0 PRODUCT DESCRIPTION

2.1 PRODUCT NAME AND SERIES NUMBER (S)

Product name: 698~4000MHz Flexible Antenna

Series Number: 209142

2.2 DESCRIPTION

209142 is monopole flexible antenna for 4G full LTE bands in the spectrum of 698~ 4000 MHz, also optimally covers 2G and 3G. Antenna 85x14.5x0.1mm is made from flexible polymer material, cable standard length 180mm. It can be easily installed by simply "peel and stick" on non-metal surface.

2.3 FEATURES

- 698~4000MHz, Linear polarization
- Antenna size 85x14.5x0.1mm
- MHF & U.FL compatible connector
- Cable Ø1.13mm, standard length options for 180 mm
- Cable and connector can be customized
- RoHS Compliant



REVISION:	ECR/ECN INFORMATION: EC No: 731790	698~4000MHz Flexible Antenna			SHEET No.
C	DATE: 2022/12/12	Pro	2 of 8		
DOCUMENT NUMBER:		CREATED / REVISED BY:	CHECKED BY:	APPR	OVED BY:
PS-2091420180		Kang Cheng	Horace Ma	Bens	on Hung



2.4 PRODUCT STRUCTURE INFORMATION PRINT MARK(COLOR WHITE) L2 ±2.00 85.00 698MHz~4000MHz 209142 L1 ±2.00 VERTICAL DIRECTION MAX 2.0 WITH SOLDER PASTE -(INCLUDE FLEX) RELEASE PAPER CUTLINE FOR LINER SOLDER MASK PATTERN ADHESIVE(3M9077 50um) RELEASE PAPER CONNECTOR FLEX LAYER

NOTES:

1, MATERIAL:FLEX SIZE:85*14,5mm

PS-2091420180

CABLE:Ø1,13 mm

CONNECTOR:OD1,13 RF 2,5H MHF-13-N-01 PLUG GOLD PLATED (MHF & U.FL COMPATIBLE)

2. SOLDER MASK:BLACK.

3. FOR PULL TEST, CAN NOT LIFT UP IN THE VERTICAL DIRECTION.

4. THE CONNECTOR WILL BE PROTECTED WITH A CAP.

ITEM	MATERIAL NO.	"L1"-LENGTH	"L2"-LENGTH
1	2091420180	173 mm	180 mm

REVISION:	ECR/ECN INFORMATION: EC No: 731790 DATE: 2022/12/12		00MHz Flexible And oduct Specification		3 of 8
DOCUMENT NUMBER:		CREATED / REVISED BY:	CHECKED BY:	APPRO	OVED BY:

Kang Cheng

race Ma Benson Hung



3.0 APPLICABLE DOCUMENTS

Document	Number	Description
Sale Drawing(SD) SD-2091420180 Mechanical Dimension of the product		Mechanical Dimension of the product
Application Guide(AS)	Application Guide(AS) AS-2091420180 Antenna Application and surrounding	
Packing Drawing(PK) PK-2091420180 Product packaging specifications		Product packaging specifications

4.0 GENERAL SPECIFICATION

Product name	698~4000 MHz Flexible Antenna			
Part number		2091420180		
Frequency	698-960 MHz 1710-2690 MHz 3300-3800 MHz			
Polarization		Linear		
Operating temperature		-40°C to 85°C		
Storage temperature	-40°C to 85°C			
RF Power	2 Watts			
Impedance with matching	50 Ohms			
Antenna type		Flex		
Connector type	U.	FL & MHF compatib	le	
User Implementation type		Adhesive 3M 9077		
Cable diameter	Ø1.13mm			
Single weight	1.164 g (P/N For 2091420180)			
Cable length	180 mm (P/N for 2091420180)			

Adhesive Application

Bond strength is dependent upon the amount of adhesive-to-surface contact developed. Firm application pressure helps develop better adhesive contact and improves bond strength.

To obtain optimum adhesion, the bonding surfaces must be clean, dry, and well unified. Some typical surface cleaning solvents are isopropyl alcohol/water mixture or heptane.

Ideal tape application temperature range is 70°F to 100°F (21°C to 38°C). Initial tape application to surfaces at temperatures below 50°F (10°C) is not recommended because the adhesive becomes too firm to adhere readily. However, once properly applied, low temperature holding is generally satisfactory.

C REVISION:	ECR/ECN INFORMATION: EC No: 731790 DATE: 2022/12/12	698~4000MHz Flexible Antenna Product Specification		4 of 8	
DOCUMENT NUMBER:		CREATED / REVISED BY:	CHECKED BY:	APPR(OVED BY:
PS-2091420180		Kang Cheng	Horace Ma	Bens	on Hung



5.0 ANTENNA SPECIFICATION.

5.1 ELECTRICAL REQUIREMENT

5.1.1 ELECTRICAL REQUIREMENTS FOR CABLE LENGHTH 180mm						
P/N 2091420180						
Frequency Range	e 698-960MHz 1710-2690MHz 3300-3800MHz					
Peak Gain(Max)	1.2dBi 5.2dBi 2.7dBi					
Average Total efficiency	>45% >55% >55%					
Return Loss	< -10 dB	< -5 dB	< -5 dB			

Note that the above antenna performance is measured with just the antenna mounted on a PC/ABS block to similar a free-space condition. When implement into the system, the frequency resonant might be off-tune due to the loading of surrounding components especially metal plane. This off-tune can be compensated through matching. Although module manufacturers specify a peak gain limit, it is based on free-space conditions. The peak gain will be degraded by 1 to 2dBi in the actual implementation as the radiation pattern will change due to the surround components. As such, during selection of antenna, you can select one with high peak gain to compensate for the loss. Molex can offer assistant to choose the best location and best tuning in-order to meet this peak gain requirement.

6.0 MECHANICAL SPECIFICATION

DESCRIPTION	TEST CONDITION	TEST RESULT
Pull Test	 Test machine: Max intelligent load tester Stick the flex antenna on a plastic board, pull cable in axial direction. 	Pull force >8N
Un-mating force (connector)	Solder the receptacle connector to the test board ,then place the board and plug on push-on/pull-off machine, and repeat mating and un-mating 30 cycles at a speed 25±3mm/min. along the mating axis.	Un-mating force : 0.5 kgf min

C	EC No: 731790 DATE: 2022/12/12	698~4000MHz Flexible Antenna Product Specification		5 of 8	
DOCUMENT NUMBER:		CREATED / REVISED BY:	CHECKED BY:	APPR(OVED BY:
PS-2091420180		Kang Cheng	Horace Ma	Bens	on Hung




7.0 ENVIRONMENTAL SPECIFICATION

DESCRIPTION	SPECIFICATION
	1.The device under test is kept for 30 mins in an environment with a temperature of -40 ℃.
	2. Kept for 4 Hours in an environment with a temperature of 85 degrees and a relative humidity of 95%.
Tarana aratura (I bassidita Caslia a	3. Kept for 2 Hours in an environment with a temperature of 125 degrees and a relative humidity of 95%.
Temperature /Humidity Cycling	4. The cycle is repeated until a total of 40 cycles have been completed. Hereafter the conditions are stabilized at room temperature. Transfer temperature 8°C per min.
	5. Parts should meet RF spec before and after test.
	No cosmetic problem (No soldering problem; No adhesion problem of glue.)
Temperature Shock	 1.The device under test at -40 °C⇔125 °C by 100 cycles, Dwell of 30 mins, transition time between Dwell 30 secs (~ 61 mins / cycle) and each item should be measured after exposing them in normal temperature and humidity for 24 h. 2. Parts should meet RF spec before and after test. 3. No cosmetic problem (No soldering problem; No adhesion
	problem of glue). 1.Temperature:125°C, time:1008 hours
High Temperature	2.There is no substantial obstruction to air flow across and around the samples, and the samples are not touching each other
	3. Parts should meet RF spec before and after test.
	4. No cosmetic problem (No soldering problem; No adhesion problem of glue) .
Salt Mist Test	The device under test is exposed to a spray of a 5% (by volume) resolution of NACL in water for 2 hours. Thereafter the device under test is left for 1 week in room temperature at a relative humidity of 95%. The cycle is repeated until a total of 2 cycles have been completed. Here after the conditions are stabilized at room temperature.
	2. Parts should meet RF spec before and after test.
	3. No visible corrosion. Discoloration accept.

REVISION:	ECR/ECN INFORMATION: EC No: 731790 DATE: 2022/12/12	698~4000MHz Flexible Antenna Product Specification		SHEET No. 6 of 8	
DOCUMENT NUMBER: PS-2091420180		CREATED / REVISED BY: Kang Cheng	CHECKED BY: Horace Ma	-	OVED BY: on Hung





C DATE: 2022/12/12 698~4000MHz Flexible Antenna Product Specification 7 of 8

DOCUMENT NUMBER: CREATED / REVISED BY: CHECKED BY: APPROVED BY: PS-2091420180 Kang Cheng Horace Ma Benson Hung



9.0 OTHER MOLEX ANTENNA PRODUCTS

Please refer to the Antenna products in Molex home page to view all the Molex Antenna products.

https://www.molex.com Molex, LLC 2222 Wellington Court Lisle, IL 60532 USA

10.0 CHANGE HISTORY

REV	DATA	DESCRIPTION	
В	2019/03/18	Update general specification description	
С	2022/12/12	Add 9.0 other molex antenna products	

REVISION:	ECR/ECN INFORMATION: EC No: 731790 DATE: 2022/12/12	698~4000MHz Flexible Antenna Product Specification			SHEET No. 8 of 8
DOCUMENT NUMBER:		CREATED / REVISED BY:	CHECKED BY:	APPROVED BY:	
PS-2091420180		Kang Cheng	Horace Ma	Benson Hung	