

### MLFB-Ordering data

6SL3220-3YE48-0UF0



Client order no.: Order no. :

Offer no. : Remarks:

Item no.: Consignment no. : Project:

nemarks.		
Rated data		
Input		
Number of phases	3 AC	
Line voltage	380 480 V +10 % -20 %	
Line frequency	47 63 Hz	

Line voltage	380 480 V +10 % -20 %	
Line frequency	47 63 Hz	
Rated voltage	400V IEC	480V NEC
Rated current (LO)	247.00 A	232.00 A
Rated current (HO)	218.00 A	191.00 A

## 0

Output		
Number of phases	3 AC	
Rated voltage	400V IEC	480V NEC
Rated power (LO)	132.00 kW	200.00 hp
Rated power (HO)	110.00 kW	125.00 hp
Rated current (LO)	250.00 A	240.00 A
Rated current (HO)	205.00 A	180.00 A
Rated current (IN)	256.00 A	
Max. output current	338.00 A	
Pulse frequency	2 kHz	
Output frequency for vector control	0 200 Hz	
Output frequency for V/f control	0 550 Hz	

# General tech. specifications

concrat teem speemeations		
Power factor λ	0.90 0.95	
Offset factor cos φ	0.99	
Efficiency η	0.98	
Sound pressure level (1m)	72 dB	
Power loss	2.350 kW	
Filter class (integrated)	Unfiltered	
EMC category (with accessories)	without	

#### **Ambient conditions**

Standard board coating type	Class 3C2, according to IEC 60721-3-3: 2002

#### Cooling Air cooling using an integrated fan

Cooling air requirement	0.153 m <sup>3</sup> /s (5.403 ft <sup>3</sup> /s)

#### Installation altitude 1000 m (3280.84 ft)

#### **Ambient temperature**

Operation	-20 45 °C (-4 113 °F)
Transport	-40 70 °C (-40 158 °F)
Storage	-25 55°C (-13 131°F)

#### **Relative humidity**

	95 % At 40 °C (104 °F), condensation
Max. operation	and icing not permissible

#### Overload capability

#### Low Overload (LO)

110% base load current IL for 60 s in a 300 s cycle time

#### High Overload (HO)

150% x base load current IH for 60 s within a 600 s cycle time



### **MLFB-Ordering data**

#### 6SL3220-3YE48-0UF0



Mechanical data		Closed-loop control techniques		
Degree of protection	IP20 / UL open type			
Size	FSF	V/f linear / square-law / parameterizable Yes		
Net weight	67 kg (147.71 lb)	V/f with flux current control (FCC) Yes		
Width	305 mm (12.01 in)	V/f ECO linear / square-law	Yes	
Height	709 mm (27.91 in)	Sensorless vector control	Yes	
Depth	369 mm (14.53 in)	Vector control, with sensor	No	
Inputs / out		Encoderless torque control	Yes	
Standard digital inputs	<i>p</i> a to	Torque control, with encoder	No	
Number	6	rorque control, with encouer	INO	
Switching level: 0→1	11 V	Commu	nication	
Switching level: 1→0	5 V	Communication	PROFINET, EtherNet/IP	
Max. inrush current		Connections		
Fail-safe digital inputs	15 mA	Signal cable		
Number	1	Conductor cross-section	0.15 1.50 mm <sup>2</sup>	
Digital outputs	'	Line side	(AWG 24 AWG 16)	
			M10	
Number as relay changeover contact	2	Version	M10 screw	
Output (resistive load)	DC 30 V, 5.0 A	Conductor cross-section	35.00 120.00 mm <sup>2</sup> (AWG 1 AWG 4/0)	
Number as transistor	0	Motor end		
Analog / digital inputs		Version	M10 screw	
Number	2 (Differential input)	Conductor cross-section	35.00 120.00 mm <sup>2</sup>	
Resolution	10 bit		(AWG 1 AWG 4/0)	
Switching threshold as digital inp	nut	DC link (for braking resistor)		
		PE connection	M10 screw	
0→1	4 V	Max. motor cable length		
1→0	1.6 V	Shielded	300 m (984.25 ft)	
Analog outputs		Unshielded	450 m (1476.38 ft)	
Number	1 (Non-isolated output)			
PTC/ KTY interface				
1 motor temperature sensor input, sensor and Thermo-Click, accuracy ±5 °C	rs that can be connected: PTC, KTY			

Page 2 of 3



#### MLFB-Ordering data

#### 6SL3220-3YE48-0UF0



Converter losses to EN 50598-2*				
Efficion	ncy class		IE2	
	•	/00% /	IEZ	Complianc
100%)	arison with the referen	ce converter (90% /	-43.80 %	
1.	<b>↑</b>			o= !!
100% -	2008.3 W (1.16 %)	2415.5 W (1.39 %)	3104.8 W (1.79 %)	CE marking
100%				
50% -	1051.9 W (0.61 %)	1201.6 W (0.69 %)	1423.5 W (0.82 %)	
	744 6 W (0 43 %)	808 W (0 47 %)		

90%

**Standards** 

ce with standards

UL, cUL, CE, C-Tick (RCM), EAC, KCC, SEMI F47, REACH

ηg

EMC Directive 2004/108/EC, Low-Voltage Directive 2006/95/EC

The percentage values show the losses in relation to the rated apparent power of the converter.

50%

The diagram shows the losses for the points (as per standard EN 50598) of the relative torque generating current (I) over the relative motor stator frequency(f). The values are valid for the basic version of the converter without options/components.

## Operator panel: Intelligent Operator Panel (IOP-2)

S	Screen	Ambie	ent conditions
Display design	LCD colors	Ambient temperature durin	g
		Operation	0 50 °C (32 122 °F)
Screen resolution	320 x 240 Pixel		55 °C only with door mounting kit
Mech	anical data	Storage	-40 70 °C (-40 158 °F)
Degree of protection	IP55 / UL type 12	Transport	-40 70 °C (-40 158 °F)
Net weight	0.13 kg (0.30 lb)	Relative humidity at 25°C di	uring
Width	70.0 mm (2.76 in)	Max. operation	95 %
Height	106.85 mm (4.21 in)		
Depth	19.65 mm (0.77 in)	P	Approvals
<b>r</b>	(6177 1117)	Certificate of suitability	CE, cULus, EAC, KCC, RCM

<sup>\*</sup>converted values