SIEMENS

Data sheet

3RW5214-1TC15



SIRIUS soft starter 200-600 V 18 A, 110-250 V AC Screw terminals Thermistor input

product brand name	SIRIUS		
product category	Hybrid switching devices		
product designation	Soft starter		
product type designation	3RW52		
manufacturer's article number			
 of standard HMI module usable 	<u>3RW5980-0HS00</u>		
 of high feature HMI module usable 	<u>3RW5980-0HF00</u>		
 of communication module PROFINET standard usable 	<u>3RW5980-0CS00</u>		
 of communication module PROFIBUS usable 	<u>3RW5980-0CP00</u>		
 of communication module Modbus TCP usable 	<u>3RW5980-0CT00</u>		
 of communication module Modbus RTU usable 	<u>3RW5980-0CR00</u>		
 of communication module Ethernet/IP 	<u>3RW5980-0CE00</u>		
 of circuit breaker usable at 400 V 	3RV2032-4DA10; Type of coordination 1, Iq = 65 kA, CLASS 10		
 of circuit breaker usable at 500 V 	3RV2032-4DA10; Type of coordination 1, Iq = 15 kA, CLASS 10		
 of circuit breaker usable at 400 V at inside-delta circuit 	3RV2032-4EA10; Type of coordination 1, Iq = 65 kA, CLASS 10		
 of circuit breaker usable at 500 V at inside-delta circuit 	3RV2032-4EA10; Type of coordination 1, Iq = 15 kA, CLASS 10		
 of the gG fuse usable up to 690 V 	3NA3820-6; Type of coordination 1, Iq = 65 kA		
 of the gG fuse usable at inside-delta circuit up to 500 V 	<u>3NA3820-6; Type of coordination 1, Iq = 65 kA</u>		
 of full range R fuse link for semiconductor protection usable up to 690 V 	<u>3NE1802-0: Type of coordination 2. Iq = 65 kA</u>		
 of back-up R fuse link for semiconductor protection usable up to 690 V 	<u>3NE8020-1; Type of coordination 2, Iq = 65 kA</u>		
General technical data			
starting voltage [%]	30 100 %		
stopping voltage [%]	50 %; non-adjustable		
start-up ramp time of soft starter	0 20 s		
current limiting value [%] adjustable	130 700 %		
certificate of suitability			
CE marking	Yes		
UL approval	Yes		
CSA approval	Yes		
product component			
HMI-High Feature	No		
 is supported HMI-Standard 	Yes		
 is supported HMI-High Feature 	Yes		
product feature integrated bypass contact system	Yes		
number of controlled phases	3		

trip class	CLASS 10A (default) / 10E / 20E; acc. to IEC 60947-4-2
buffering time in the event of power failure	
for main current circuit	100 ms
for control circuit	100 ms
insulation voltage rated value	600 V
degree of pollution	3, acc. to IEC 60947-4-2
impulse voltage rated value	6 kV
blocking voltage of the thyristor maximum	1 600 V
service factor	1
surge voltage resistance rated value	6 kV
maximum permissible voltage for safe isolation	
 between main and auxiliary circuit 	600 V
shock resistance	15 g / 11 ms, from 12 g / 11 ms with potential contact lifting
vibration resistance	15 mm to 6 Hz; 2g to 500 Hz
utilization category according to IEC 60947-4-2	AC 53a
reference code according to IEC 81346-2	Q
Substance Prohibitance (Date)	02/15/2018
product function	
 ramp-up (soft starting) 	Yes
• ramp-down (soft stop)	Yes
Soft Torque	Yes
adjustable current limitation	Yes
• pump ramp down	Yes
intrinsic device protection	Yes
motor overload protection	Yes; Full motor protection (thermistor motor protection and electronic
	motor overload protection)
 evaluation of thermistor motor protection 	Yes; Type A PTC or Klixon / Thermoclick
• inside-delta circuit	Yes
● auto-RESET	Yes
manual RESET	Yes
remote reset	Yes; By turning off the control supply voltage
 communication function 	Yes
 operating measured value display 	Yes; Only in conjunction with special accessories
• error logbook	Yes; Only in conjunction with special accessories
via software parameterizable	No
via software configurable	Yes
PROFlenergy	Yes; in connection with the PROFINET Standard communication
(internetionally)	module
 firmware update 	Yes
 removable terminal for control circuit 	Yes
torque control	No
● analog output	No
Power Electronics	
operational current	
at 40 °C rated value	18 A
• at 50 °C rated value	16 A
at 50 °C rated value	14 A
operational current at inside-delta circuit	
at 40 °C rated value	31.5 A
at 50 °C rated value	28 A
at 50 °C rated value at 60 °C rated value	23.9 A
operating voltage	20.0 M
rated value	200 600 V
 rated value at inside-delta circuit rated value 	200 600 V
	-15 %
relative negative tolerance of the operating voltage	
relative positive tolerance of the operating voltage	10 %
relative negative tolerance of the operating voltage at inside-delta circuit	-15 %
relative positive tolerance of the operating voltage at	10 %
inside-delta circuit	
operating power for 3-phase motors	
i i on i i primeri i i i primeri i i i o primeri i i o primeri i o primeri i o primeri i o primeri o primeri o	

• at 230 V at 40 °C rated value	4 kW			
 at 230 V at inside-delta circuit at 40 °C rated value 	7.5 kW			
 at 400 V at 40 °C rated value 	7.5 kW			
 at 400 V at inside-delta circuit at 40 °C rated value 	15 kW			
 at 500 V at 40 °C rated value 	11 kW			
 at 500 V at inside-delta circuit at 40 °C rated value 	18.5 kW			
Operating frequency 1 rated value	50 Hz			
Operating frequency 2 rated value	60 Hz			
relative negative tolerance of the operating frequency	-10 %			
relative positive tolerance of the operating frequency	10 %			
adjustable motor current				
 at rotary coding switch on switch position 1 	7.5 A			
at rotary coding switch on switch position 2	8.2 A			
at rotary coding switch on switch position 3	8.9 A 9.6 A			
 at rotary coding switch on switch position 4 				
at rotary coding switch on switch position 5	10.3 A			
• at rotary coding switch on switch position 6	11 A			
 at rotary coding switch on switch position 7 	11.7 A			
 at rotary coding switch on switch position 8 	12.4 A			
 at rotary coding switch on switch position 9 	13.1 A			
 at rotary coding switch on switch position 10 	13.8 A			
 at rotary coding switch on switch position 11 	14.5 A			
 at rotary coding switch on switch position 12 	15.2 A			
 at rotary coding switch on switch position 13 	15.9 A			
 at rotary coding switch on switch position 14 	16.6 A			
 at rotary coding switch on switch position 15 	17.3 A			
 at rotary coding switch on switch position 16 	18 A			
• minimum	7.5 A			
adjustable motor current				
 for inside-delta circuit at rotary coding switch on switch position 1 	13 A			
 for inside-delta circuit at rotary coding switch on switch position 2 	14.2 A			
 for inside-delta circuit at rotary coding switch on switch position 3 	15.4 A			
 for inside-delta circuit at rotary coding switch on switch position 4 	16.6 A			
 for inside-delta circuit at rotary coding switch on switch position 5 	17.8 A			
 for inside-delta circuit at rotary coding switch on switch position 6 	19.1 A			
 for inside-delta circuit at rotary coding switch on switch position 7 	20.3 A			
 for inside-delta circuit at rotary coding switch on switch position 8 	21.5 A			
 for inside-delta circuit at rotary coding switch on switch position 9 	22.7 A			
 for inside-delta circuit at rotary coding switch on switch position 10 	23.9 A			
 for inside-delta circuit at rotary coding switch on switch position 11 	25.1 A			
 for inside-delta circuit at rotary coding switch on switch position 12 	26.3 A			
 for inside-delta circuit at rotary coding switch on switch position 13 	27.5 A			
 for inside-delta circuit at rotary coding switch on switch position 14 	28.8 A			
 for inside-delta circuit at rotary coding switch on switch position 15 	30 A			
 for inside-delta circuit at rotary coding switch on switch position 16 	31.2 A			
at inside-delta circuit minimum	13 A			
minimum load [%]	15 %; Relative to smallest settable le			
power loss [W] for rated value of the current at AC				

• at 40 °C after startup	17 W			
• at 50 °C after startup	17 W			
• at 60 °C after startup	16 W			
power loss [W] at AC at current limitation 350 %				
 at 40 °C during startup 	276 W			
 at 50 °C during startup 	241 W			
• at 60 °C during startup	200 W			
Control circuit/ Control				
type of voltage of the control supply voltage	AC			
control supply voltage at AC				
• at 50 Hz	110 250 V			
• at 60 Hz	110 250 V			
relative negative tolerance of the control supply	-15 %			
voltage at AC at 50 Hz	40.0/			
relative positive tolerance of the control supply voltage at AC at 50 Hz	10 %			
relative negative tolerance of the control supply voltage at AC at 60 Hz	-15 %			
relative positive tolerance of the control supply voltage at AC at 60 Hz	10 %			
control supply voltage frequency	50 60 Hz			
relative negative tolerance of the control supply voltage frequency	-10 %			
relative positive tolerance of the control supply voltage frequency	10 %			
control supply current in standby mode rated value	30 mA			
holding current in bypass operation rated value	75 mA			
locked-rotor current at close of bypass contact maximum	0.17 A			
inrush current peak at application of control supply voltage maximum	12.2 A			
duration of inrush current peak at application of control supply voltage	2.2 ms			
design of the overvoltage protection	Varistor			
design of short-circuit protection for control circuit	4 A gG fuse (Icu=1 kA), 6 A quick-acting fuse (Icu=1 kA), C1 miniature circuit breaker (Icu= 600 A), C6 miniature circuit breaker (Icu= 300 A); Is not part of scope of supply			
Inputs/ Outputs				
number of digital inputs	1			
number of digital outputs	3			
not parameterizable	2			
digital output version	2 normally-open contacts (NO) / 1 changeover contact (CO)			
number of analog outputs	0			
switching capacity current of the relay outputs				
at AC-15 at 250 V rated value	3 A			
 at DC-13 at 24 V rated value 	1 A			
Installation/ mounting/ dimensions				
mounting position	+/- 10° rotation possible and can be tilted forward or backward on vertical mounting surface			
fastening method	screw fixing			
height	275 mm			
width	170 mm			
depth	152 mm			
required spacing with side-by-side mounting				
• forwards	10 mm			
backwards	0 mm			
• upwards	100 mm			
downwards	75 mm			
• at the side	5 mm			
weight without packaging	2.1 kg			
Connections/ Terminals				
type of electrical connection				
*1				

for main current circuit	screw-type terminals			
for control circuit	screw-type terminals			
wire length for thermistor connection				
 with conductor cross-section = 0.5 mm² maximum 	50 m			
 with conductor cross-section = 1.5 mm² maximum 	150 m			
 with conductor cross-section = 2.5 mm² maximum 	250 m			
type of connectable conductor cross-sections				
 for main contacts 				
— solid	2x (1.0 2.5 mm²), 2x (2.5 10 mm²)			
 finely stranded with core end processing 	2x (1.0 2.5 mm ²), 2x (2.5 6.0 mm ²)			
 at AWG cables for main current circuit solid 	2x (16 12), 2x (14 8)			
type of connectable conductor cross-sections				
 for control circuit solid 	1x (0.5 4.0 mm²), 2x (0.5 2.5 mm²)			
 for control circuit finely stranded with core end 	1x (0.5 2.5 mm²), 2x (0.5 1.5 mm²)			
processing				
 at AWG cables for control circuit solid 	1x (20 12), 2x (20 14)			
wire length				
 between soft starter and motor maximum 	800 m			
 at the digital inputs at AC maximum 	100 m			
tightening torque				
 for main contacts with screw-type terminals 	2 2.5 N·m			
 for auxiliary and control contacts with screw-type 	0.8 1.2 N⋅m			
terminals				
tightening torque [lbf·in]				
 for main contacts with screw-type terminals 	18 22 lbf·in			
 for auxiliary and control contacts with screw-type 	7 10.3 lbf·in			
terminals				
Ambient conditions				
installation altitude at height above sea level maximum	5 000 m; Derating as of 1000 m, see catalog			
ambient temperature				
 during operation 	-25 +60 °C; Please observe derating at temperatures of 40 °C or			
	above			
 during storage and transport 	-40 +80 °C			
environmental category				
 during operation according to IEC 60721 	3K6 (no ice formation, only occasional condensation), 3C3 (no salt mist), 3S2 (sand must not get into the devices), 3M6			
 during storage according to IEC 60721 	1K6 (only occasional condensation), 1C2 (no salt mist), 1S2 (sand must not get inside the devices), 1M4			
during transport according to IEC 60721	2K2, 2C1, 2S1, 2M2 (max. fall height 0.3 m)			
EMC emitted interference	acc. to IEC 60947-4-2: Class A			
Communication/ Protocol				
communication module is supported				
 PROFINET standard 	Yes			
EtherNet/IP	Yes			
Modbus RTU	Yes			
Modbus TCP	Yes			
PROFIBUS	Yes			
UL/CSA ratings				
manufacturer's article number				
of circuit breaker				
 usable for Standard Faults at 460/480 V according to UL 	Siemens type: 3RV2742, max. 60 A or 3VA51, max. 60 A; Iq = 5 kA			
— usable for High Faults at 460/480 V according to UL	Siemens type: 3RV2742, max. 30 A or 3VA51, max. 35 A; Iq max = 65 kA			
 usable for Standard Faults at 460/480 V at inside-delta circuit according to UL 	Siemens type: 3RV2742, max. 60 A or 3VA51, max. 60 A; lq = 5 kA			
— usable for High Faults at 460/480 V at inside- delta circuit according to UL	Siemens type: 3VA51, max. 35 A; lq max = 65 kA			
 usable for Standard Faults at 575/600 V according to UL 	Siemens type: 3RV2742, max. 60 A or 3VA51, max. 60 A; Iq = 5 kA			
 usable for Standard Faults at 575/600 V at inside-delta circuit according to UL 	Siemens type: 3RV2742, max. 60 A or 3VA51, max. 60 A; lq = 5 kA			
 of the fuse 				

	 — usable for Standard Faults up to 575/600 V according to UL 		Type: Clas	ss RK5 / K5, max	x. 70 A; lq = 5 kA		
— usable for High Faults up to 575/600 V according to UL		Type: Class J / L, max. 70 A; Iq = 100 kA					
	— usable for Standard Faults at inside-delta circuit up to 575/600 V according to UL		Type: Class RK5 / K5, max. 70 A; lq = 5 kA				
	— usable for High Faults at inside-delta circuit up to 575/600 V according to UL		Type: Class J / L, max. 70 A; lq = 100 kA				
operating power [hp]] for 3-phase motors	;					
• at 200/208 V at	50 °C rated value		3 hp				
• at 220/230 V at	50 °C rated value		5 hp				
• at 460/480 V at	50 °C rated value		10 hp				
• at 575/600 V at			10 hp				
	inside-delta circuit at	50 °C rated	7.5 hp				
	inside-delta circuit at	50 °C rated	7.5 hp				
• at 460/480 V at value	inside-delta circuit at	50 °C rated	20 hp				
● at 575/600 V at value	inside-delta circuit at	50 °C rated	25 hp				
contact rating of aux	iliary contacts acco	rding to UL	R300-B30	0			
Safety related data	-						
protection class IP o	n the front accordin	a to IEC	IP20				
60529		g to ieo	11 20				
touch protection on	the front according	to IEC 60529	finger-safe	, for vertical con	tact from the front		
· · ·			-				
electromagnetic com	npatibility		in accorda	nce with IEC 60	947-4-2		
electromagnetic com			in accorda	nce with IEC 60	947-4-2		
Certificates/ approvals	5		in accorda	nce with IEC 60	947-4-2	EMC	
Ŭ	5		in accorda	nce with IEC 60	947-4-2	EMC	
Certificates/ approvals	5	CCC CCC	in accorda	nce with IEC 60	ERC	EMC ECM	
Certificates/ approvals	proval <u>Confirmation</u>	Ccc Test Certifica		rine / Shipping	BAT-4-2	EMC ECM	
Certificates/ approvals General Product Ap	proval <u>Confirmation</u>	ccc Test Certifica		(U) UL	P47-4-2	EMC ECM	
Certificates/ approvals General Product Ap	proval <u>Confirmation</u>	Test Certifica Type Test Certifica	ates Ma rtific-	(U) UL	947-4-2 EAC	EMC ECM	
Certificates/ approvals General Product Ap	proval <u>Confirmation</u> ormity	<u>Type Test Cer</u> ates/Test Re	ates Ma rtific-	(U) UL	EAC	RCM	
Certificates/ approvals General Product Ap	proval <u>Confirmation</u> ormity	Type Test Cer	ates Ma rtific-	(U) UL	EAC	RCM	
Certificates/ approvals General Product Ap	proval <u>Confirmation</u> ormity	<u>Type Test Cer</u> ates/Test Re	ates Ma r <u>tific-</u> port	(U) UL	EAC	RCM	

Further information
Information- and Downloadcenter (Catalogs, Brochures,)
https://www.siemens.com/ic10
Industry Mall (Online ordering system)
https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RW5214-1TC15
Cax online generator
http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RW5214-1TC15
Service&Support (Manuals, Certificates, Characteristics, FAQs,)
https://support.industry.siemens.com/cs/ww/en/ps/3RW5214-1TC15
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros,) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RW5214-1TC15⟨=en
Characteristic: Tripping characteristics, I ² t, Let-through current

https://support.industry.siemens.com/cs/ww/en/ps/3RW5214-1TC15/char Characteristic: Installation altitude http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RW5214-1TC15&objecttype=14&gridview=view1 Simulation Tool for Soft Starters (STS) https://support.industry.siemens.com/cs/ww/en/view/101494917

last modified:

4/10/2022 🖸