SIEMENS

Data sheet 3RW5215-1TC15



SIRIUS soft starter 200-600 V 25 A, 110-250 V AC Screw terminals Thermistor input

product brand name	SIRIUS
product category	Hybrid switching devices
product designation	Soft starter
product type designation	3RW52
manufacturer's article number	
 of standard HMI module usable 	3RW5980-0HS00
 of high feature HMI module usable 	3RW5980-0HF00
 of communication module PROFINET standard usable 	3RW5980-0CS00
 of communication module PROFIBUS usable 	3RW5980-0CP00
 of communication module Modbus TCP usable 	3RW5980-0CT00
 of communication module Modbus RTU usable 	3RW5980-0CR00
 of communication module Ethernet/IP 	3RW5980-0CE00
 of circuit breaker usable at 400 V 	3RV2032-4EA10; Type of coordination 1, Iq = 65 kA, CLASS 10
 of circuit breaker usable at 500 V 	3RV2032-4EA10; Type of coordination 1, Iq = 15 kA, CLASS 10
 of circuit breaker usable at 400 V at inside-delta circuit 	3RV2032-4VA10; Type of coordination 1, Iq = 65 kA, CLASS 10
 of circuit breaker usable at 500 V at inside-delta circuit 	3RV2032-4VA10; Type of coordination 1, Iq = 15 kA, CLASS 10
 of the gG fuse usable up to 690 V 	3NA3822-6; Type of coordination 1, Iq = 65 kA
 of the gG fuse usable at inside-delta circuit up to 500 V 	3NA3822-6; Type of coordination 1, Iq = 65 kA
 of full range R fuse link for semiconductor protection usable up to 690 V 	3NE1817-0: Type of coordination 2, Iq = 65 kA
 of back-up R fuse link for semiconductor protection usable up to 690 V 	3NE8021-1; Type of coordination 2, Iq = 65 kA

General technical data	
starting voltage [%]	30 100 %
stopping voltage [%]	50 %; non-adjustable
start-up ramp time of soft starter	0 20 s
current limiting value [%] adjustable	130 700 %
certificate of suitability	
CE marking	Yes
 UL approval 	Yes
CSA approval	Yes
product component	
 HMI-High Feature 	No
 is supported HMI-Standard 	Yes
is supported HMI-High Feature	Yes
product feature integrated bypass contact system	Yes
number of controlled phases	3

trip class	CLASS 10A (default) / 10E / 20E; acc. to IEC 60947-4-2
buffering time in the event of power failure	
for main current circuit	100 ms
for control circuit	100 ms
insulation voltage rated value	600 V
degree of pollution	3, acc. to IEC 60947-4-2
impulse voltage rated value	6 kV
blocking voltage of the thyristor maximum	1 600 V
service factor	1
surge voltage resistance rated value	6 kV
maximum permissible voltage for safe isolation	
between main and auxiliary circuit	600 V
shock resistance	15 g / 11 ms, from 12 g / 11 ms with potential contact lifting
vibration resistance	15 mm to 6 Hz; 2g to 500 Hz
utilization category according to IEC 60947-4-2	AC 53a
reference code according to IEC 81346-2	Q
Substance Prohibitance (Date)	02/15/2018
product function	
ramp-up (soft starting)	Yes
ramp-down (soft stop)	Yes
Soft Torque	Yes
 adjustable current limitation 	Yes
pump ramp down	Yes
intrinsic device protection	Yes
motor overload protection	Yes; Full motor protection (thermistor motor protection and electronic motor overload protection)
 evaluation of thermistor motor protection 	Yes; Type A PTC or Klixon / Thermoclick
inside-delta circuit	Yes
auto-RESET	Yes
manual RESET	Yes
• remote reset	Yes; By turning off the control supply voltage
 communication function 	Yes
 operating measured value display 	Yes; Only in conjunction with special accessories
error logbook	Yes; Only in conjunction with special accessories
 via software parameterizable 	No
 via software configurable 	Yes
PROFlenergy	Yes; in connection with the PROFINET Standard communication module
firmware update	Yes
 removable terminal for control circuit 	Yes
torque control	No
analog output	No
Power Electronics	
operational current	
 at 40 °C rated value 	25 A
 at 50 °C rated value 	22 A
at 60 °C rated value	20 A
operational current at inside-delta circuit	
 at 40 °C rated value 	43.3 A
 at 50 °C rated value 	39 A
at 60 °C rated value	33.9 A
operating voltage	
rated value	200 600 V
at inside-delta circuit rated value	200 600 V
relative negative tolerance of the operating voltage	-15 %
relative positive tolerance of the operating voltage	10 %
relative negative tolerance of the operating voltage at inside-delta circuit	-15 %
relative positive tolerance of the operating voltage at inside-delta circuit	10 %
operating power for 3-phase motors	

at 220 V at 40 °C rated value	E E LAM
• at 230 V at 40 °C rated value	5.5 kW
• at 230 V at inside-delta circuit at 40 °C rated value	11 kW
• at 400 V at 40 °C rated value	11 kW
 at 400 V at inside-delta circuit at 40 °C rated value 	18.5 kW
 at 500 V at 40 °C rated value 	15 kW
at 500 V at inside-delta circuit at 40 °C rated value	22 kW
Operating frequency 1 rated value	50 Hz
Operating frequency 2 rated value	60 Hz
relative negative tolerance of the operating frequency	-10 %
relative positive tolerance of the operating frequency	10 %
adjustable motor current	
 at rotary coding switch on switch position 1 	11.5 A
 at rotary coding switch on switch position 2 	12.4 A
 at rotary coding switch on switch position 3 	13.3 A
 at rotary coding switch on switch position 4 	14.2 A
 at rotary coding switch on switch position 5 	15.1 A
 at rotary coding switch on switch position 6 	16 A
 at rotary coding switch on switch position 7 	16.9 A
 at rotary coding switch on switch position 8 	17.8 A
 at rotary coding switch on switch position 9 	18.7 A
 at rotary coding switch on switch position 10 	19.6 A
 at rotary coding switch on switch position 11 	20.5 A
 at rotary coding switch on switch position 12 	21.4 A
 at rotary coding switch on switch position 13 	22.3 A
 at rotary coding switch on switch position 14 	23.2 A
 at rotary coding switch on switch position 15 	24.1 A
 at rotary coding switch on switch position 16 	25 A
• minimum	11.5 A
adjustable motor current	
 for inside-delta circuit at rotary coding switch on switch position 1 	19.9 A
 for inside-delta circuit at rotary coding switch on switch position 2 	21.5 A
 for inside-delta circuit at rotary coding switch on switch position 3 	23 A
 for inside-delta circuit at rotary coding switch on switch position 4 	24.6 A
 for inside-delta circuit at rotary coding switch on switch position 5 	26.2 A
 for inside-delta circuit at rotary coding switch on switch position 6 	27.7 A
 for inside-delta circuit at rotary coding switch on switch position 7 	29.3 A
 for inside-delta circuit at rotary coding switch on switch position 8 	30.8 A
for inside-delta circuit at rotary coding switch on switch position 9 for inside delta circuit at rotary coding switch on switch on the formula delta circuit at rotary coding switch on the formula delta circuit at rotary coding switch on the formula delta circuit at rotary coding switch on the formula delta circuit at rotary coding switch on the formula delta circuit at rotary coding switch on the formula delta circuit at rotary coding switch on switch on the formula delta circuit at rotary coding switch on switch position.	32.4 A
for inside-delta circuit at rotary coding switch on switch position 10 for inside delta circuit at rotary coding switch on	33.9 A
for inside-delta circuit at rotary coding switch on switch position 11 for inside delta circuit at rotary coding switch on	35.5 A
for inside-delta circuit at rotary coding switch on switch position 12 for inside delta circuit at rotary coding switch on	37.1 A
for inside-delta circuit at rotary coding switch on switch position 13 for inside delta circuit at rotary coding switch on	38.6 A
for inside-delta circuit at rotary coding switch on switch position 14 for inside delta circuit at rotary coding switch on	40.2 A
for inside-delta circuit at rotary coding switch on switch position 15 for inside delta circuit at retary coding switch on	41.7 A
 for inside-delta circuit at rotary coding switch on switch position 16 at inside-delta circuit minimum 	43.3 A
	19.9 A
minimum load [%]	15 %; Relative to smallest settable le
power loss [W] for rated value of the current at AC	

 at 40 °C after startup 	20 W
 at 50 °C after startup 	19 W
 at 60 °C after startup 	18 W
power loss [W] at AC at current limitation 350 %	
 at 40 °C during startup 	376 W
 at 50 °C during startup 	318 W
 at 60 °C during startup 	278 W
Control circuit/ Control	
type of voltage of the control supply voltage	AC
control supply voltage at AC	
• at 50 Hz	110 250 V
• at 60 Hz	110 250 V
relative negative tolerance of the control supply	-15 %
voltage at AC at 50 Hz relative positive tolerance of the control supply	10 %
voltage at AC at 50 Hz	10 /3
relative negative tolerance of the control supply voltage at AC at 60 Hz	-15 %
relative positive tolerance of the control supply voltage at AC at 60 Hz	10 %
control supply voltage frequency	50 60 Hz
relative negative tolerance of the control supply voltage frequency	-10 %
relative positive tolerance of the control supply voltage frequency	10 %
control supply current in standby mode rated value	30 mA
holding current in bypass operation rated value	75 mA
locked-rotor current at close of bypass contact maximum	0.17 A
inrush current peak at application of control supply voltage maximum	12.2 A
duration of inrush current peak at application of control supply voltage	2.2 ms
design of the overvoltage protection	Varistor
design of short-circuit protection for control circuit	4 A gG fuse (Icu=1 kA), 6 A quick-acting fuse (Icu=1 kA), C1 miniature circuit breaker (Icu= 600 A), C6 miniature circuit breaker (Icu= 300 A); Is not part of scope of supply
Inputs/ Outputs	
number of digital inputs	1
number of digital outputs	3
not parameterizable	2
digital output version	2 normally-open contacts (NO) / 1 changeover contact (CO)
number of analog outputs	0
switching capacity current of the relay outputs	
• at AC-15 at 250 V rated value	3 A
• at DC-13 at 24 V rated value	1 A
Installation/ mounting/ dimensions	
mounting position	+/- 10° rotation possible and can be tilted forward or backward on vertical mounting surface
fastening method	screw fixing
height	275 mm
width	170 mm
depth	152 mm
required spacing with side-by-side mounting	
• forwards	10 mm
• backwards	0 mm
• upwards	100 mm
downwards	75 mm
• at the side	5 mm
weight without packaging	2.1 kg
Connections/ Terminals	
type of electrical connection	

for main current circuit	screw-type terminals
• for control circuit	screw-type terminals
wire length for thermistor connection	S. S. Spoterminals
with conductor cross-section = 0.5 mm² maximum	50 m
with conductor cross-section = 1.5 mm² maximum	150 m
with conductor cross-section = 2.5 mm² maximum	250 m
type of connectable conductor cross-sections	200
• for main contacts	
— solid	2x (1.0 2.5 mm²), 2x (2.5 10 mm²)
finely stranded with core end processing	2x (1.0 2.5 mm²), 2x (2.5 10 mm²)
at AWG cables for main current circuit solid	2x (16 12), 2x (14 8)
type of connectable conductor cross-sections	ZX (10 12), ZX (14 0)
for control circuit solid	1x (0.5 4.0 mm²), 2x (0.5 2.5 mm²)
for control circuit solid for control circuit finely stranded with core end	1x (0.5 2.5 mm²), 2x (0.5 2.5 mm²)
processing	1% (0.5 2.5 11111), 2% (0.5 1.5 111111)
at AWG cables for control circuit solid	1x (20 12), 2x (20 14)
wire length	(20 iii 12); 2x (20 iii 11)
between soft starter and motor maximum	800 m
at the digital inputs at AC maximum	100 m
tightening torque	100 111
	2 2.5 N·m
for main contacts with screw-type terminals for auxiliary and control contacts with screw-type	2 2.5 N·Ⅲ 0.8 1.2 N·m
 for auxiliary and control contacts with screw-type terminals 	0.0 1.2 IVIII
tightening torque [lbf·in]	
for main contacts with screw-type terminals	18 22 lbf·in
for auxiliary and control contacts with screw-type	7 10.3 lbf·in
terminals	
Ambient conditions	
installation altitude at height above sea level maximum	5 000 m; Derating as of 1000 m, see catalog
ambient temperature	,
during operation	-25 +60 °C; Please observe derating at temperatures of 40 °C or
	above
 during storage and transport 	-40 +80 °C
environmental category	
 during operation according to IEC 60721 	3K6 (no ice formation, only occasional condensation), 3C3 (no salt mist), 3S2 (sand must not get into the devices), 3M6
 during storage according to IEC 60721 	1K6 (only occasional condensation), 1C2 (no salt mist), 1S2 (sand must not get inside the devices), 1M4
 during transport according to IEC 60721 	2K2, 2C1, 2S1, 2M2 (max. fall height 0.3 m)
EMC emitted interference	acc. to IEC 60947-4-2: Class A
Communication/ Protocol	
communication module is supported	
 PROFINET standard 	Yes
EtherNet/IP	Yes
Modbus RTU	Yes
Modbus TCP	Yes
• PROFIBUS	Yes
UL/CSA ratings	
manufacturer's article number	
of circuit breaker	
— usable for Standard Faults at 460/480 V according to UL	Siemens type: 3RV2742, max. 70 A or 3VA51, max. 80 A; Iq = 5 kA
usable for High Faults at 460/480 V according to UL	Siemens type: 3RV2742, max.40 A or 3VA51, max. 60 A; Iq max = 65 kA
 usable for Standard Faults at 460/480 V at inside-delta circuit according to UL 	Siemens type: 3RV2742, max. 70 A or 3VA51, max. 80 A; Iq = 5 kA
 usable for High Faults at 460/480 V at inside- delta circuit according to UL 	Siemens type: 3VA51, max. 60 A; lq max = 65 kA
 usable for Standard Faults at 575/600 V according to UL 	Siemens type: 3RV2742, max. 70 A or 3VA51, max. 80 A; Iq = 5 kA
 usable for Standard Faults at 575/600 V at inside-delta circuit according to UL 	Siemens type: 3RV2742, max. 70 A or 3VA51, max. 80 A; Iq = 5 kA
of the fuse	

- usable for Standard Faults up to 575/600 V Type: Class RK5 / K5, max. 100 A; Iq = 5 kA according to UL — usable for High Faults up to 575/600 V Type: Class J / L, max. 100 A; Iq = 100 kA according to UL - usable for Standard Faults at inside-delta Type: Class RK5 / K5, max. 100 A; Iq = 5 kA circuit up to 575/600 V according to UL - usable for High Faults at inside-delta circuit up Type: Class J / L, max. 100 A; Iq = 100 kA to 575/600 V according to UL operating power [hp] for 3-phase motors at 200/208 V at 50 °C rated value 5 hp • at 220/230 V at 50 °C rated value 7.5 hp • at 460/480 V at 50 °C rated value 15 hp • at 575/600 V at 50 °C rated value 20 hp • at 200/208 V at inside-delta circuit at 50 °C rated 10 hp value • at 220/230 V at inside-delta circuit at 50 °C rated 10 hp value • at 460/480 V at inside-delta circuit at 50 °C rated 25 hp value at 575/600 V at inside-delta circuit at 50 °C rated 30 hp value contact rating of auxiliary contacts according to UL R300-B300 Safety related data protection class IP on the front according to IEC IP20 60529 touch protection on the front according to IEC 60529 finger-safe, for vertical contact from the front

Certificates/ approvals

General Product Approval

electromagnetic compatibility

EMC





Confirmation



in accordance with IEC 60947-4-2





Declaration of Conformity

Test Certificates

Marine / Shipping





Type Test Certificates/Test Report







Marine / Shipping

other





Confirmation

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RW5215-1TC15

Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RW5215-1TC15

 ${\bf Service \& Support~(Manuals,~Certificates,~Characteristics,~FAQs,...)}$

https://support.industry.siemens.com/cs/ww/en/ps/3RW5215-1TC15

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax de.aspx?mlfb=3RW5215-1TC15&lang=en

Characteristic: Tripping characteristics, I2t, Let-through current

https://support.industry.siemens.com/cs/ww/en/ps/3RW5215-1TC15/char Characteristic: Installation altitude Simulation Tool for Soft Starters (STS)
https://support.industry.siemens.com/cs/ww/en/view/101494917 4/10/2022 last modified: