SIEMENS

3RW5235-6AC05 **Data sheet**



SIRIUS soft starter 200-600 V 143 A, 24 V AC/DC Screw terminals Analog output

product category product designation product type designation manufacturer's article number • of standard HMI module usable	Hybrid switching devices Soft starter 3RW52
product type designation manufacturer's article number	
manufacturer's article number	3RW52
of standard HMI module usable	
	3RW5980-0HS00
 of high feature HMI module usable 	3RW5980-0HF00
 of communication module PROFINET standard usable 	3RW5980-0CS00
of communication module PROFIBUS usable	3RW5980-0CP00
of communication module Modbus TCP usable	3RW5980-0CT00
of communication module Modbus RTU usable	3RW5980-0CR00
of communication module Ethernet/IP	3RW5980-0CE00
of circuit breaker usable at 400 V	3VA2220-7MN32-0AA0; Type of coordination 1, lq = 65 kA, CLASS 10
 of circuit breaker usable at 400 V at inside-delta circuit 	3VA2325-7MN32-0AA0; Type of coordination 1, Iq = 65 kA, CLASS 10
 of the gG fuse usable up to 690 V 	3NA3244-6; Type of coordination 1, Iq = 65 kA
 of the gG fuse usable at inside-delta circuit up to 500 V 	3NA3244-6; Type of coordination 1, Iq = 65 kA
 of full range R fuse link for semiconductor protection usable up to 690 V 	3NE1227-0; Type of coordination 2, Iq = 65 kA
 of back-up R fuse link for semiconductor protection usable up to 690 V 	3NE3334-0B; Type of coordination 2, Iq = 65 kA
General technical data	
starting voltage [%]	30 100 %
stopping voltage [%]	50 %; non-adjustable
start-up ramp time of soft starter	0 20 s
current limiting value [%] adjustable	130 700 %
certificate of suitability	
CE marking	Yes
UL approval	Yes
CSA approval	Yes
product component	
HMI-High Feature	No
• is supported HMI-Standard	Yes
is supported HMI-High Feature	Yes
product feature integrated bypass contact system	Yes
number of controlled phases	3
trip class	CLASS 10A (default) / 10E / 20E; acc. to IEC 60947-4-2
buffering time in the event of power failure	
for main current circuit	100 ms

for control circuit	100 ms
insulation voltage rated value	600 V
degree of pollution	3, acc. to IEC 60947-4-2
impulse voltage rated value	6 kV
blocking voltage of the thyristor maximum	1 800 V
service factor	1
surge voltage resistance rated value	6 kV
maximum permissible voltage for safe isolation	
 between main and auxiliary circuit 	600 V
shock resistance	15 g / 11 ms, from 12 g / 11 ms with potential contact lifting
vibration resistance	15 mm to 6 Hz; 2g to 500 Hz
utilization category according to IEC 60947-4-2	AC 53a
reference code according to IEC 81346-2	Q
Substance Prohibitance (Date)	02/15/2018
product function	
ramp-up (soft starting)	Yes
• ramp-down (soft stop)	Yes
• Soft Torque	Yes
adjustable current limitation	Yes
pump ramp down	Yes
	Yes
intrinsic device protection meter everlend protection	
motor overload protection application of thermister mater protection	Yes; Electronic motor overload protection
evaluation of thermistor motor protection incide delta giravit	No Yea
• inside-delta circuit	Yes
auto-RESET	Yes
manual RESET	Yes
remote reset	Yes; By turning off the control supply voltage
 communication function 	Yes
 operating measured value display 	Yes; Only in conjunction with special accessories
 error logbook 	Yes; Only in conjunction with special accessories
 via software parameterizable 	No
 via software configurable 	Yes
PROFlenergy	Yes; in connection with the PROFINET Standard communication module
firmware update	Yes
 removable terminal for control circuit 	Yes
torque control	No
analog output	Yes; 4 20 mA (default) / 0 10 V (parameterizable with High Feature HMI)
Power Electronics	
operational current	
at 40 °C rated value	143 A
at 50 °C rated value	128 A
at 60 °C rated value	118 A
operational current at inside-delta circuit	
at 40 °C rated value	248 A
at 50 °C rated value at 50 °C rated value	222 A
at 60 °C rated value at 60 °C rated value	204 A
operating voltage	20171
rated value	200 600 V
	200 600 V
at inside-delta circuit rated value relative possitive telegrapes of the energting voltage.	
relative negative tolerance of the operating voltage	-15 % 10 %
relative positive tolerance of the operating voltage	-15 %
inside-delta circuit relative positive tolerance of the operating voltage at inside-delta circuit	10 %
operating power for 3-phase motors	27 MM
• at 230 V at 40 °C rated value	37 kW
at 230 V at inside-delta circuit at 40 °C rated value	75 kW
 at 400 V at 40 °C rated value 	75 kW

e at 400 V at incide delta singuit at 40 90 anti-delta	122 1/1/
at 400 V at inside-delta circuit at 40 °C rated value at 500 V at 40 °C rated value	132 kW
• at 500 V at 40 °C rated value	90 kW
at 500 V at inside-delta circuit at 40 °C rated value Operating frequency 1 rated value	160 kW 50 Hz
Operating frequency 1 rated value Operating frequency 2 rated value	60 Hz
relative negative tolerance of the operating frequency	-10 %
relative negative tolerance of the operating frequency	10 %
adjustable motor current	10 70
at rotary coding switch on switch position 1	68 A
at rotary coding switch on switch position 2	73 A
at rotary coding switch on switch position 3	78 A
at rotary coding switch on switch position 4	83 A
at rotary coding switch on switch position 5	88 A
 at rotary coding switch on switch position 6 	93 A
 at rotary coding switch on switch position 7 	98 A
 at rotary coding switch on switch position 8 	103 A
 at rotary coding switch on switch position 9 	108 A
 at rotary coding switch on switch position 10 	113 A
at rotary coding switch on switch position 11	118 A
at rotary coding switch on switch position 12	123 A
at rotary coding switch on switch position 13	128 A
at rotary coding switch on switch position 14	133 A
at rotary coding switch on switch position 15	138 A
 at rotary coding switch on switch position 16 	143 A
• minimum	68 A
adjustable motor current	
 for inside-delta circuit at rotary coding switch on switch position 1 	118 A
 for inside-delta circuit at rotary coding switch on switch position 2 	126 A
 for inside-delta circuit at rotary coding switch on switch position 3 	135 A
 for inside-delta circuit at rotary coding switch on switch position 4 	144 A
 for inside-delta circuit at rotary coding switch on switch position 5 	152 A
 for inside-delta circuit at rotary coding switch on switch position 6 	161 A
 for inside-delta circuit at rotary coding switch on switch position 7 	170 A
 for inside-delta circuit at rotary coding switch on switch position 8 	178 A
 for inside-delta circuit at rotary coding switch on switch position 9 	187 A
 for inside-delta circuit at rotary coding switch on switch position 10 	196 A
for inside-delta circuit at rotary coding switch on switch position 11	204 A
for inside-delta circuit at rotary coding switch on switch position 12 for inside delta circuit at rotary coding switch on	213 A
for inside-delta circuit at rotary coding switch on switch position 13 for inside delta circuit at rotary coding switch on	222 A 230 A
for inside-delta circuit at rotary coding switch on switch position 14 for inside-delta circuit at rotary coding switch on	239 A
 for inside-delta circuit at rotary coding switch on switch position 15 for inside-delta circuit at rotary coding switch on 	248 A
switch position 16 at inside-delta circuit minimum	118 A
• at inside-delta circuit minimum minimum load [%]	15 %; Relative to smallest settable le
power loss [W] for rated value of the current at AC	10 /v, Notative to official octable to
• at 40 °C after startup	55 W
at 50 °C after startup	50 W
at 60 °C after startup	47 W
·	

power loss [W] at AC at current limitation 350 %	
 at 40 °C during startup 	2 127 W
 at 50 °C during startup 	1 807 W
 at 60 °C during startup 	1 605 W
Control circuit/ Control	
type of voltage of the control supply voltage	AC/DC
control supply voltage at AC	
at 50 Hz rated value	24 V
at 60 Hz rated value	24 V
relative negative tolerance of the control supply	-20 %
voltage at AC at 50 Hz	
relative positive tolerance of the control supply	20 %
voltage at AC at 50 Hz	
relative negative tolerance of the control supply voltage at AC at 60 Hz	-20 %
relative positive tolerance of the control supply voltage at AC at 60 Hz	20 %
control supply voltage frequency	50 60 Hz
relative negative tolerance of the control supply	-10 %
voltage frequency	
relative positive tolerance of the control supply voltage frequency	10 %
control supply voltage	
at DC rated value	24 V
relative negative tolerance of the control supply	-20 %
voltage at DC	
relative positive tolerance of the control supply voltage at DC	20 %
control supply current in standby mode rated value	160 mA
holding current in bypass operation rated value	380 mA
locked-rotor current at close of bypass contact maximum	7.6 A
inrush current peak at application of control supply voltage maximum	3.3 A
duration of inrush current peak at application of control supply voltage	12.1 ms
design of the overvoltage protection	Varistor
design of short-circuit protection for control circuit	4 A gG fuse (Icu=1 kA), 6 A quick-acting fuse (Icu=1 kA), C1 miniature circuit breaker (Icu= 600 A), C6 miniature circuit breaker (Icu= 300 A); Is not part of scope of supply
Inputs/ Outputs	
number of digital inputs	1
number of digital outputs	3
not parameterizable	2
digital output version	2 normally-open contacts (NO) / 1 changeover contact (CO)
number of analog outputs	1
switching capacity current of the relay outputs	
• at AC-15 at 250 V rated value	3 A
• at DC-13 at 24 V rated value	1 A
Installation/ mounting/ dimensions	
mounting position	with vertical mounting surface +/-90° rotatable, with vertical mounting surface +/- 22.5° tiltable to the front and back
fastening method	screw fixing
height	306 mm
width	185 mm
depth	203 mm
required spacing with side-by-side mounting	
• forwards	10 mm
• backwards	0 mm
• upwards	100 mm
downwards	75 mm
• at the side	5 mm
weight without packaging	6.6 kg

Connections/ Terminals	
type of electrical connection	
for main current circuit	busbar connection
for control circuit	screw-type terminals
width of connection bar maximum	25 mm
type of connectable conductor cross-sections	
for DIN cable lug for main contacts stranded	2x (16 95 mm²)
for DIN cable lug for main contacts finely stranded	2x (25 120 mm²)
type of connectable conductor cross-sections	
for control circuit solid	1x (0.5 4.0 mm²), 2x (0.5 2.5 mm²)
 for control circuit finely stranded with core end 	1x (0.5 2.5 mm²), 2x (0.5 1.5 mm²)
processing	
at AWG cables for control circuit solid	1x (20 12), 2x (20 14)
wire length	
 between soft starter and motor maximum 	800 m
 at the digital inputs at AC maximum 	100 m
at the digital inputs at DC maximum	1 000 m
tightening torque	
for main contacts with screw-type terminals	10 14 N·m
 for auxiliary and control contacts with screw-type terminals 	0.8 1.2 N·m
tightening torque [lbf·in]	
for main contacts with screw-type terminals	89 124 lbf·in
for auxiliary and control contacts with screw-type	7 10.3 lbf·in
terminals	7 10.0 101 111
Ambient conditions	
installation altitude at height above sea level maximum	5 000 m; Derating as of 1000 m, see catalog
ambient temperature	
during operation	-25 +60 °C; Please observe derating at temperatures of 40 °C or
during stances 10	above
during storage and transport	-40 +80 °C
environmental category	OVC (no ice formation onlyin-land) ") CCC (
 during operation according to IEC 60721 	3K6 (no ice formation, only occasional condensation), 3C3 (no salt mist), 3S2 (sand must not get into the devices), 3M6
 during storage according to IEC 60721 	1K6 (only occasional condensation), 1C2 (no salt mist), 1S2 (sand must
adming otologo dooolamig to 120 oo. 21	not get inside the devices), 1M4
 during transport according to IEC 60721 	2K2, 2C1, 2S1, 2M2 (max. fall height 0.3 m)
EMC emitted interference	acc. to IEC 60947-4-2: Class A
Communication/ Protocol	
communication module is supported	
 PROFINET standard 	Yes
• EtherNet/IP	Yes
 Modbus RTU 	Yes
Modbus TCP	Yes
• PROFIBUS	Yes
UL/CSA ratings	
manufacturer's article number	
of circuit breaker	
 usable for Standard Faults at 460/480 V according to UL 	Siemens type: 3VA52, max. 250 A; lq = 10 kA
usable for High Faults at 460/480 V according to UL	Siemens type: 3VA52, max. 250 A; lq max = 65 kA
usable for Standard Faults at 460/480 V at inside-delta circuit according to UL	Siemens type: 3VA52, max. 250 A; Iq = 10 kA
usable for High Faults at 460/480 V at inside- delta circuit according to UL	Siemens type: 3VA52, max. 250 A; Iq max = 65 kA
usable for Standard Faults at 575/600 V according to UL	Siemens type: 3VA52, max. 250 A; Iq = 10 kA
 usable for Standard Faults at 575/600 V at inside-delta circuit according to UL 	Siemens type: 3VA52, max. 250 A; lq = 10 kA
of the fuse usable for Standard Faults up to 575/600 V according to LII.	Type: Class RK5 / K5, max. 350 A; Iq = 10 kA
according to UL	

- usable for High Faults up to 575/600 V Type: Class J / L, max. 350 A; Iq = 100 kA according to UL - usable for Standard Faults at inside-delta Type: Class RK5 / K5, max. 350 A; Iq = 10 kA circuit up to 575/600 V according to UL - usable for High Faults at inside-delta circuit up Type: Class J / L, max. 350 A; Iq = 100 kA to 575/600 V according to UL operating power [hp] for 3-phase motors • at 200/208 V at 50 °C rated value 40 hp • at 220/230 V at 50 °C rated value 40 hp • at 460/480 V at 50 °C rated value 100 hp • at 575/600 V at 50 °C rated value 125 hp at 200/208 V at inside-delta circuit at 50 °C rated 75 hp value • at 220/230 V at inside-delta circuit at 50 °C rated 75 hp value • at 460/480 V at inside-delta circuit at 50 °C rated 150 hp value • at 575/600 V at inside-delta circuit at 50 °C rated 200 hp value contact rating of auxiliary contacts according to UL R300-B300 Safety related data protection class IP on the front according to IEC IP00; IP20 with cover 60529 touch protection on the front according to IEC 60529 finger-safe, for vertical contact from the front with cover in accordance with IEC 60947-4-2 electromagnetic compatibility

Certificates/ approvals

General Product Approval

EMC





Confirmation







Declaration of Conformity

Test Certificates

Marine / Shipping





Type Test Certificates/Test Report







Marine / Shipping

other





Confirmation

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RW5235-6AC05

Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RW5235-6AC05

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3RW5235-6AC05

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)


http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RW5235-6AC05&lang=en


Characteristic: Tripping characteristics, I²t, Let-through current

https://support.industry.siemens.com/cs/ww/en/ps/3RW5235-6AC05/char

Characteristic: Installation altitude

http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RW5235-6AC05&objecttype=14&gridview=view1





4/10/2022 last modified: