

**MAAL-011155** 

Rev. V3

#### **Features**

- Wideband Performance
- Phase Noise: -167 dBc/Hz @ 10 kHz Offset
- Noise Figure: 5 dB @ 6 GHz
- Bias Voltage: 5 V
- Bias Current: 90 mA
- 50 Ω Matched Input / Output
- Positive Voltage Only
- Lead-Free 4 mm 16-lead PQFN Package
- RoHS\* Compliant

### **Applications**

Test & Measurement, EW, ECM, and Radar

### **Description**

The MAAL-011155 is an easy to use, wideband ultra low phase noise distributed amplifier in a lead-free 4 mm 16-lead PQFN package. It operates from 6 to 12 GHz and provides -167 dBc/Hz phase noise, 15.6 dB of linear gain, 20 dBm of P1dB, and 5 dB of noise figure. The input and output are fully matched to 50  $\Omega$  with typical return loss of 16 dB.

The RF output port is DC blocked. Amplifier control is available through the use of a control circuit.

This product is fabricated using a low phase noise HBT process which features full passivation for enhanced reliability.


The MAAL-011155 can be used as a low noise amplifier stage for signal generation applications. This device is ideally suited for Test and Measurement, EW, ECM, and Radar applications where ultra low phase noise and drive power is required.

# Ordering Information<sup>1,2</sup>

Part Number	Package
MAAL-011155-TR0100	100 piece reel
MAAL-011155-SMB	Sample Board

- 1. Reference Application Note M513 for reel size information.
- 2. All sample boards include 3 loose parts.

#### **Functional Schematic**



# **Pin Configuration**

Pin #	Pin Name	Description	
1,5,6,8,9,13,15,16	N/C <sup>3</sup>	No Connection	
2,4,10,12	GND	Ground	
3	RF <sub>IN</sub>	RF Input	
7	$V_{REF}$	Reference Voltage	
11	RF <sub>OUT</sub>	RF Output	
14	V <sub>CC</sub>	Collector Voltage	
Paddle <sup>4</sup>	GND	Ground	

- MACOM recommends connecting unused package pins to ground.
- The exposed pad centered on the package bottom must be connected to RF, DC and thermal ground.

<sup>\*</sup> Restrictions on Hazardous Substances, compliant to current RoHS EU directive.



Rev. V3

# Electrical Specifications: Freq. = 6 - 12 GHz, $T_A = +25$ °C, $V_{CC} = +5$ V, $Z_0 = 50$ $\Omega$

Parameter	Test Conditions	Units	Min.	Тур.	Max.
Gain	P <sub>IN</sub> = -15 dBm 6 GHz 9 GHz 12 GHz	dB	13.5 13.0 12.5	16.0 15.5 15.0	_
Gain Flatness	_	dB	_	±0.4	_
Gain Variation over Temperature	_	dB/°C	_	0.017	_
Output Power	P <sub>IN</sub> = 5.0 dBm, 6 GHz P <sub>IN</sub> = 4.7 dBm, 9 GHz P <sub>IN</sub> = 3.0 dBm, 12 GHz	dBm	17.0 17.0 14.5	20.0 20.0 17.5	_
Noise Figure	_	dB	_	5	_
Input Return Loss	_	dB	_	16	_
Output Return Loss	_	dB	_	16	_
P1dB	6 GHz	dBm	_	20	_
P3dB	6 GHz	dBm	_	23	_
OIP3	6 GHz, -10 dBm per tone	dBm	_	31.5	_
Phase Noise	6 GHz, P1dB 100 Hz 1 kHz 10 kHz 1 MKz	dBc/Hz	_	146 160 167 175	_
Icq	_	mA	_	90	_

# **Maximum Operating Conditions**

Parameter	Maximum	
P <sub>IN</sub>	12 dBm	
V <sub>CC</sub>	6 V	
Icq	105 mA	
Junction Temperature <sup>5,6</sup>	+130°C	
Operating Temperature	-40°C to +85°C	
Storage Temperature	-40°C to +150°C	

# **Absolute Maximum Ratings**<sup>7,8</sup>

Parameter	Absolute Maximum		
Input Power	20 dBm		
V <sub>CC</sub>	6.5 V		
Icq	170 mA		
Junction Temperature <sup>5,6</sup>	+150°C		
Operating Temperature	-40°C to +85°C		
Storage Temperature	-40°C to +150°C		

- 5. Operating at nominal conditions with  $T_{J} \leq +150\,^{\circ}\text{C}$  will ensure MTTF > 1 x  $10^{6}$  hours.
- 6. Junction Temperature  $(T_J) = T_C + \Theta jc * (V * I)$ Typical thermal resistance  $(\Theta jc) = 21.0$ °C/W.
  - a) For  $T_C = +25^{\circ}C$ ,


T<sub>J</sub> = 38.2°C @ 6 V, 105 mA

- b) For  $T_C = +85^{\circ}C$ ,
- T<sub>J</sub> = 98.2°C @ 6 V, 105 mA
- 7. Exceeding any one or combination of these limits may cause permanent damage to this device.
- 8. MACOM does not recommend sustained operation near these survivability limits.



Rev. V3

## **PCB Layout**



#### **Parts List**

Part	Value	Case Style
C1,C3	100 pF	0402
C2,C4	0.1 μF	0402

# **Evaluation PCB Specifications**


Top Layer: 1 oz Copper Cladding, 0.034 mm thickness Dielectric Layer: Rogers RO4350B 0.245 mm thickness Bottom Layer: 1 oz Copper Cladding, 0.034 mm thickness Finished overall thickness: 0.313 mm



MAAL-011155

Rev. V3

# **Application Schematic**



# Operation

The technology is HBT; so, the turn-on and turn-off procedure is fairly simple.

To turn-on simply:

- 1. Apply +5 V to V<sub>CC</sub>
- 2. Starting at 0 V, adjust V<sub>REF</sub> for target I<sub>CC</sub>

#### To turn-off:

- 1. Set V<sub>REF</sub> to 0 V
- 2. Set V<sub>CC</sub> to 0 V

# **Handling Procedures**

Please observe the following precautions to avoid damage:

## **Static Sensitivity**

These electronic devices are sensitive to electrostatic discharge (ESD) and can be damaged by static electricity. Proper ESD control techniques should be used when handling these HBM Class 1A devices.





12

14

Rev. V3


# Typical Performance Curves: $V_{cc} = 5 \text{ V}$ , $I_{cc} = 90 \text{ mA}$






Frequency (GHz)

#### Input Return Loss




#### **Output Return Loss**


0



#### Reverse Isolation



Output IP3 (10 MHz Tone Spacing,  $P_{IN} = -10$  dBm per tone)



MACOM Technology Solutions Inc. (MACOM) and its affiliates reserve the right to make changes to the product(s) or information contained herein without notice.


Visit <a href="https://www.macom.com">www.macom.com</a> for additional data sheets and product information.

5




Rev. V3


# Typical Performance Curves: V<sub>CC</sub> = 5 V, +25°C



### Input Return Loss




#### **Output Return Loss**




#### Reverse Isolation


**P**SAT





6





Frequency (GHz)


MACOM Technology Solutions Inc. (MACOM) and its affiliates reserve the right to make changes to the product(s) or information contained herein without notice.


Visit <a href="https://www.macom.com">www.macom.com</a> for additional data sheets and product information.





MAAL-011155 Rev. V3


# Typical Performance Curves: I<sub>CC</sub> = 90 mA, +25°C














7

MACOM Technology Solutions Inc. (MACOM) and its affiliates reserve the right to make changes to the product(s) or information contained herein without notice.

Visit <a href="https://www.macom.com">www.macom.com</a> for additional data sheets and product information.



MAAL-011155 Rev. V3

# Typical Performance Curves: I<sub>CC</sub> = 90 mA, +25°C

# Phase Noise @ 6 GHz, P1dB -130 -140 -150 -160 -170 -180 100 10000 100000 1000000

Frequency (Hz)

# Phase Noise @ 6 GHz, P4dB -130 -140 | THO | T

10000


Frequency (Hz)


100000


1000000


100

1000









MACOM Technology Solutions Inc. (MACOM) and its affiliates reserve the right to make changes to the product(s) or information contained herein without notice.

Visit <a href="https://www.macom.com">www.macom.com</a> for additional data sheets and product information.


8



MAAL-011155

Rev. V3

## Lead-Free 4 mm 16-Lead PQFN Package



<sup>†</sup> Reference Application Note S2083 for lead-free solder reflow recommendations. Meets JEDEC moisture sensitivity level 1 requirements. Plating is NiPdAuAg.



MAAL-011155

Rev. V3

# MACOM Technology Solutions Inc. ("MACOM"). All rights reserved.

These materials are provided in connection with MACOM's products as a service to its customers and may be used for informational purposes only. Except as provided in its Terms and Conditions of Sale or any separate agreement, MACOM assumes no liability or responsibility whatsoever, including for (i) errors or omissions in these materials; (ii) failure to update these materials; or (iii) conflicts or incompatibilities arising from future changes to specifications and product descriptions, which MACOM may make at any time, without notice. These materials grant no license, express or implied, to any intellectual property rights.

THESE MATERIALS ARE PROVIDED "AS IS" WITH NO WARRANTY OR LIABILITY, EXPRESS OR IMPLIED, RELATING TO SALE AND/OR USE OF MACOM PRODUCTS INCLUDING FITNESS FOR A PARTICULAR PURPOSE, MERCHANTABILITY, INFRINGEMENT OF INTELLECTUAL PROPERTY RIGHT, ACCURACY OR COMPLETENESS, OR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES WHICH MAY RESULT FROM USE OF THESE MATERIALS.

MACOM products are not intended for use in medical, lifesaving or life sustaining applications. MACOM customers using or selling MACOM products for use in such applications do so at their own risk and agree to fully indemnify MACOM for any damages resulting from such improper use or sale.