SIEMENS

Data sheet 3RW5225-1AC05



SIRIUS soft starter 200-600 V 63 A, 24 V AC/DC Screw terminals Analog output

product brand name	SIRIUS
product category	Hybrid switching devices
product designation	Soft starter
product type designation	3RW52
manufacturer's article number	
 of standard HMI module usable 	<u>3RW5980-0HS00</u>
 of high feature HMI module usable 	3RW5980-0HF00
 of communication module PROFINET standard usable 	3RW5980-0CS00
 of communication module PROFIBUS usable 	3RW5980-0CP00
 of communication module Modbus TCP usable 	3RW5980-0CT00
 of communication module Modbus RTU usable 	3RW5980-0CR00
 of communication module Ethernet/IP 	3RW5980-0CE00
 of circuit breaker usable at 400 V 	3VA2163-7MN32-0AA0; Type of coordination 1, Iq = 65 kA, CLASS 10
 of circuit breaker usable at 500 V 	3VA2163-7MN32-0AA0; Type of coordination 1, Iq = 20 kA, CLASS 10
 of circuit breaker usable at 400 V at inside-delta circuit 	3VA2110-7MN32-0AA0; Type of coordination 1, Iq = 65 kA, CLASS 10
 of circuit breaker usable at 500 V at inside-delta circuit 	3VA2110-7MN32-0AA0; Type of coordination 1, Iq = 20 kA, CLASS 10
 of the gG fuse usable up to 690 V 	3NA3830-6; Type of coordination 1, Iq = 65 kA
 of the gG fuse usable at inside-delta circuit up to 500 V 	3NA3830-6; Type of coordination 1, Iq = 65 kA
 of full range R fuse link for semiconductor protection usable up to 690 V 	3NE1022-0; Type of coordination 2, Iq = 65 kA
 of back-up R fuse link for semiconductor protection usable up to 690 V 	3NE8024-1; Type of coordination 2, Iq = 65 kA

General technical data	
starting voltage [%]	30 100 %
stopping voltage [%]	50 %; non-adjustable
start-up ramp time of soft starter	0 20 s
current limiting value [%] adjustable	130 700 %
certificate of suitability	
 CE marking 	Yes
 UL approval 	Yes
CSA approval	Yes
product component	
 HMI-High Feature 	No
 is supported HMI-Standard 	Yes
is supported HMI-High Feature	Yes
product feature integrated bypass contact system	Yes
number of controlled phases	3

trin class	CLASS 10A (default) / 10E / 20E: 200 to IEC 60047 4.2
trip class	CLASS 10A (default) / 10E / 20E; acc. to IEC 60947-4-2
buffering time in the event of power failure	100 mg
for main current circuit for control circuit	100 ms
• for control circuit	100 ms
insulation voltage rated value	600 V
degree of pollution	3, acc. to IEC 60947-4-2
impulse voltage rated value	6 kV
blocking voltage of the thyristor maximum	1 800 V
service factor	1
surge voltage resistance rated value	6 kV
maximum permissible voltage for safe isolation	600.1/
between main and auxiliary circuit	600 V
shock resistance	15 g / 11 ms, from 12 g / 11 ms with potential contact lifting
vibration resistance	15 mm to 6 Hz; 2g to 500 Hz
utilization category according to IEC 60947-4-2	AC 53a
reference code according to IEC 81346-2	Q
Substance Prohibitance (Date)	02/15/2018
product function	Voc
• ramp-up (soft starting)	Yes
• ramp-down (soft stop)	Yes
Soft Torque	Yes
adjustable current limitation	Yes
pump ramp down intrinsis double grantoption	Yes
• intrinsic device protection	Yes
motor overload protection	Yes; Electronic motor overload protection
evaluation of thermistor motor protection	No
• inside-delta circuit	Yes
• auto-RESET	Yes
• manual RESET	Yes
• remote reset	Yes; By turning off the control supply voltage
communication function	Yes
operating measured value display	Yes; Only in conjunction with special accessories
• error logbook	Yes; Only in conjunction with special accessories
via software parameterizable	No Voc
via software configurable PROFlement	Yes
PROFlenergy	Yes; in connection with the PROFINET Standard communication module
• firmware update	Yes
 removable terminal for control circuit 	Yes
torque control	No
analog output	Yes; 4 20 mA (default) / 0 10 V (parameterizable with High Feature HMI)
Power Electronics	
operational current	
at 40 °C rated value	63 A
● at 50 °C rated value	56 A
at 60 °C rated value	51 A
operational current at inside-delta circuit	
at 40 °C rated value	109 A
at 50 °C rated value	96 A
at 60 °C rated value	87.5 A
operating voltage	
• rated value	200 600 V
at inside-delta circuit rated value	200 600 V
relative negative tolerance of the operating voltage	-15 %
relative positive tolerance of the operating voltage	10 %
relative negative tolerance of the operating voltage at inside-delta circuit	-15 %
relative positive tolerance of the operating voltage at inside-delta circuit	10 %
operating power for 3-phase motors	

a at 220 V at 40 °C rotad value	10 E I/M
• at 230 V at 40 °C rated value	18.5 kW
at 230 V at inside-delta circuit at 40 °C rated value	30 kW
• at 400 V at 40 °C rated value	30 kW
• at 400 V at inside-delta circuit at 40 °C rated value	55 kW
• at 500 V at 40 °C rated value	37 kW
at 500 V at inside-delta circuit at 40 °C rated value	55 kW
Operating frequency 1 rated value	50 Hz
Operating frequency 2 rated value	60 Hz
relative negative tolerance of the operating frequency	-10 %
relative positive tolerance of the operating frequency adjustable motor current	10 %
at rotary coding switch on switch position 1	25.5 A
at rotary coding switch on switch position 2	28 A
at rotary coding switch on switch position 3 at rotary coding switch on switch position 3	30.5 A
 at rotary coding switch on switch position 4 	33 A
, ,	35.5 A
at rotary coding switch on switch position 5 at rotary coding switch on switch position 6	38 A
 at rotary coding switch on switch position 6 at rotary coding switch on switch position 7 	40.5 A
 at rotary coding switch on switch position / at rotary coding switch on switch position 8 	40.5 A 43 A
 at rotary coding switch on switch position 8 at rotary coding switch on switch position 9 	45.5 A
at rotary coding switch on switch position 9 at rotary coding switch on switch position 10	48 A
at rotary coding switch on switch position 10 at rotary coding switch on switch position 11	50.5 A
at rotary coding switch on switch position 11 at rotary coding switch on switch position 12	50.5 A 53 A
at rotary coding switch on switch position 12 at rotary coding switch on switch position 13	55.5 A
at rotary coding switch on switch position 13 at rotary coding switch on switch position 14	58 A
at rotary coding switch on switch position 14 at rotary coding switch on switch position 15	60.5 A
at rotary coding switch on switch position 16 at rotary coding switch on switch position 16	63 A
minimum	25.5 A
adjustable motor current	20.0 A
for inside-delta circuit at rotary coding switch on	44.2 A
switch position 1	
 for inside-delta circuit at rotary coding switch on switch position 2 	48.5 A
 for inside-delta circuit at rotary coding switch on switch position 3 	52.8 A
 for inside-delta circuit at rotary coding switch on switch position 4 	57.2 A
 for inside-delta circuit at rotary coding switch on switch position 5 	61.5 A
 for inside-delta circuit at rotary coding switch on switch position 6 	65.8 A
 for inside-delta circuit at rotary coding switch on switch position 7 	70.1 A
for inside-delta circuit at rotary coding switch on switch position 8 for inside delta circuit at rotary coding switch on	74.5 A
for inside-delta circuit at rotary coding switch on switch position 9 for inside delta circuit at rotary coding switch on	78.8 A 83.1 A
 for inside-delta circuit at rotary coding switch on switch position 10 for inside-delta circuit at rotary coding switch on 	83.1 A 87.5 A
switch position 11 for inside-delta circuit at rotary coding switch on	91.8 A
switch position 12 • for inside-delta circuit at rotary coding switch on	96.1 A
switch position 13 • for inside-delta circuit at rotary coding switch on	100 A
switch position 14 • for inside-delta circuit at rotary coding switch on	105 A
switch position 15	109 A
 for inside-delta circuit at rotary coding switch on switch position 16 at inside-delta circuit minimum 	44.2 A
at inside-delta circuit minimum minimum load [%]	44.2 A 15 %; Relative to smallest settable le
	10 /0, 1/GIALIVE (U SITIALIES) SELIADIE IE
power loss [W] for rated value of the current at AC	

 at 40 °C after startup 	31 W
 at 50 °C after startup 	29 W
at 60 °C after startup	27 W
power loss [W] at AC at current limitation 350 %	
 at 40 °C during startup 	882 W
 at 50 °C during startup 	744 W
 at 60 °C during startup 	659 W
Control circuit/ Control	
type of voltage of the control supply voltage	AC/DC
control supply voltage at AC	
at 50 Hz rated value	24 V
at 60 Hz rated value	24 V
relative negative tolerance of the control supply voltage at AC at 50 Hz	-20 %
relative positive tolerance of the control supply	20 %
voltage at AC at 50 Hz relative negative tolerance of the control supply	-20 %
voltage at AC at 60 Hz	
relative positive tolerance of the control supply voltage at AC at 60 Hz	20 %
control supply voltage frequency	50 60 Hz
relative negative tolerance of the control supply voltage frequency	-10 %
relative positive tolerance of the control supply voltage frequency	10 %
control supply voltage	
at DC rated value	24 V
relative negative tolerance of the control supply voltage at DC	-20 %
relative positive tolerance of the control supply voltage at DC	20 %
control supply current in standby mode rated value	160 mA
holding current in bypass operation rated value	380 mA
locked-rotor current at close of bypass contact maximum	7.6 A
inrush current peak at application of control supply voltage maximum	3.3 A
duration of inrush current peak at application of control supply voltage	12.1 ms
design of the overvoltage protection	Varistor
design of short-circuit protection for control circuit	4 A gG fuse (Icu=1 kA), 6 A quick-acting fuse (Icu=1 kA), C1 miniature circuit breaker (Icu= 600 A), C6 miniature circuit breaker (Icu= 300 A); Is not part of scope of supply
Inputs/ Outputs	
number of digital inputs	1
number of digital outputs	3
not parameterizable	2
digital output version	2 normally-open contacts (NO) / 1 changeover contact (CO)
number of analog outputs	1
switching capacity current of the relay outputs	
 at AC-15 at 250 V rated value 	3 A
at DC-13 at 24 V rated value	1 A
Installation/ mounting/ dimensions	
mounting position	+/- 10° rotation possible and can be tilted forward or backward on vertical mounting surface
fastening method	screw fixing
height	306 mm
width	185 mm
depth	203 mm
required spacing with side-by-side mounting	
forwards	10 mm
backwards	0 mm
• upwards	100 mm

downwards	75 mm
at the side	5 mm
weight without packaging	5.6 kg
Connections/ Terminals	
type of electrical connection	
for main current circuit	box terminal
for control circuit	screw-type terminals
width of connection bar maximum	25 mm
type of connectable conductor cross-sections	
 for main contacts for box terminal using the front clamping point solid 	1x (2.5 16 mm²)
 for main contacts for box terminal using the front clamping point finely stranded with core end processing 	1x (2.5 50 mm²)
 for main contacts for box terminal using the front clamping point stranded 	1x (10 70 mm²)
 at AWG cables for main contacts for box terminal using the front clamping point 	1x (10 2/0)
 for main contacts for box terminal using the back clamping point solid 	1x (2.5 16 mm²)
 at AWG cables for main contacts for box terminal using the back clamping point 	1x (10 2/0)
 for main contacts for box terminal using both clamping points solid 	2x (2.5 16 mm²)
 for main contacts for box terminal using both clamping points finely stranded with core end processing 	2x (2.5 35 mm²)
 for main contacts for box terminal using both clamping points stranded 	2x (6 16 mm²), 2x (10 50 mm²)
 for main contacts for box terminal using the back clamping point finely stranded with core end processing 	1x (2.5 50 mm²)
for main contacts for box terminal using the back clamping point stranded	1x (10 70 mm²)
type of connectable conductor cross-sections	
 for control circuit solid 	1x (0.5 4.0 mm²), 2x (0.5 2.5 mm²)
for control circuit finely stranded with core end processing	1x (0.5 2.5 mm²), 2x (0.5 1.5 mm²)
at AWG cables for control circuit solid	1x (20 12), 2x (20 14)
wire length	900 m
between soft starter and motor maximum at the digital inputs at AC maximum	800 m 100 m
 at the digital inputs at AC maximum at the digital inputs at DC maximum 	1 000 m
tightening torque	. 000 111
for main contacts with screw-type terminals	4.5 6 N·m
for auxiliary and control contacts with screw-type	0.8 1.2 N·m
terminals	
tightening torque [lbf·in]	
 for main contacts with screw-type terminals 	40 53 lbf·in
for auxiliary and control contacts with screw-type terminals.	7 10.3 lbf·in
terminals Ambient conditions	
	5 000 m. Derating as of 1000 m. see catalog
installation altitude at height above sea level maximum ambient temperature	5 000 m; Derating as of 1000 m, see catalog
during operation	-25 +60 °C; Please observe derating at temperatures of 40 °C or above
during storage and transport	-40 +80 °C
environmental category	
 during operation according to IEC 60721 	3K6 (no ice formation, only occasional condensation), 3C3 (no salt mist), 3S2 (sand must not get into the devices), 3M6
 during storage according to IEC 60721 	1K6 (only occasional condensation), 1C2 (no salt mist), 1S2 (sand must not get inside the devices), 1M4
during transport according to IEC 60721	2K2, 2C1, 2S1, 2M2 (max. fall height 0.3 m)
EMC emitted interference	acc. to IEC 60947-4-2: Class A

Communication/ Protocol	
communication module is supported	
PROFINET standard	Yes
EtherNet/IP	Yes
Modbus RTU	Yes
Modbus TCP	Yes
• PROFIBUS	Yes
UL/CSA ratings	
manufacturer's article number	
of circuit breaker	
 usable for Standard Faults at 460/480 V according to UL 	Siemens type: 3RV2742, max. 70 A or 3VA51, max. 125 A; Iq = 10 kA
 usable for High Faults at 460/480 V according to UL 	Siemens type: 3VA51, max. 125 A; lq max = 65 kA
 usable for Standard Faults at 460/480 V at inside-delta circuit according to UL 	Siemens type: 3VA51, max. 125 A; Iq = 10 kA
 usable for High Faults at 460/480 V at inside- delta circuit according to UL 	Siemens type: 3VA51, max. 125 A; Iq max = 65 kA
 usable for Standard Faults at 575/600 V according to UL 	Siemens type: 3RV2742, max. 70 A or 3VA51, max. 125 A; Iq = 10 kA
 usable for Standard Faults at 575/600 V at inside-delta circuit according to UL 	Siemens type: 3VA51, max. 125 A; Iq = 10 kA
of the fuse	
 usable for Standard Faults up to 575/600 V according to UL 	Type: Class RK5 / K5, max. 200 A; Iq = 10 kA
 usable for High Faults up to 575/600 V according to UL 	Type: Class J / L, max. 225 A; Iq = 100 kA
 usable for Standard Faults at inside-delta circuit up to 575/600 V according to UL 	Type: Class RK5 / K5, max. 200 A; Iq = 10 kA
 usable for High Faults at inside-delta circuit up to 575/600 V according to UL 	Type: Class J / L, max. 225 A; lq = 100 kA
operating power [hp] for 3-phase motors	
 at 200/208 V at 50 °C rated value 	15 hp
 at 220/230 V at 50 °C rated value 	20 hp
 at 460/480 V at 50 °C rated value 	40 hp
 at 575/600 V at 50 °C rated value 	50 hp
 at 200/208 V at inside-delta circuit at 50 °C rated value 	30 hp
 at 220/230 V at inside-delta circuit at 50 °C rated value 	30 hp
 at 460/480 V at inside-delta circuit at 50 °C rated value 	75 hp
 at 575/600 V at inside-delta circuit at 50 °C rated value 	75 hp
contact rating of auxiliary contacts according to UL	R300-B300
Safety related data	
protection class IP on the front according to IEC 60529	IP00; IP20 with cover
touch protection on the front according to IEC 60529	finger-safe, for vertical contact from the front with cover
electromagnetic compatibility	in accordance with IEC 60947-4-2
Certificates/ approvals	
General Product Approval	EMC





Confirmation







Declaration of Conformity Test Certificates Marine / Shipping





Type Test Certificates/Test Report







Marine / Shipping

other





Confirmation

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RW5225-1AC05

Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RW5225-1AC05

 $Service \& Support \ (Manuals, \ Certificates, \ Characteristics, \ FAQs, ...)$

https://support.industry.siemens.com/cs/ww/en/ps/3RW5225-1AC05

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RW5225-1AC05&lang=en

Characteristic: Tripping characteristics, I2t, Let-through current


https://support.industry.siemens.com/cs/ww/en/ps/3RW5225-1AC05/char

Characteristic: Installation altitude

http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RW5225-1AC05&objecttype=14&gridview=view1

Simulation Tool for Soft Starters (STS)

https://support.industry.siemens.com/cs/ww/en/view/101494917



last modified: 4/10/2022 🖸