




SUGGEST SOLDERING PAD DIMENSIONS







NOTES:	
--------	--

ECN NO

95158

99313

Ι.	DIALI(
2.	597-60 THIS F
	WITH F
	LED MU
3.	LED i:

ABSOLUTE MAXIMUM RATINGS AT 25° C AMBIENT	VALUES	UNITS	
POWER DISSIPATION	72	mW	
CONTINUOUS FORWARD CURRENT	30	mA	
PEAK FORWARD CURRENT (I/IO DUTY CYCLE, IOms PULSE WIDTH)	125	mA	
REFLOW SOLDERING TEMPERATURE FOR 5 SEC.	260	°C	
OPERATING TEMPERATURE	-40 TO +85	°C	
STORAGE TEMPERATURE	-40 TO +85	°C	

OPERATING CHARACTERISTICS AT 25° C AMBIENT										
LED COLOR	TEST CONDITION (mA)	LUMINOUS INTENSITY (mcd)		FORWARD VOLTAGE (V)		DOMINANT WAVELENGTH (nm)		REVERSE CURRENT (uA)	VIEWING ANGLE (DEGREES)	
	TYP	MIN	TYP	MAX	MIN	MAX	MIN	MAX	MAX	TYP
R E D	20	630	1000	1600	1.8	2.4	620	630	10	30

