# **SIEMENS**

# **Data sheet**

# 6GK5793-8DJ00-0AA0

# product type designation



# Antenna ANT793-8DJ

ANT793-8DJ IWLAN antenna Vertically-horizontally polarized with strong directional effect incl. 2x N-female socket; 18 dBi; IP67 (-45-+70 °C), 5 GHz; Wi-Fi compliance and observe national approvals; mounting on wall or mast; compact instructions as hard copy German/English; scope of delivery: 1x ANT793-8DJ, 1x mounting aid for alignment.

radio frequencies		
type of wireless network / is supported	WLAN	
operating frequency		
<ul> <li>for WLAN in 5 GHz frequency band 1</li> </ul>	5.15 5.875 GHz	
antenna gain compared to spherical radiator		
<ul> <li>of the WLAN antenna / in the 5 GHz frequency band</li> </ul>	18 dB	
electrical data		
impedance	50 Ω	
polarization	Dual linear vertical-horizontal	
radiation characteristic	directional	
antenna gain compared to spherical radiator		
<ul> <li>of the WLAN antenna / in the 5 GHz frequency band</li> </ul>	18 dB	
standing wave ratio (VSWR) / maximum	1.7	
radiating angle of the antenna		
<ul> <li>in the 5 GHz frequency band / horizontal</li> </ul>	17°	
<ul> <li>in the 5 GHz frequency band / vertical</li> </ul>	17°	
number of electrical connections / of the antenna	2	
type of electrical connection / of the antenna	N-Connector	
design of plug-in connection	female	
angle of inclination / downward / maximum	0°	
crosstalk attenuation / between the antenna connections	30 dB	
front-to-back ratio	30 dB	
mechanical data		
material		
<ul><li>of outer shell</li></ul>	Polycarbonate / aluminum	
ambient conditions		
ambient temperature		
<ul> <li>during operation</li> </ul>	-45 +70 °C	
<ul> <li>during storage</li> </ul>	-45 +70 °C	
<ul> <li>during transport</li> </ul>	-45 +70 °C	
protection class IP	IP67	
wind load / maximum	104 N; frontal at 220 km/h	
design, dimensions and weights		
width	190 mm	
height	190 mm	
depth	30.5 mm	
net weight	700 g	
fastening method		

<ul> <li>mast mounting</li> </ul>	Yes
<ul> <li>wall mounting</li> </ul>	Yes
<ul> <li>roof mounting</li> </ul>	No
<ul> <li>directly on the device</li> </ul>	No
standards, specifications, approvals	
certificate of suitability	
RoHS conformity	Yes
product conformity	UL 94-HB
wireless approval	Current national approvals can be found on the Internet under www.siemens.com/funkzulassungen
reference code	
<ul> <li>according to IEC 81346-2</li> </ul>	TF
<ul> <li>according to IEC 81346-2:2019</li> </ul>	TFB
further information / internet-Links	
Internet-Link	
<ul> <li>to web page: selection aid TIA Selection Tool</li> </ul>	http://www.siemens.com/snst
<ul> <li>to website: Industrial communication</li> </ul>	http://www.siemens.com/simatic-net
<ul> <li>to website: Industry Mall</li> </ul>	https://mall.industry.siemens.com
<ul> <li>to website: Information and Download Center</li> </ul>	http://www.siemens.com/industry/infocenter
<ul><li>to website: Image database</li></ul>	http://automation.siemens.com/bilddb
<ul> <li>to website: CAx-Download-Manager</li> </ul>	http://www.siemens.com/cax
<ul> <li>to website: Industry Online Support</li> </ul>	https://support.industry.siemens.com

last modified: 11/3/2021 🖸