
т	۵ ا	п	п	0







LAYOUT SHOWN AS

Keying Shown as example

## CHARACTERISTICS

BASIC SERIES:

SHELL SIZE : 13

PLATING : M = Nickel

Н

SHELL TYPE : Square Flange Receptacle

CONTACT TYPE : Standard Crimp Contact

ω

-Standard : Based on MIL-DTL-38999 Series III

	-Shell Material	: Composite			
	-Shell Plating	: Nickel			
2	-Insulator	: Thermoplastic			
	-Contacts	: Copper Alloy			
	-Seals & Grommet	: Silicon Elastomer			
	-Contact Plating	: Gold over copper Alloy 0.8µm minimum			
	-Durability	: 500 Mating cycles			
	-Delivered with Souriau contacts and Accessories				
	-Temperature Range	65°C to +200°C			
	-Salt Spray	: 2000 hours			
	-Mass	: 18.3 g ± 10%			

8D 0

G

13

Μ

98

В

F


Ν

Dim	Nominal
Р	3.25±0.2
РР	4.93±0.2
R1	23.01
R2	20.62
S	28.6±0.3
V'	19.5+1.4/-0
W'	2.1/3.65
Ζ'	32 Max
VV THREAD	M18x1-6g

CONTACT TYPE : SOCKET(500 Matings)

Е

SOURIAU shall not be liable for due to a use of the Products the Specifications issued by either (professional recomment



					1	
	Φ		А			
A		0			4	
	h (e					
	-					
	1				3	
S EXA	AMPLE					
	non-conformit ch does not co					
er of t	he Parties or b on, technical n	by a third par	ty			
untry		liction & Cont	trol List			
R	541154	Not Listed			2	
3M98BN						
		CUSTOME	R DRAWING	MOD N°	-	
it≏	Recentaci					
	e Receptacle 8D series					
ar			' PROJECT <b>59</b>		1	
	This document is the property of					
I.CC	.COM SOURIAU it must not be reproduced or communicated without permission					
U I	DRG N°			SHEET		
M9	8BN-C			1/2	]	
	В		А			

		۵	гт —	m		0	
		Contact Layout					Panel Cutout
4	د.	$ \begin{pmatrix} \bullet & \bullet \\ \bullet$				SQUARE FLANGE RECEPTACLE ( REAR MOUNTING R1	TYPE 0)
	Contr positio A B C C D E F G G H H J J K	n D  (mm)  (mm)    +.000 (0.00)  +.195 (4.95)    +.125 (3.18)  +.150 (3.81)    +.123 (4.90)  +.030 (0.76)   104 (4.17) 105 (2.67)    +.193 (4.90)  +.015 (3.43)   164 (4.17) 105 (2.67)   193 (4.90)  +.030 (0.76)   125 (3.18)  +.150 (3.81)    +.026 (1.85) 015 (0.38)			₩ ₩		
ω	Shell Arrangement N size no. cc	umber Size Service Contact Supersedes of contacts rating location 10 20 I All MS20051-96					Dim ØA ØAA R1 ØT
						due to a use the Specifications	not be liable for any of the Products whi issued by either of onal recommendati
N							Country FR
						P	N: 8D013N
					A 15-10-202 ISS DATE Designed By:	L6 First Release Latest modificatio Date:	n - by
					TITLE		Composite
<u> </u>					SCALE NA		General linear Tolerances: ±
					SOURIAU	J www.	.SOURIAU.C
					FORMAT A3		SOURIAU 8D013M9
	Н	G	F	E	D	С	

